

P4R

Philips Lightolier C-Plus 4" Miniature Remodel Recessed Non IC Incandescent Downlight

Catalog Number: _____

Type: _____

Project: _____



Description

For remodel construction. Thermally protected recessed housing. Fixture is c/ETL Listed for through-branch circuit wiring and damp location use.

Features

- Compact size permits installation with 2X6 joist construction and as close as 8" on center.
- 50 watt maximum.
- Thermal protection standard.
- c/ETL listed for damp locations and through branch circuit wiring.
- Wide variety of trim options.
- Pre-installed socket.
- Non-IC rated.

CATALOG SYSTEM AND OPTIONS

SAMPLE CATALOG NUMBER: P4R-P4BW

HOUSING___ TRIMS (choose only one)

P4R

- _____
- P4B** – Black Baffle, white flange
- P4BW** – White Baffle, white flange
- P4EW** – White Eyeball
- P4EB** – Black Eyeball
- P4F** – Fresnel lens, white flange, wet location listed
- P4RC** – Clear reflector, white flange
- P4GW** – White adjustable gimball
- P4GB** – Black adjustable gimball
- CP430K6** – CorePro White Splay


General Notes:

See Trims on reverse side of the sheet for lamp compatibility.

SPECIFICATIONS

1. Housing - Deep drawn 22 gauge steel single piece housing painted white. Adjusts vertically in frame to accommodate ceiling thickness up to 1-3/8" thick. Ceiling opening 4-1/4". Accommodates lamp up to 50 watts depending on trim used.
2. Socket- Medium base screw shell porcelain socket attached to adjustable socket supporting bracket.
3. Installation - designed for installation below finished ceiling. Four retractable spring clips hold fixture tight into the ceiling.
4. Junction Box - 14 cu. inch, 18 gauge galvanized steel with two snap-on covers and grounding pigtail. Knock-outs for 1/2" and 3/4" conduit. Meets all safety requirements of c/ETL and N.E.C.
5. Thermal Protection - Standard thermal protection device inside housing automatically takes the fixture out of service if temperature becomes excessive from over lamping or wrong lamp/trim combination.
6. C/ETL Listed - for damp locations and through-branch wiring, 3 in/3 out.
7. Trims - Spun and stamped steel is powder coated in a variety of colors. Features three spring steel, friction fit clips for a secure hold within the housing.

DIMENSIONS



PHILIPS
LIGHTOLIER



P4B Black Baffle w/White Flange
P4BW White Baffle w/White Flange (Shown)
 5" O.D. (127mm)

Lamp	IC
R20	50W
PAR20	50W



P4EW White Eyeball (Shown)
P4EB Black Eyeball
 30° Adjustment
 5" O.D. (127 mm)

Lamp	IC
R20	35W
PAR20	35W



P4F Fresnel Lens/White Flange,
 Wet Location Listed
 5" O.D. (127 mm)

Lamp	IC
R20	35W
PAR20	35W



P4RC Clear Reflector, White Flange (Shown)
 5" O.D. (127 mm)

Lamp	IC
R20	50W
PAR20	50W



P4GW White Adjustable Gimbal (shown)
P4GB Black Adjustable Gimbal
 30° Adjustment
 5" O.D. (127 mm)

Lamp	IC
R20	50W
PAR20	50W



CP430K6 CorePro White Splay
 5-1/2" O.D. (140 mm)

600 lm 30K

