



**PHILIPS
HADCO**

Urban

Baltimore

VX651/VX681



Timeless grace,
fresh technology

Baltimore

LED luminaires

The Philips Hadco Baltimore LED post top luminaires consist of a traditional stately form that has created an industry standard. It offers the style of traditional lanterns with today's cutting edge LEDgine technology. The Baltimore luminaires combine high-performance optical assemblies and money-saving maintenance benefits. For historic areas and new street-scapes Baltimore is available in sizes that are in proportion to most applications including residential streets, city streets, campuses and parking lots.



Benefits

- Seamlessly replaces traditional HID technology.
- Clear, frosted and vertical rib globe panels available.
- Maximizes energy savings to minimize total cost of ownership and significantly reduces maintenance and re-lamping costs.
- Highly efficient IP66 LED engine compartment is protected from the elements and ensure optimal photometric performance.
- Color temperatures 4000K and 3000K are available.
- Dimming driver standard.
- Maximizes energy savings with multiple driver options and programmed dimming options.




Post top (small)



VX651

Dimensions



VX651

Max. EPA: 1.65 sq. ft
Max. Weight: 28 lbs

Lumen range: 2,708-10,172

Wattage range: 38-104

Efficacy range: 69-104



Lumen range: 2,848-12,004

Wattage range: 37-128


Efficacy range: 72-99

Post top (large)



VX681

Dimensions



VX681

Max. EPA: 2.2 sq. ft
Max. Weight: 37.5 lbs

Historical charm for your project

See how **Philips Hadco Baltimore LED** luminaires can add charm with refined and bold styling in your urban projects.

Visit **philips.com/luminaires** for more information.

Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.

