



RBX LED High Bay

15,000 Nominal Delivered Lumens, 4000K, 80 CRI, 22" Clear Acrylic Standard Reflector

15,000 Nominal Delivered Lumens, 4000K, 80 CRI, 22" Clear Acrylic Standard Reflector - 130 lm/W

The RBX LED high bay luminaires have the familiar look and feel of traditional high bay luminaires. Available with acrylic or aluminum reflectors and a variety of lumen packages and color temperatures, the RBX is ideal for retail, industrial, and commercial applications.

Product data

General Information	
Lamp Source Code	LED
Colour Temperature	4000K
CRI	80
Photometric Distribution Type	Direct
Mounting	Suspended
Operating and Electrical	
Voltages	120/208/240/277/347/UNIV V
Luminaire Input Watts	132
Mechanical and Housing	
Fixture Size	22 in
Shape	Round
Approval and Application	
Energy Certifications	DLC Standard

DesignLights Consortium Qualified Product List	
DesignLights Consortium Qualified Product List	
Initial Performance (IEC Compliant)	
Luminaire Lumens	15000
Efficacy	130 lm/W
Product Data	
Order product name	15,000 Nominal Delivered Lumens, 4000K, 80 CRI, 22" Clear Acrylic Standard Reflector
Order code	RBX15L840-ARR22
Material Nr. (12NC)	CFI00001880
Catalog Number	RBX15L840-ARR22
Catalog Number Description	15,000 Nominal Delivered Lumens, 4000K, 80 CRI, 22" Clear Acrylic Standard Reflector