



# FluxPanel LED

2x4, 4800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse

2x4, 4800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse - 105 lm/W

Philips Day-Brite/Philips CFI FluxPanel LED recessed is a highly versatile luminaire designed to provide smooth lighting gradient on the lens surface and ease of installation. Available for use in recessed, suspended, and surface mount orientation, FluxPanel is ideal for general lighting applications such as open office, schools, healthcare, and retail.

## Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	4800
Color Temperature	4000K	Efficacy	105 lm/W
CRI	80		
Mounting	Recessed Surface Suspended		
Operating and Electrical		Product Data	
Luminaire Input Watts	47	Order product name	2x4, 4800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
Voltages	120/277/347/UNIV V	Commercial Code	2FXP48L840-4-DS-UNV-DIM
		Order code	2FXP48L840-4-DS-UNV-DIM
		Catalog Number Description	2x4, 4800 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
		Material Nr. (12NC)	CFI70000754
Mechanical and Housing			
Fixture Size	2 ft x 4 ft		
Shape	Rectangular		