



# FluxPanel LED

2x4, 6000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse

2x4, 6000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse - 100 lm/W

Philips Day-Brite/Philips CFI FluxPanel LED recessed is a highly versatile luminaire designed to provide smooth lighting gradient on the lens surface and ease of installation. Available for use in recessed, suspended, and surface mount orientation, FluxPanel is ideal for general lighting applications such as open office, schools, healthcare, and retail.

## Product data

<b>General Information</b>		<b>Initial Performance (IEC Compliant)</b>	
Lamp Source Code	LED	Luminaire Lumens	6000
Color Temperature	4000K	Efficacy	100 lm/W
CRI	80		
Mounting	Recessed Surface Suspended		
<b>Operating and Electrical</b>		<b>Product Data</b>	
Luminaire Input Watts	58	Order product name	2x4, 6000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
Voltages	120/277/347/UNIV V	Commercial Code	2FXP60L840-4-DS-UNV-DIM
		Order code	2FXP60L840-4-DS-UNV-DIM
		Catalog Number Description	2x4, 6000 Nominal Delivered Lumens, 80 CRI, 4000K, Diffuse
		Material Nr. (12NC)	CFI70000758
<b>Mechanical and Housing</b>			
Fixture Size	2 ft x 4 ft		
Shape	Rectangular		