



Maxos LED Performer – effiziente und präzise Lichtbänder

Maxos LED Performer

Die Verbraucher suchen zunehmend nach Alternativen, die energieeffizienter und kostensparender sind als die bisherige, herkömmliche Beleuchtung. Gleichzeitig müssen in vielen Bereichen aber auch hervorragende Beleuchtungsbedingungen garantiert werden; z.B. in der Industrie, um eine hohe Sicherheit und Produktivität zu gewährleisten, oder im Einzelhandel, wo die Waren besonders attraktiv aussehen sollen. Maxos LED Performer ist eine extrem flexible Lichtbandlösung, die durch LED Technologie wenig Strom verbraucht, hervorragend geformte Lichtbündel ausstrahlt und einen angemessenen Preis hat. Durch die Abdeckung des Lichtträgers kann dieser bis IP40 eingesetzt werden.

Vorteile

- Extrem kurze Amortisationszeit durch LED optimierte Längen von 1,8, 1,5 und 1,2m
- Bahnbrechendes optisches System für präzise geformtes Lichtbündel in vielen Optiken
- Hohe Flexibilität bei Nachrüstungen, Strahlern, Veränderungen, Zubehör

Merkmale

- Geringerer Energieverbrauch als Leuchtstofflampen
- Hervorragend geformtes Lichtbündel reduziert Streulicht durch opale Abdeckung und genauer horizontale und vertikale Lichtverteilung
- Bewährte LED-Module von Philips (Fortimo)
- Kann neu oder als Nachrüstung an Maxos-Schienen montiert werden
- Auch als Ausführung mit flexiblen Paneelen (Maxos LED Panel – 4MX800) oder als hocheffiziente Ausführung (Maxos LED – 4MX850) erhältlich

Maxos LED Performer

Anwendung

- Supermärkte
- Lagerhäuser
- Produktionseinrichtungen

Versions







IPPR1 4MX900i 0001.JPG



IPPR 4MX900i 0003

Abmessungsskizzen



Maxos LED Performer

Produktdetails

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer

Allgemeine Informationen	
CE-Zeichen	Ja
Betriebsgerät inklusive	Ja
ENEC-Zeichen	ENEC-Zeichen
Entflammbarkeitszeichen	-
Glühfadentest	Temperatur: 650 °C, Dauer: 30 s
Lichtquelle austauschbar	Nein
Anzahl Vorschaltgeräte	Einheit
Produktfamiliencode	4MX900
Lichttechnische Daten	
Abstrahlungswinkel der Lichtquelle	120 Grad
Ähnlichste Farbtemperatur (Nom)	4000 K
Farbwiedergabeindex (CRI)	≥80
Betrieb und Elektrik	
Netzfrequenz	50 to 60 Hz
Temperatur	
Umgebungstemperaturbereich	-20 bis +40 °C
Genehmigung und Anwendung	
IEC-Schutzklasse	Schutzklasse I
Schlagfestigkeit (IK)	IK02
Schutzart (IP)	IP40
Initialkennwerte (IEC-konform)	
Lichtstromtoleranz	+/-10%
Anwendungsbedingungen	
Geeignet zum häufigen An- und Ausschalten	Nicht anwendbar

Allgemeine Informationen

Order Code	Full Product Name	Lampenfamiliencode	Lichtregelung
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	-	-
66882399	4MX900 581 LED50S/840 PSD MB WH	LED50S	-
66977699	4MX900 581 LED50S/840 PSD WB WH	LED50S	-
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	LED75S	Konstanter Lichtstrom
66387399	4MX900 LED40S/840 PSD WB WH L1200	LED40S	-
66444399	4MX900 LED60S/840 PSD WB WH L1800	LED60S	-
66445099	4MX900 LED60S/840 PSD MB WH L1800	LED60S	-
66460399	4MX900 LED90S/840 PSD WB WH L1800	LED90S	-
66461099	4MX900 LED90S/840 PSD MB WH L1800	LED90S	-
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S	-
66476499	4MX900 581 LED40S/840 PSU WB WH	LED40S	-
66477199	4MX900 581 LED40S/840 PSU MB WH	LED40S	-
66492499	4MX900 491 LED40S/840 PSU WB WH	LED40S	-
66493199	4MX900 491 LED40S/840 PSU MB WH	LED40S	-
66624999	4MX900 491 LED40S/840 PSD WB WH	LED40S	-
66625699	4MX900 491 LED40S/840 PSD MB WH	LED40S	-
66626399	4MX900 491 LED40S/840 PSD NB WH	LED40S	-
66628799	4MX900 491 LED50S/840 PSD WB WH	LED50S	-
66629499	4MX900 491 LED50S/840 PSD MB WH	LED50S	-
66633199	4MX900 LED40S/840 PSD A30 WH L1200	LED40S	-
66635599	4MX900 LED60S/840 PSD A30 WH L1800	LED60S	-
66636299	4MX900 581 LED40S/840 PSU A30 WH	LED40S	-
66640999	4MX900 581 LED50S/840 PSU WB WH	LED50S	-
66641699	4MX900 581 LED50S/840 PSU MB WH	LED50S	-
66644799	4MX900 491 LED50S/840 PSU WB WH	LED50S	-
66645499	4MX900 491 LED50S/840 PSU MB WH	LED50S	-
66646199	4MX900 491 LED50S/840 PSU NB WH	LED50S	-
66709399	4MX900 581 LED75S/840 PSU A30 WH	LED75S	-
66790199	4MX900 491 LED75S/840 PSU WB WH	LED75S	-
66795699	4MX900 581 LED75S/840 PSU WB WH	LED75S	-
66796399	4MX900 581 LED75S/840 PSU MB WH	LED75S	-
66797099	4MX900 581 LED75S/840 PSU NB WH	LED75S	-
66800799	4MX900 491 LED75S/840 PSD WB WH	LED75S	-
66801499	4MX900 491 LED75S/840 PSD MB WH	LED75S	-
66802199	4MX900 491 LED75S/840 PSD NB WH	LED75S	-
66805299	4MX900 491 LED75S/840 PSD A30 WH	LED75S	-
66806999	4MX900 581 LED75S/840 PSD WB WH	LED75S	-
66807699	4MX900 581 LED75S/840 PSD MB WH	LED75S	-
66811399	4MX900 581 LED75S/840 PSD A30 WH	LED75S	-
66379899	4MX900 LED40S/840 PSD WB SI L1200	LED40S	-
66485699	4MX900 491 LED40S/840 PSU MB SI	LED40S	-

Lichttechnische Daten

Order Code	Full Product Name	Nennlichtausbeute (nom.)	Lichtstrom	Anzahl Lichtquellen	Optik	Order Code	Full Product Name	Nennlichtausbeute (nom.)	Lichtstrom	Anzahl Lichtquellen	Optik
97670899	4MX900 491 LED75S/	149 lm/W	7.500 lm	-	Breitstrahlend (WB)	840	PSD-				

Maxos LED Performer

Full						Full					
Order	Product	Nennlichtausbeute		Anzahl		Order	Product	Nennlichtausbeute		Anzahl	
Code	Name	(nom.)	Lichtstrom	Lichtquellen	Optik	Code	Name	(nom.)	Lichtstrom	Lichtquellen	Optik
	CLO WB					66476499	4MX900	159 lm/W	4.000 lm	1	Breitstrahlend (WB)
	WH						581				
66882399	4MX900	155 lm/W	5.000 lm	-	Tiefbreitstrahlend (MB)		LED40S/				
	581						840 PSU				
	LED50S/						WB WH				
	840 PSD					66477199	4MX900	159 lm/W	4.000 lm	1	Tiefbreitstrahlend (MB)
	MB WH						581				
66977699	4MX900	155 lm/W	5.000 lm	-	Breitstrahlend (WB)		LED40S/				
	581						840 PSU				
	LED50S/						MB WH				
	840 PSD					66492499	4MX900	159 lm/W	4.000 lm	1	Breitstrahlend (WB)
	WB WH						491				
87967299	4MX900	149 lm/W	7.500 lm	1	Tiefbreitstrahlend (MB)		LED40S/				
	581						840 PSU				
	LED75S/						WB WH				
	840					66493199	4MX900	159 lm/W	4.000 lm	1	Tiefbreitstrahlend (MB)
	PSD-						491				
	CLO MB						LED40S/				
	WH						840 PSU				
66387399	4MX900	154 lm/W	4.000 lm	1	Breitstrahlend (WB)		MB WH				
	LED40S/					66624999	4MX900	159 lm/W	4.000 lm	1	Breitstrahlend (WB)
	840 PSD						491				
	WB WH						LED40S/				
	L1200						840 PSD				
66444399	4MX900	161 lm/W	6.000 lm	1	Breitstrahlend (WB)		WB WH				
	LED60S/					66625699	4MX900	159 lm/W	4.000 lm	1	Tiefbreitstrahlend (MB)
	840 PSD						491				
	WB WH						LED40S/				
	L1800						840 PSD				
66445099	4MX900	161 lm/W	6.000 lm	1	Tiefbreitstrahlend (MB)		MB WH				
	LED60S/					66626399	4MX900	159 lm/W	4.000 lm	1	Tiefstrahlend (NB)
	840 PSD						491				
	MB WH						LED40S/				
	L1800						840 PSD				
66460399	4MX900	150 lm/W	9.000 lm	1	Breitstrahlend (WB)		NB WH				
	LED90S/					66628799	4MX900	155 lm/W	5.000 lm	1	Breitstrahlend (WB)
	840 PSD						491				
	WB WH						LED50S/				
	L1800						840 PSD				
66461099	4MX900	150 lm/W	9.000 lm	1	Tiefbreitstrahlend (MB)		WB WH				
	LED90S/					66629499	4MX900	155 lm/W	5.000 lm	1	Tiefbreitstrahlend (MB)
	840 PSD						491				
	MB WH						LED50S/				
	L1800						840 PSD				
66463499	4MX900	150 lm/W	9.000 lm	1	Doppelt asymmetrische		MB WH				
	LED90S/				Optik (20°)	66633199	4MX900	154 lm/W	4.000 lm	1	Asymmetrischer
	840 PSD						LED40S/				SpiegelAbstrahlungswinkel
	DA20						840 PSD				(30°)
	WH						A30 WH				
	L1800						L1200				

Maxos LED Performer

Full						Full					
Order	Product	Nennlichtausbeute		Anzahl		Order	Product	Nennlichtausbeute		Anzahl	
Code	Name	(nom.)	Lichtstrom	Lichtquellen	Optik	Code	Name	(nom.)	Lichtstrom	Lichtquellen	Optik
66635599	4MX900 LED60S/ 840 PSD A30 WH L1800	161 lm/W	6.000 lm	1	Asymmetrischer SpiegelAbstrahlungswinkel (30°)	66796399	4MX900 581 LED75S/ 840 PSU MB WH	149 lm/W	7.500 lm	1	Tiefbreitstrahlend (MB)
66636299	4MX900 581 LED40S/ 840 PSU A30 WH	159 lm/W	4.000 lm	1	Asymmetrischer SpiegelAbstrahlungswinkel (30°)	66797099	4MX900 581 LED75S/ 840 PSU NB WH	149 lm/W	7.500 lm	1	Tiefstrahlend (NB)
66640999	4MX900 581 LED50S/ 840 PSU WB WH	155 lm/W	5.000 lm	1	Breitstrahlend (WB)	66800799	4MX900 491 LED75S/ 840 PSD WB WH	149 lm/W	7.500 lm	1	Breitstrahlend (WB)
66641699	4MX900 581 LED50S/ 840 PSU MB WH	155 lm/W	5.000 lm	1	Tiefbreitstrahlend (MB)	66801499	4MX900 491 LED75S/ 840 PSD MB WH	149 lm/W	7.500 lm	1	Tiefbreitstrahlend (MB)
66644799	4MX900 491 LED50S/ 840 PSU WB WH	155 lm/W	5.000 lm	1	Breitstrahlend (WB)	66802199	4MX900 491 LED75S/ 840 PSD NB WH	149 lm/W	7.500 lm	1	Tiefstrahlend (NB)
66645499	4MX900 491 LED50S/ 840 PSU MB WH	155 lm/W	5.000 lm	1	Tiefbreitstrahlend (MB)	66805299	4MX900 491 LED75S/ 840 PSD A30 WH	149 lm/W	7.500 lm	1	Asymmetrischer SpiegelAbstrahlungswinkel (30°)
66646199	4MX900 491 LED50S/ 840 PSU NB WH	155 lm/W	5.000 lm	1	Tiefstrahlend (NB)	66806999	4MX900 581 LED75S/ 840 PSD WB WH	149 lm/W	7.500 lm	1	Breitstrahlend (WB)
66709399	4MX900 581 LED75S/ 840 PSU A30 WH	149 lm/W	7.500 lm	1	Asymmetrischer SpiegelAbstrahlungswinkel (30°)	66807699	4MX900 581 LED75S/ 840 PSD MB WH	149 lm/W	7.500 lm	1	Tiefbreitstrahlend (MB)
66790199	4MX900 491 LED75S/ 840 PSU WB WH	149 lm/W	7.500 lm	1	Breitstrahlend (WB)	66811399	4MX900 581 LED75S/ 840 PSD A30 WH	149 lm/W	7.500 lm	1	Asymmetrischer SpiegelAbstrahlungswinkel (30°)
66795699	4MX900 581 LED75S/ 840 PSU WB WH	149 lm/W	7.500 lm	1	Breitstrahlend (WB)	66379899	4MX900 LED40S/ 840 PSD WB SI L1200	154 lm/W	4.000 lm	1	Breitstrahlend (WB)

Maxos LED Performer

Order Code	Full					Order Code	Full				
	Product	Nennlichtausbeute	Anzahl				Product	Nennlichtausbeute	Anzahl		
	Name	(nom.)	Lichtstrom	Lichtquellen	Optik		Name	(nom.)	Lichtstrom	Lichtquellen	Optik
66485699	4MX900	159 lm/W	4.000 lm	1	Tiefbreitstrahlend (MB)	840 PSU					
	491					MB SI					
	LED40S/										

Betrieb und Elektrik

Order Code	Full Product Name	Eingangsspannung	Energieverbrauch	Order Code	Full Product Name	Eingangsspannung	Energieverbrauch
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	220 bis 240 V	50,2 W	66636299	4MX900 581 LED40S/840 PSU A30 WH	220 bis 240 V	25,2 W
66882399	4MX900 581 LED50S/840 PSD MB WH	220 bis 240 V	32,2 W	66640999	4MX900 581 LED50S/840 PSU WB WH	220 bis 240 V	32,2 W
66977699	4MX900 581 LED50S/840 PSD WB WH	220-240 V	32,2 W	66641699	4MX900 581 LED50S/840 PSU MB WH	220 bis 240 V	32,2 W
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	220 bis 240 V	50,2 W	66644799	4MX900 491 LED50S/840 PSU WB WH	220 bis 240 V	32,2 W
66387399	4MX900 LED40S/840 PSD WB WH L1200	220 bis 240 V	25,9 W	66645499	4MX900 491 LED50S/840 PSU MB WH	220 bis 240 V	32,2 W
66444399	4MX900 LED60S/840 PSD WB WH L1800	220 bis 240 V	37,3 W	66646199	4MX900 491 LED50S/840 PSU NB WH	220 bis 240 V	32,2 W
66445099	4MX900 LED60S/840 PSD MB WH L1800	220 bis 240 V	37,3 W	66709399	4MX900 581 LED75S/840 PSU A30 WH	220 bis 240 V	50,2 W
66460399	4MX900 LED90S/840 PSD WB WH L1800	220 bis 240 V	60,1 W	66790199	4MX900 491 LED75S/840 PSU WB WH	220 bis 240 V	50,2 W
66461099	4MX900 LED90S/840 PSD MB WH L1800	220 bis 240 V	60,1 W	66795699	4MX900 581 LED75S/840 PSU WB WH	220 bis 240 V	50,2 W
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	220 bis 240 V	60,1 W	66796399	4MX900 581 LED75S/840 PSU MB WH	220 bis 240 V	50,2 W
66476499	4MX900 581 LED40S/840 PSU WB WH	220 bis 240 V	25,2 W	66797099	4MX900 581 LED75S/840 PSU NB WH	220 bis 240 V	50,2 W
66477199	4MX900 581 LED40S/840 PSU MB WH	220 bis 240 V	25,2 W	66800799	4MX900 491 LED75S/840 PSD WB WH	220 bis 240 V	50,2 W
66492499	4MX900 491 LED40S/840 PSU WB WH	220 bis 240 V	25,2 W	66801499	4MX900 491 LED75S/840 PSD MB WH	220 bis 240 V	50,2 W
66493199	4MX900 491 LED40S/840 PSU MB WH	220 bis 240 V	25,2 W	66802199	4MX900 491 LED75S/840 PSD NB WH	220 bis 240 V	50,2 W
66624999	4MX900 491 LED40S/840 PSD WB WH	220 bis 240 V	25,2 W	66805299	4MX900 491 LED75S/840 PSD A30 WH	220 bis 240 V	50,2 W
66625699	4MX900 491 LED40S/840 PSD MB WH	220 bis 240 V	25,2 W	66806999	4MX900 581 LED75S/840 PSD WB WH	220 bis 240 V	50,2 W
66626399	4MX900 491 LED40S/840 PSD NB WH	220 bis 240 V	25,2 W	66807699	4MX900 581 LED75S/840 PSD MB WH	220 bis 240 V	50,2 W
66628799	4MX900 491 LED50S/840 PSD WB WH	220 bis 240 V	32,2 W	66811399	4MX900 581 LED75S/840 PSD A30 WH	220 bis 240 V	50,2 W
66629499	4MX900 491 LED50S/840 PSD MB WH	220 bis 240 V	32,2 W	66379899	4MX900 LED40S/840 PSD WB SI L1200	220 bis 240 V	25,9 W
66633199	4MX900 LED40S/840 PSD A30 WH L1200	220 bis 240 V	25,9 W	66485699	4MX900 491 LED40S/840 PSU MB SI	220 bis 240 V	25,2 W
66635599	4MX900 LED60S/840 PSD A30 WH L1800	220 bis 240 V	37,3 W				

Lichtregelung und Dimmen

Order Code	Full Product Name	Dimmbar
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	Ja
66882399	4MX900 581 LED50S/840 PSD MB WH	Ja
66977699	4MX900 581 LED50S/840 PSD WB WH	Ja
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	Ja
66387399	4MX900 LED40S/840 PSD WB WH L1200	Ja
66444399	4MX900 LED60S/840 PSD WB WH L1800	Ja
66445099	4MX900 LED60S/840 PSD MB WH L1800	Ja
66460399	4MX900 LED90S/840 PSD WB WH L1800	Ja
66461099	4MX900 LED90S/840 PSD MB WH L1800	Ja
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Ja
66476499	4MX900 581 LED40S/840 PSU WB WH	Nein
66477199	4MX900 581 LED40S/840 PSU MB WH	Nein
66492499	4MX900 491 LED40S/840 PSU WB WH	Nein
66493199	4MX900 491 LED40S/840 PSU MB WH	Nein
66624999	4MX900 491 LED40S/840 PSD WB WH	Ja
66625699	4MX900 491 LED40S/840 PSD MB WH	Ja
66626399	4MX900 491 LED40S/840 PSD NB WH	Ja
66628799	4MX900 491 LED50S/840 PSD WB WH	Ja
66629499	4MX900 491 LED50S/840 PSD MB WH	Ja
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Ja
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Ja

Order Code	Full Product Name	Dimmbar
66636299	4MX900 581 LED40S/840 PSU A30 WH	Nein
66640999	4MX900 581 LED50S/840 PSU WB WH	Nein
66641699	4MX900 581 LED50S/840 PSU MB WH	Nein
66644799	4MX900 491 LED50S/840 PSU WB WH	Nein
66645499	4MX900 491 LED50S/840 PSU MB WH	Nein
66646199	4MX900 491 LED50S/840 PSU NB WH	Nein
66709399	4MX900 581 LED75S/840 PSU A30 WH	Nein
66790199	4MX900 491 LED75S/840 PSU WB WH	Nein
66795699	4MX900 581 LED75S/840 PSU WB WH	Nein
66796399	4MX900 581 LED75S/840 PSU MB WH	Nein
66797099	4MX900 581 LED75S/840 PSU NB WH	Nein
66800799	4MX900 491 LED75S/840 PSD WB WH	Ja
66801499	4MX900 491 LED75S/840 PSD MB WH	Ja
66802199	4MX900 491 LED75S/840 PSD NB WH	Ja
66805299	4MX900 491 LED75S/840 PSD A30 WH	Ja
66806999	4MX900 581 LED75S/840 PSD WB WH	Ja
66807699	4MX900 581 LED75S/840 PSD MB WH	Ja
66811399	4MX900 581 LED75S/840 PSD A30 WH	Ja
66379899	4MX900 LED40S/840 PSD WB SI L1200	Ja
66485699	4MX900 491 LED40S/840 PSU MB SI	Nein

Mechanik und Gehäuse

Order Code	Full Product Name	Gehäusefarbe
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	Weiß
66882399	4MX900 581 LED50S/840 PSD MB WH	Weiß
66977699	4MX900 581 LED50S/840 PSD WB WH	Weiß
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	Weiß
66387399	4MX900 LED40S/840 PSD WB WH L1200	Weiß
66444399	4MX900 LED60S/840 PSD WB WH L1800	Weiß
66445099	4MX900 LED60S/840 PSD MB WH L1800	Weiß
66460399	4MX900 LED90S/840 PSD WB WH L1800	Weiß
66461099	4MX900 LED90S/840 PSD MB WH L1800	Weiß
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	Weiß
66476499	4MX900 581 LED40S/840 PSU WB WH	Weiß
66477199	4MX900 581 LED40S/840 PSU MB WH	Weiß
66492499	4MX900 491 LED40S/840 PSU WB WH	Weiß
66493199	4MX900 491 LED40S/840 PSU MB WH	Weiß
66624999	4MX900 491 LED40S/840 PSD WB WH	Weiß
66625699	4MX900 491 LED40S/840 PSD MB WH	Weiß
66626399	4MX900 491 LED40S/840 PSD NB WH	Weiß
66628799	4MX900 491 LED50S/840 PSD WB WH	Weiß
66629499	4MX900 491 LED50S/840 PSD MB WH	Weiß
66633199	4MX900 LED40S/840 PSD A30 WH L1200	Weiß
66635599	4MX900 LED60S/840 PSD A30 WH L1800	Weiß

Order Code	Full Product Name	Gehäusefarbe
66636299	4MX900 581 LED40S/840 PSU A30 WH	Weiß
66640999	4MX900 581 LED50S/840 PSU WB WH	Weiß
66641699	4MX900 581 LED50S/840 PSU MB WH	Weiß
66644799	4MX900 491 LED50S/840 PSU WB WH	Weiß
66645499	4MX900 491 LED50S/840 PSU MB WH	Weiß
66646199	4MX900 491 LED50S/840 PSU NB WH	Weiß
66709399	4MX900 581 LED75S/840 PSU A30 WH	Weiß
66790199	4MX900 491 LED75S/840 PSU WB WH	Weiß
66795699	4MX900 581 LED75S/840 PSU WB WH	Weiß
66796399	4MX900 581 LED75S/840 PSU MB WH	Weiß
66797099	4MX900 581 LED75S/840 PSU NB WH	Weiß
66800799	4MX900 491 LED75S/840 PSD WB WH	Weiß
66801499	4MX900 491 LED75S/840 PSD MB WH	Weiß
66802199	4MX900 491 LED75S/840 PSD NB WH	Weiß
66805299	4MX900 491 LED75S/840 PSD A30 WH	Weiß
66806999	4MX900 581 LED75S/840 PSD WB WH	Weiß
66807699	4MX900 581 LED75S/840 PSD MB WH	Weiß
66811399	4MX900 581 LED75S/840 PSD A30 WH	Weiß
66379899	4MX900 LED40S/840 PSD WB SI L1200	Silber
66485699	4MX900 491 LED40S/840 PSU MB SI	Silber

Initialkennwerte (IEC-konform)

Maxos LED Performer

Order Code	Full Product Name	Anfängliche Farbsättigung
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5
66882399	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66977699	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5
66387399	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5
66444399	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66445099	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66460399	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38) SDCM <3.5
66461099	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38) SDCM <3.5
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	(0.38, 0.38) SDCM <3.5
66476499	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66477199	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66492499	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66493199	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66624999	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66625699	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66626399	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66628799	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66629499	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66633199	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5
66635599	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5


Order Code	Full Product Name	Anfängliche Farbsättigung
66636299	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66640999	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66641699	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66644799	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66645499	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66646199	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
66709399	4MX900 581 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5
66790199	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66795699	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5
66796399	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5
66797099	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5
66800799	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66801499	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66802199	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5
66805299	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
66806999	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5
66807699	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5
66811399	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38) SDCM <3.5
66379899	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38) SDCM <3.5
66485699	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3

Anwendungsbedingungen


Order Code	Full Product Name	Maximaler Dimmlevel
97670899	4MX900 491 LED75S/840 PSD-CLO WB WH	1%
66882399	4MX900 581 LED50S/840 PSD MB WH	1%
66977699	4MX900 581 LED50S/840 PSD WB WH	1%
87967299	4MX900 581 LED75S/840 PSD-CLO MB WH	1%
66387399	4MX900 LED40S/840 PSD WB WH L1200	1%
66444399	4MX900 LED60S/840 PSD WB WH L1800	1%
66445099	4MX900 LED60S/840 PSD MB WH L1800	1%
66460399	4MX900 LED90S/840 PSD WB WH L1800	1%
66461099	4MX900 LED90S/840 PSD MB WH L1800	1%
66463499	4MX900 LED90S/840 PSD DA20 WH L1800	1%
66476499	4MX900 581 LED40S/840 PSU WB WH	Nicht anwendbar
66477199	4MX900 581 LED40S/840 PSU MB WH	Nicht anwendbar
66492499	4MX900 491 LED40S/840 PSU WB WH	Nicht anwendbar
66493199	4MX900 491 LED40S/840 PSU MB WH	Nicht anwendbar
66624999	4MX900 491 LED40S/840 PSD WB WH	1%
66625699	4MX900 491 LED40S/840 PSD MB WH	1%
66626399	4MX900 491 LED40S/840 PSD NB WH	1%
66628799	4MX900 491 LED50S/840 PSD WB WH	1%
66629499	4MX900 491 LED50S/840 PSD MB WH	1%
66633199	4MX900 LED40S/840 PSD A30 WH L1200	1%
66635599	4MX900 LED60S/840 PSD A30 WH L1800	1%

Order Code	Full Product Name	Maximaler Dimmlevel
66636299	4MX900 581 LED40S/840 PSU A30 WH	Nicht anwendbar
66640999	4MX900 581 LED50S/840 PSU WB WH	Nicht anwendbar
66641699	4MX900 581 LED50S/840 PSU MB WH	Nicht anwendbar
66644799	4MX900 491 LED50S/840 PSU WB WH	Nicht anwendbar
66645499	4MX900 491 LED50S/840 PSU MB WH	Nicht anwendbar
66646199	4MX900 491 LED50S/840 PSU NB WH	Nicht anwendbar
66709399	4MX900 581 LED75S/840 PSU A30 WH	Nicht anwendbar
66790199	4MX900 491 LED75S/840 PSU WB WH	Nicht anwendbar
66795699	4MX900 581 LED75S/840 PSU WB WH	Nicht anwendbar
66796399	4MX900 581 LED75S/840 PSU MB WH	Nicht anwendbar
66797099	4MX900 581 LED75S/840 PSU NB WH	Nicht anwendbar
66800799	4MX900 491 LED75S/840 PSD WB WH	1%
66801499	4MX900 491 LED75S/840 PSD MB WH	1%
66802199	4MX900 491 LED75S/840 PSD NB WH	1%
66805299	4MX900 491 LED75S/840 PSD A30 WH	1%
66806999	4MX900 581 LED75S/840 PSD WB WH	1%
66807699	4MX900 581 LED75S/840 PSD MB WH	1%
66811399	4MX900 581 LED75S/840 PSD A30 WH	1%
66379899	4MX900 LED40S/840 PSD WB SI L1200	1%
66485699	4MX900 491 LED40S/840 PSU MB SI	Nicht anwendbar


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSU NB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)



IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED50S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 491 1xLED71S/830 PSD A30-
Polar Normal (separate)


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 581 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED50S/840 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED71S/830 PSU NB-Polar
Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED57S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1200 1xLED60S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED48S/840 PSD
DA20-Polar Normal (separate)**



IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)






IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)



IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)




Polar Wide Diagrams



**IFPS_4MX900 G3 491 1xLED40S/830 PSD
A30-Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/830 PSU NB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**


**IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**

**IFPS_4MX900 G3 491 1xLED40S/840 PSU MB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU MB-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 G3 491 1xLED50S/840 PSU NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED75S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED75S/840 PSU NB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)




**IFPS_4MX900 G3 581 1xLED40S/830 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**


Polar Wide Diagrams




**IFPS_4MX900 G3 581 1xLED50S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED71S/830 PSU NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED75S/840 PSD A30-
Polar Normal (separate)**


Polar Wide Diagrams




IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU A30-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-
Polar Normal (separate)




IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
MB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)



IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)

Maxos LED Performer

