



Maxos LED Performer – efficient and precise line lighting

Maxos LED Performer

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Benefits

- Extremely fast payback
- Breakthrough optical system for precise beam shaping
- Flexible in terms of retrofits, spots, changes, accessories

Features

- Low energy consumption compared to fluorescent
- Excellent beam shaping for less spill light and exact light distribution in horizontal and vertical planes
- Proven Philips LED engines (Fortimo)
- Can be mounted, new or retrofit, onto a Maxos rail
- Also available in a flexible panel version 4MX800 or high-efficiency version 4MX850

Application

- Supermarkets
- Warehouses
- Production facilities

Specifications

Maxos LED Performer

Type	4MX900
Light source	Philips Fortimo LED Line 1R
Power	1.2 m version: 27 to 53 W 1.5 m version: 31 to 65 W 1.8 m version: 40 to 78 W
Beam angle	2 x 50° (Wide beam) 2 x 34° (Medium beam) 2 x 25° (Narrow beam) 2 x 20° DA-20 (Double asymmetric) 2 x 30° DA-30 (Double asymmetric) 1 x 30° A-30 (Asymmetric)
Luminous flux	1.2 m version: 3200 or 6000 lm 1.5 m version: 4000, 5000 or 7500 lm 1.8 m version: 4800, 6000 or 9000 lm
Correlated Color Temperature	3000 or 4000 K
Color Rendering Index	> 80
Median useful life	70,000 hours
L70B50	
Median useful life	50,000 hours
L80B50	
Median useful life	25,000 hours
L90B50	

Driver failure rate	1% per 5000 hours
Average ambient temperature	+25 °C
Operating temperature range	-20 to +35 °C
Driver	Philips Xitanium
Power/Data supply	27 to 78 W depending on the version
Mains voltage	220-240 V / 50-60 Hz
Options	EL central or EL3 with battery possible
Dimming	DALI dimmable and fixed output versions
Controls system input	DALI
Material	Gear tray: aluminum Lens plate: PMMA, PC for EL and EL3 versions
Color	White (WH) Silver (SI)
Optical cover	PMMA, PC (for EL and EL3 versions)
Connection	Electrical contact via standard Maxos through-wiring connector
Maintenance	Module can be clicked out, driver can be serviced
Installation	Fixation of the 4MX900 unit on the Maxos trunking with springs Suspended or surface (ceiling) mounted
Accessories	Maxos accessory range

Versions



Maxos LED Performer 4MX900 electrical unit



Maxos LED Performer - LED Module, system flux 5000 lm



Maxos LED Performer 4MX900 electrical unit

Maxos LED Performer

Product details

Top view of insert



Partial side view



Front view with suspension



Close-up view from below



Close-up view from below



Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Ingress protection code IP40

General Information

CE mark CE mark

Protection class IEC Safety class I

Driver included Yes

Flammability mark For mounting on easily flammable surfaces

Light source replaceable No

Application Conditions

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	1%	Not applicable
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	1%	Not applicable
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	1%	Not applicable
910629132426	4MX900 LED40S/840 PSD WB WH L1200	1%	Not applicable
910629132526	4MX900 LED40S/840 PSD MB WH L1200	1%	Not applicable
910629132626	4MX900 LED40S/840 PSD NB WH L1200	1%	Not applicable
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	1%	Not applicable
910629132826	4MX900 LED40S/830 PSD WB WH L1200	1%	Not applicable
910629137226	4MX900 LED60S/840 PSD WB WH L1800	1%	Not applicable
910629137326	4MX900 LED60S/840 PSD MB WH L1800	1%	Not applicable
910629137426	4MX900 LED60S/840 PSD NB WH L1800	1%	Not applicable
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	1%	Not applicable
910629137626	4MX900 LED60S/830 PSD WB WH L1800	1%	Not applicable
910629137726	4MX900 LED60S/830 PSD MB WH L1800	1%	Not applicable
910629138826	4MX900 LED90S/840 PSD WB WH L1800	1%	Not applicable
910629138926	4MX900 LED90S/840 PSD MB WH L1800	1%	Not applicable
910629139026	4MX900 LED90S/840 PSD NB WH L1800	1%	Not applicable
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	1%	Not applicable
910629139226	4MX900 LED90S/830 PSD WB WH L1800	1%	Not applicable
910629140426	4MX900 581 LED40S/840 PSU WB WH	-	Not applicable
910629140526	4MX900 581 LED40S/840 PSU MB WH	-	Not applicable
910629140926	4MX900 581 LED40S/830 PSU MB WH	-	Not applicable
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	-	Not applicable
910629142026	4MX900 491 LED40S/840 PSU WB WH	-	Not applicable
910629142126	4MX900 491 LED40S/840 PSU MB WH	-	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910629142426	4MX900 491 LED40S/830 PSU WB WH	-	Not applicable
910629143226	4MX900 LED40S/840 PSU WB WH L1200	-	Not applicable
910629144426	4MX900 491 LED40S/840 PSD WB WH	1%	Not applicable
910629144526	4MX900 491 LED40S/840 PSD MB WH	1%	Not applicable
910629144626	4MX900 491 LED40S/840 PSD NB WH	1%	Not applicable
910629144826	4MX900 491 LED50S/840 PSD WB WH	1%	Not applicable
910629144926	4MX900 491 LED50S/840 PSD MB WH	1%	Not applicable
910629145026	4MX900 491 LED50S/840 PSD NB WH	1%	Not applicable
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	1%	Not applicable
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	1%	Not applicable
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	1%	Not applicable
910629145626	4MX900 581 LED40S/840 PSU A30 WH	-	Not applicable
910629145726	4MX900 581 LED50S/840 PSU A30 WH	-	Not applicable
910629145826	4MX900 491 LED40S/840 PSU A30 WH	-	Not applicable
910629145926	4MX900 491 LED50S/840 PSU A30 WH	-	Not applicable
910629146026	4MX900 581 LED50S/840 PSU WB WH	-	Not applicable
910629146126	4MX900 581 LED50S/840 PSU MB WH	-	Not applicable
910629146426	4MX900 491 LED50S/840 PSU WB WH	-	Not applicable
910629146526	4MX900 491 LED50S/840 PSU MB WH	-	Not applicable
910629146626	4MX900 491 LED50S/840 PSU NB WH	-	Not applicable
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	1%	Not applicable
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	1%	Not applicable
910629148126	4MX900 491 LED40S/830 PSU A30 WH	-	Not applicable
910629148226	4MX900 491 LED50S/830 PSU A30 WH	-	Not applicable
910629148326	4MX900 581 LED75S/840 PSU A30 WH	-	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910629148526	4MX900 491 LED75S/840 PSU A30 WH	-	Not applicable
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	-	Not applicable
910629170326	4MX900 491 LED75S/840 PSU WB WH	-	Not applicable
910629170426	4MX900 491 LED75S/840 PSU MB WH	-	Not applicable
910629170826	4MX900 581 LED75S/840 PSU WB WH	-	Not applicable
910629170926	4MX900 581 LED75S/840 PSU MB WH	-	Not applicable
910629171026	4MX900 581 LED75S/840 PSU NB WH	-	Not applicable
910629171326	4MX900 491 LED75S/840 PSD WB WH	1%	Not applicable
910629171426	4MX900 491 LED75S/840 PSD MB WH	1%	Not applicable
910629171526	4MX900 491 LED75S/840 PSD NB WH	1%	Not applicable
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	1%	Yes
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	1%	Not applicable
910629171826	4MX900 491 LED75S/840 PSD A30 WH	1%	Not applicable
910629171926	4MX900 581 LED75S/840 PSD WB WH	1%	Not applicable
910629172026	4MX900 581 LED75S/840 PSD MB WH	1%	Not applicable
910629172126	4MX900 581 LED75S/840 PSD NB WH	1%	Not applicable
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	1%	Not applicable
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	1%	Not applicable
910629172426	4MX900 581 LED75S/840 PSD A30 WH	1%	Not applicable
910629173226	4MX900 581 LED50S/840 PSD A30 WH	1%	Not applicable
910629177426	4MX900 491 LED75S/830 PSD WB WH	1%	Not applicable
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	1%	Not applicable
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	1%	Not applicable
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	1%	Not applicable
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	1%	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	1%	Not applicable
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	1%	Not applicable
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	1%	Not applicable
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	1%	Not applicable
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	1%	Not applicable
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	1%	Not applicable
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	1%	Not applicable
910500460309	4MX900 581 LED40S/840 PSD MB WH	1%	Not applicable
910500460310	4MX900 581 LED40S/840 PSD NB WH	1%	Not applicable
910500460311	4MX900 581 LED40S/840 PSD WB WH	1%	Not applicable
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	1%	Not applicable
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	1%	Not applicable
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	1%	Not applicable
910500460315	4MX900 581 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460316	4MX900 581 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460317	4MX900 581 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460318	4MX900 581 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	1%	Not applicable
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	1%	Not applicable
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	1%	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	1%	Not applicable
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	1%	Not applicable
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	1%	Not applicable
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	-	Not applicable
910500460327	4MX916 491 LED50S/840 PSU MB WH	-	Not applicable
910500460328	4MX916 491 LED50S/840 PSU NB WH	-	Not applicable
910500460329	4MX916 491 LED50S/840 PSU WB WH	-	Not applicable
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	-	Not applicable
910500460343	4MX916 581 LED50S/840 PSU MB WH	-	Not applicable
910500460344	4MX916 581 LED50S/840 PSU NB WH	-	Not applicable
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	1%	Not applicable
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	1%	Not applicable
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	1%	Not applicable
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	-	Not applicable
910500460359	4MX933 491 LED50S/840 PSU MB WH	-	Not applicable
910500460360	4MX933 491 LED50S/840 PSU NB WH	-	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500460361	4MX933 491 LED50S/840 PSU WB WH	-	Not applicable
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	1%	Not applicable
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	1%	Not applicable
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	1%	Not applicable
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	-	Not applicable
910500460375	4MX933 581 LED50S/840 PSU MB WH	-	Not applicable
910500460377	4MX933 581 LED50S/840 PSU WB WH	-	Not applicable
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	1%	Not applicable
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	1%	Not applicable
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	1%	Not applicable
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	1%	Not applicable
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	1%	Not applicable
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	1%	Not applicable
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	1%	Not applicable
910629173126	4MX900 581 LED50S/840 PSD MB WH	1%	Not applicable
910629177026	4MX900 581 LED50S/840 PSD WB WH	1%	Not applicable
910629131626	4MX900 LED40S/840 PSD WB SI L1200	1%	Not applicable
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	1%	Not applicable
910629136426	4MX900 LED60S/840 PSD WB SI L1800	1%	Not applicable

Maxos LED Performer

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	1%	Not applicable
910629136826	4MX900 LED60S/830 PSD WB SI L1800	1%	Not applicable
910629136926	4MX900 LED60S/830 PSD MB SI L1800	1%	Not applicable
910629138026	4MX900 LED90S/840 PSD WB SI L1800	1%	Not applicable
910629138126	4MX900 LED90S/840 PSD MB SI L1800	1%	Not applicable
910629138426	4MX900 LED90S/830 PSD WB SI L1800	1%	Not applicable

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910629141226	4MX900 491 LED40S/840 PSU WB SI	-	Not applicable
910629141326	4MX900 491 LED40S/840 PSU MB SI	-	Yes
910629141626	4MX900 491 LED40S/830 PSU WB SI	-	Not applicable
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	1%	Not applicable
910629172926	4MX900 LED40S/840 PSU WB SI L1200	-	Not applicable
910629177526	4MX900 581 LED50S/840 PSU A30 SI	-	Not applicable

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	IK02
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	IK02
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	IK02
910629132426	4MX900 LED40S/840 PSD WB WH L1200	IK02
910629132526	4MX900 LED40S/840 PSD MB WH L1200	IK02
910629132626	4MX900 LED40S/840 PSD NB WH L1200	IK02
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	IK02
910629132826	4MX900 LED40S/830 PSD WB WH L1200	IK02
910629137226	4MX900 LED60S/840 PSD WB WH L1800	IK02
910629137326	4MX900 LED60S/840 PSD MB WH L1800	IK02
910629137426	4MX900 LED60S/840 PSD NB WH L1800	IK02
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	IK02
910629137626	4MX900 LED60S/830 PSD WB WH L1800	IK02
910629137726	4MX900 LED60S/830 PSD MB WH L1800	IK02
910629138826	4MX900 LED90S/840 PSD WB WH L1800	IK02
910629138926	4MX900 LED90S/840 PSD MB WH L1800	IK02
910629139026	4MX900 LED90S/840 PSD NB WH L1800	IK02
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	IK02
910629139226	4MX900 LED90S/830 PSD WB WH L1800	IK02
910629140426	4MX900 581 LED40S/840 PSU WB WH	IK02
910629140526	4MX900 581 LED40S/840 PSU MB WH	IK02
910629140926	4MX900 581 LED40S/830 PSU MB WH	IK02
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	IK02
910629142026	4MX900 491 LED40S/840 PSU WB WH	IK02
910629142126	4MX900 491 LED40S/840 PSU MB WH	IK02
910629142426	4MX900 491 LED40S/830 PSU WB WH	IK02
910629143226	4MX900 LED40S/840 PSU WB WH L1200	IK02
910629144426	4MX900 491 LED40S/840 PSD WB WH	IK02
910629144526	4MX900 491 LED40S/840 PSD MB WH	IK02
910629144626	4MX900 491 LED40S/840 PSD NB WH	IK02
910629144826	4MX900 491 LED50S/840 PSD WB WH	IK02
910629144926	4MX900 491 LED50S/840 PSD MB WH	IK02
910629145026	4MX900 491 LED50S/840 PSD NB WH	IK02

Order Code	Full Product Name	Mech. impact protection code
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	IK02
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	IK02
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	IK02
910629145626	4MX900 581 LED40S/840 PSU A30 WH	IK02
910629145726	4MX900 581 LED50S/840 PSU A30 WH	IK02
910629145826	4MX900 491 LED40S/840 PSU A30 WH	IK02
910629145926	4MX900 491 LED50S/840 PSU A30 WH	IK02
910629146026	4MX900 581 LED50S/840 PSU WB WH	IK02
910629146126	4MX900 581 LED50S/840 PSU MB WH	IK02
910629146426	4MX900 491 LED50S/840 PSU WB WH	IK02
910629146526	4MX900 491 LED50S/840 PSU MB WH	IK02
910629146626	4MX900 491 LED50S/840 PSU NB WH	IK02
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	IK02
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	IK02
910629148126	4MX900 491 LED40S/830 PSU A30 WH	IK02
910629148226	4MX900 491 LED50S/830 PSU A30 WH	IK02
910629148326	4MX900 581 LED75S/840 PSU A30 WH	IK02
910629148526	4MX900 491 LED75S/840 PSU A30 WH	IK02
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	IK02
910629170326	4MX900 491 LED75S/840 PSU WB WH	IK02
910629170426	4MX900 491 LED75S/840 PSU MB WH	IK02
910629170826	4MX900 581 LED75S/840 PSU WB WH	IK02
910629170926	4MX900 581 LED75S/840 PSU MB WH	IK02
910629171026	4MX900 581 LED75S/840 PSU NB WH	IK02
910629171326	4MX900 491 LED75S/840 PSD WB WH	IK02
910629171426	4MX900 491 LED75S/840 PSD MB WH	IK02
910629171526	4MX900 491 LED75S/840 PSD NB WH	IK02
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	-
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	IK02
910629171826	4MX900 491 LED75S/840 PSD A30 WH	IK02
910629171926	4MX900 581 LED75S/840 PSD WB WH	IK02
910629172026	4MX900 581 LED75S/840 PSD MB WH	IK02
910629172126	4MX900 581 LED75S/840 PSD NB WH	IK02

Maxos LED Performer

Order Code	Full Product Name	Mech. impact protection code
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	IK02
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	IK02
910629172426	4MX900 581 LED75S/840 PSD A30 WH	IK02
910629173226	4MX900 581 LED50S/840 PSD A30 WH	IK02
910629177426	4MX900 491 LED75S/830 PSD WB WH	IK02
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	IK02
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	IK02
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	IK02
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	IK02
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	IK02
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	IK02
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	IK02
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	IK02
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	IK02
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	IK02
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	IK02
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	IK02
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	IK02
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	IK02
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	IK02
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	IK02
910500460309	4MX900 581 LED40S/840 PSD MB WH	IK02
910500460310	4MX900 581 LED40S/840 PSD NB WH	IK02
910500460311	4MX900 581 LED40S/840 PSD WB WH	IK02
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	IK02
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	IK02
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	IK02
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	IK02
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	IK02
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	IK02
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	IK02
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	IK02
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	IK02
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	IK02
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	IK02
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	IK02
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	IK02
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	IK02
910500460327	4MX916 491 LED50S/840 PSU MB WH	IK02
910500460328	4MX916 491 LED50S/840 PSU NB WH	IK02
910500460329	4MX916 491 LED50S/840 PSU WB WH	IK02
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	IK02
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	IK02
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	IK02
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	IK02
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	IK02
910500460343	4MX916 581 LED50S/840 PSU MB WH	IK02
910500460344	4MX916 581 LED50S/840 PSU NB WH	IK02

Order Code	Full Product Name	Mech. impact protection code
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	IK02
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	IK02
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	IK02
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	IK02
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	IK02
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	IK02
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	IK02
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	IK02
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	IK02
910500460359	4MX933 491 LED50S/840 PSU MB WH	IK02
910500460360	4MX933 491 LED50S/840 PSU NB WH	IK02
910500460361	4MX933 491 LED50S/840 PSU WB WH	IK02
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	IK02
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	IK02
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	IK02
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	IK02
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	IK02
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	IK02
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	IK02
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	IK02
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	IK02
910500460375	4MX933 581 LED50S/840 PSU MB WH	IK02
910500460377	4MX933 581 LED50S/840 PSU WB WH	IK02
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	IK02
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	IK02
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	IK02
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	IK02
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	IK02
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	IK02
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	IK02
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	IK02
910629173126	4MX900 581 LED50S/840 PSD MB WH	IK02
910629177026	4MX900 581 LED50S/840 PSD WB WH	IK02
910629131626	4MX900 LED40S/840 PSD WB SI L1200	IK02
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	IK02
910629136426	4MX900 LED60S/840 PSD WB SI L1800	IK02
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	IK02
910629136826	4MX900 LED60S/830 PSD WB SI L1800	IK02
910629136926	4MX900 LED60S/830 PSD MB SI L1800	IK02
910629138026	4MX900 LED90S/840 PSD WB SI L1800	IK02
910629138126	4MX900 LED90S/840 PSD MB SI L1800	IK02
910629138426	4MX900 LED90S/830 PSD WB SI L1800	IK02
910629141226	4MX900 491 LED40S/840 PSU WB SI	IK02
910629141326	4MX900 491 LED40S/840 PSU MB SI	-
910629141626	4MX900 491 LED40S/830 PSU WB SI	IK02
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	IK02
910629172926	4MX900 LED40S/840 PSU WB SI L1200	IK02
910629177526	4MX900 581 LED50S/840 PSU A30 SI	IK02

Controls and Dimming

Maxos LED Performer

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	Yes	910629170326	4MX900 491 LED75S/840 PSU WB WH	No
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	Yes	910629170426	4MX900 491 LED75S/840 PSU MB WH	No
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	Yes	910629170826	4MX900 581 LED75S/840 PSU WB WH	No
910629132426	4MX900 LED40S/840 PSD WB WH L1200	Yes	910629170926	4MX900 581 LED75S/840 PSU MB WH	No
910629132526	4MX900 LED40S/840 PSD MB WH L1200	Yes	910629171026	4MX900 581 LED75S/840 PSU NB WH	No
910629132626	4MX900 LED40S/840 PSD NB WH L1200	Yes	910629171326	4MX900 491 LED75S/840 PSD WB WH	Yes
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	Yes	910629171426	4MX900 491 LED75S/840 PSD MB WH	Yes
910629132826	4MX900 LED40S/830 PSD WB WH L1200	Yes	910629171526	4MX900 491 LED75S/840 PSD NB WH	Yes
910629137226	4MX900 LED60S/840 PSD WB WH L1800	Yes	910629171626	4MX900 491 LED75S/840 PSD DA30 WH	Yes
910629137326	4MX900 LED60S/840 PSD MB WH L1800	Yes	910629171726	4MX900 491 LED75S/840 PSD DA20 WH	Yes
910629137426	4MX900 LED60S/840 PSD NB WH L1800	Yes	910629171826	4MX900 491 LED75S/840 PSD A30 WH	Yes
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	Yes	910629171926	4MX900 581 LED75S/840 PSD WB WH	Yes
910629137626	4MX900 LED60S/830 PSD WB WH L1800	Yes	910629172026	4MX900 581 LED75S/840 PSD MB WH	Yes
910629137726	4MX900 LED60S/830 PSD MB WH L1800	Yes	910629172126	4MX900 581 LED75S/840 PSD NB WH	Yes
910629138826	4MX900 LED90S/840 PSD WB WH L1800	Yes	910629172226	4MX900 581 LED75S/840 PSD DA30 WH	Yes
910629138926	4MX900 LED90S/840 PSD MB WH L1800	Yes	910629172326	4MX900 581 LED75S/840 PSD DA20 WH	Yes
910629139026	4MX900 LED90S/840 PSD NB WH L1800	Yes	910629172426	4MX900 581 LED75S/840 PSD A30 WH	Yes
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	Yes	910629173226	4MX900 581 LED50S/840 PSD A30 WH	Yes
910629139226	4MX900 LED90S/830 PSD WB WH L1800	Yes	910629177426	4MX900 491 LED75S/830 PSD WB WH	Yes
910629140426	4MX900 581 LED40S/840 PSU WB WH	No	910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	Yes
910629140526	4MX900 581 LED40S/840 PSU MB WH	No	910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	Yes
910629140926	4MX900 581 LED40S/830 PSU MB WH	No	910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	Yes
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	No	910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	Yes
910629142026	4MX900 491 LED40S/840 PSU WB WH	No	910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	Yes
910629142126	4MX900 491 LED40S/840 PSU MB WH	No	910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	Yes
910629142426	4MX900 491 LED40S/830 PSU WB WH	No	910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	Yes
910629143226	4MX900 LED40S/840 PSU WB WH L1200	No	910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	Yes
910629144426	4MX900 491 LED40S/840 PSD WB WH	Yes	910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	Yes
910629144526	4MX900 491 LED40S/840 PSD MB WH	Yes	910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	Yes
910629144626	4MX900 491 LED40S/840 PSD NB WH	Yes	910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	Yes
910629144826	4MX900 491 LED50S/840 PSD WB WH	Yes	910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	Yes
910629144926	4MX900 491 LED50S/840 PSD MB WH	Yes	910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	Yes
910629145026	4MX900 491 LED50S/840 PSD NB WH	Yes	910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	Yes
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	Yes	910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	Yes
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	Yes	910500460308	4MX900 581 LED40S/840 PSD DA20 WH	Yes
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	Yes	910500460309	4MX900 581 LED40S/840 PSD MB WH	Yes
910629145626	4MX900 581 LED40S/840 PSU A30 WH	No	910500460310	4MX900 581 LED40S/840 PSD NB WH	Yes
910629145726	4MX900 581 LED50S/840 PSU A30 WH	No	910500460311	4MX900 581 LED40S/840 PSD WB WH	Yes
910629145826	4MX900 491 LED40S/840 PSU A30 WH	No	910500460312	4MX900 581 LED50S/840 PSD DA20 WH	Yes
910629145926	4MX900 491 LED50S/840 PSU A30 WH	No	910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	Yes
910629146026	4MX900 581 LED50S/840 PSU WB WH	No	910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	Yes
910629146126	4MX900 581 LED50S/840 PSU MB WH	No	910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	Yes
910629146426	4MX900 491 LED50S/840 PSU WB WH	No	910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	Yes
910629146526	4MX900 491 LED50S/840 PSU MB WH	No	910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	Yes
910629146626	4MX900 491 LED50S/840 PSU NB WH	No	910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	Yes
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	Yes	910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	Yes
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	Yes	910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	Yes
910629148126	4MX900 491 LED40S/830 PSU A30 WH	No	910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	Yes
910629148226	4MX900 491 LED50S/830 PSU A30 WH	No	910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	Yes
910629148326	4MX900 581 LED75S/840 PSU A30 WH	No	910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	Yes
910629148526	4MX900 491 LED75S/840 PSU A30 WH	No	910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	Yes
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	No	910500460326	4MX916 491 LED50S/840 PSU DA20 WH	No

Maxos LED Performer

Order Code	Full Product Name	Dimmable
910500460327	4MX916 491 LED50S/840 PSU MB WH	No
910500460328	4MX916 491 LED50S/840 PSU NB WH	No
910500460329	4MX916 491 LED50S/840 PSU WB WH	No
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	Yes
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	Yes
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	Yes
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	Yes
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	No
910500460343	4MX916 581 LED50S/840 PSU MB WH	No
910500460344	4MX916 581 LED50S/840 PSU NB WH	No
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	Yes
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	Yes
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	Yes
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	Yes
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	Yes
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	Yes
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	Yes
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	Yes
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	No
910500460359	4MX933 491 LED50S/840 PSU MB WH	No
910500460360	4MX933 491 LED50S/840 PSU NB WH	No
910500460361	4MX933 491 LED50S/840 PSU WB WH	No
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	Yes
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	Yes
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	Yes
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	Yes
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	Yes
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	Yes
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	Yes

Order Code	Full Product Name	Dimmable
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	Yes
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	No
910500460375	4MX933 581 LED50S/840 PSU MB WH	No
910500460377	4MX933 581 LED50S/840 PSU WB WH	No
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	Yes
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	Yes
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	Yes
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	Yes
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	Yes
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	Yes
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	Yes
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	Yes
910629173126	4MX900 581 LED50S/840 PSD MB WH	Yes
910629177026	4MX900 581 LED50S/840 PSD WB WH	Yes
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Yes
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	Yes
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Yes
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	Yes
910629136826	4MX900 LED60S/830 PSD WB SI L1800	Yes
910629136926	4MX900 LED60S/830 PSD MB SI L1800	Yes
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Yes
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Yes
910629138426	4MX900 LED90S/830 PSD WB SI L1800	Yes
910629141226	4MX900 491 LED40S/840 PSU WB SI	No
910629141326	4MX900 491 LED40S/840 PSU MB SI	No
910629141626	4MX900 491 LED40S/830 PSU WB SI	No
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Yes
910629172926	4MX900 LED40S/840 PSU WB SI L1200	No
910629177526	4MX900 581 LED50S/840 PSU A30 SI	No

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	220 to 240 V
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	220 to 240 V
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	220 to 240 V
910629132426	4MX900 LED40S/840 PSD WB WH L1200	220 to 240 V
910629132526	4MX900 LED40S/840 PSD MB WH L1200	220 to 240 V
910629132626	4MX900 LED40S/840 PSD NB WH L1200	220 to 240 V
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	220 to 240 V
910629132826	4MX900 LED40S/830 PSD WB WH L1200	220 to 240 V
910629137226	4MX900 LED60S/840 PSD WB WH L1800	220 to 240 V
910629137326	4MX900 LED60S/840 PSD MB WH L1800	220 to 240 V
910629137426	4MX900 LED60S/840 PSD NB WH L1800	220 to 240 V
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	220 to 240 V
910629137626	4MX900 LED60S/830 PSD WB WH L1800	220 to 240 V
910629137726	4MX900 LED60S/830 PSD MB WH L1800	220 to 240 V
910629138826	4MX900 LED90S/840 PSD WB WH L1800	220 to 240 V
910629138926	4MX900 LED90S/840 PSD MB WH L1800	220 to 240 V
910629139026	4MX900 LED90S/840 PSD NB WH L1800	220 to 240 V
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	220 to 240 V
910629139226	4MX900 LED90S/830 PSD WB WH L1800	220 to 240 V

Order Code	Full Product Name	Input Voltage
910629140426	4MX900 581 LED40S/840 PSU WB WH	220 to 240 V
910629140526	4MX900 581 LED40S/840 PSU MB WH	220 to 240 V
910629140926	4MX900 581 LED40S/830 PSU MB WH	220 to 240 V
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	220 to 240 V
910629142026	4MX900 491 LED40S/840 PSU WB WH	220 to 240 V
910629142126	4MX900 491 LED40S/840 PSU MB WH	220 to 240 V
910629142426	4MX900 491 LED40S/830 PSU WB WH	220 to 240 V
910629143226	4MX900 LED40S/840 PSU WB WH L1200	220 to 240 V
910629144426	4MX900 491 LED40S/840 PSD WB WH	220 to 240 V
910629144526	4MX900 491 LED40S/840 PSD MB WH	220 to 240 V
910629144626	4MX900 491 LED40S/840 PSD NB WH	220 to 240 V
910629144826	4MX900 491 LED50S/840 PSD WB WH	220 to 240 V
910629144926	4MX900 491 LED50S/840 PSD MB WH	220 to 240 V
910629145026	4MX900 491 LED50S/840 PSD NB WH	220 to 240 V
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	220 to 240 V
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	220 to 240 V
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	220 to 240 V
910629145626	4MX900 581 LED40S/840 PSU A30 WH	220 to 240 V
910629145726	4MX900 581 LED50S/840 PSU A30 WH	220 to 240 V

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
910629145826	4MX900 491 LED40S/840 PSU A30 WH	220 to 240 V	910500460312	4MX900 581 LED50S/840 PSD DA20 WH	220 to 240 V
910629145926	4MX900 491 LED50S/840 PSU A30 WH	220 to 240 V	910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	220 to 240 V
910629146026	4MX900 581 LED50S/840 PSU WB WH	220 to 240 V	910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	220 to 240 V
910629146126	4MX900 581 LED50S/840 PSU MB WH	220 to 240 V	910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	220 to 240 V
910629146426	4MX900 491 LED50S/840 PSU WB WH	220 to 240 V	910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	220 to 240 V
910629146526	4MX900 491 LED50S/840 PSU MB WH	220 to 240 V	910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	220 to 240 V
910629146626	4MX900 491 LED50S/840 PSU NB WH	220 to 240 V	910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	220 to 240 V
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	220 to 240 V	910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	220 to 240 V
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	220 to 240 V	910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	220 to 240 V
910629148126	4MX900 491 LED40S/830 PSU A30 WH	220 to 240 V	910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	220 to 240 V
910629148226	4MX900 491 LED50S/830 PSU A30 WH	220 to 240 V	910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	220 to 240 V
910629148326	4MX900 581 LED75S/840 PSU A30 WH	220 to 240 V	910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	220 to 240 V
910629148526	4MX900 491 LED75S/840 PSU A30 WH	220 to 240 V	910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	220 to 240 V
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	220 to 240 V	910500460326	4MX916 491 LED50S/840 PSU DA20 WH	220 to 240 V
910629170326	4MX900 491 LED75S/840 PSU WB WH	220 to 240 V	910500460327	4MX916 491 LED50S/840 PSU MB WH	220 to 240 V
910629170426	4MX900 491 LED75S/840 PSU MB WH	220 to 240 V	910500460328	4MX916 491 LED50S/840 PSU NB WH	220 to 240 V
910629170826	4MX900 581 LED75S/840 PSU WB WH	220 to 240 V	910500460329	4MX916 491 LED50S/840 PSU WB WH	220 to 240 V
910629170926	4MX900 581 LED75S/840 PSU MB WH	220 to 240 V	910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	220 to 240 V
910629171026	4MX900 581 LED75S/840 PSU NB WH	220 to 240 V	910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	220 to 240 V
910629171326	4MX900 491 LED75S/840 PSD WB WH	220 to 240 V	910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	220 to 240 V
910629171426	4MX900 491 LED75S/840 PSD MB WH	220 to 240 V	910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	220 to 240 V
910629171526	4MX900 491 LED75S/840 PSD NB WH	220 to 240 V	910500460342	4MX916 581 LED50S/840 PSU DA20 WH	220 to 240 V
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	220 to 240 V	910500460343	4MX916 581 LED50S/840 PSU MB WH	220 to 240 V
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	220 to 240 V	910500460344	4MX916 581 LED50S/840 PSU NB WH	220 to 240 V
910629171826	4MX900 491 LED75S/840 PSD A30 WH	220 to 240 V	910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	220 to 240 V
910629171926	4MX900 581 LED75S/840 PSD WB WH	220 to 240 V	910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	220 to 240 V
910629172026	4MX900 581 LED75S/840 PSD MB WH	220 to 240 V	910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	220 to 240 V
910629172126	4MX900 581 LED75S/840 PSD NB WH	220 to 240 V	910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	220 to 240 V
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	220 to 240 V	910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	220 to 240 V
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	220 to 240 V	910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	220 to 240 V
910629172426	4MX900 581 LED75S/840 PSD A30 WH	220 to 240 V	910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	220 to 240 V
910629173226	4MX900 581 LED50S/840 PSD A30 WH	220 to 240 V	910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	220 to 240 V
910629177426	4MX900 491 LED75S/830 PSD WB WH	220 to 240 V	910500460358	4MX933 491 LED50S/840 PSU DA20 WH	220 to 240 V
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	220 to 240 V	910500460359	4MX933 491 LED50S/840 PSU MB WH	220 to 240 V
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	220 to 240 V	910500460360	4MX933 491 LED50S/840 PSU NB WH	220 to 240 V
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	220 to 240 V	910500460361	4MX933 491 LED50S/840 PSU WB WH	220 to 240 V
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	220 to 240 V	910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	220 to 240 V
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	220 to 240 V	910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	220 to 240 V
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	220 to 240 V	910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	220 to 240 V
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	220 to 240 V	910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	220 to 240 V
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	220 to 240 V	910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	220 to 240 V
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	220 to 240 V	910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	220 to 240 V
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	220 to 240 V	910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	220 to 240 V
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	220 to 240 V	910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	220 to 240 V
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	220 to 240 V	910500460374	4MX933 581 LED50S/840 PSU DA20 WH	220 to 240 V
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	220 to 240 V	910500460375	4MX933 581 LED50S/840 PSU MB WH	220 to 240 V
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	220 to 240 V	910500460377	4MX933 581 LED50S/840 PSU WB WH	220 to 240 V
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	220 to 240 V	910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	220 to 240 V
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	220 to 240 V	910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	220 to 240 V
910500460309	4MX900 581 LED40S/840 PSD MB WH	220 to 240 V	910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	220 to 240 V
910500460310	4MX900 581 LED40S/840 PSD NB WH	220 to 240 V	910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	220 to 240 V
910500460311	4MX900 581 LED40S/840 PSD WB WH	220 to 240 V	910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	220 to 240 V

Maxos LED Performer

Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	220 to 240 V	910629136926	4MX900 LED60S/830 PSD MB SI L1800	220 to 240 V
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	220 to 240 V	910629138026	4MX900 LED90S/840 PSD WB SI L1800	220 to 240 V
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	220 to 240 V	910629138126	4MX900 LED90S/840 PSD MB SI L1800	220 to 240 V
910629173126	4MX900 581 LED50S/840 PSD MB WH	220 to 240 V	910629138426	4MX900 LED90S/830 PSD WB SI L1800	220 to 240 V
910629177026	4MX900 581 LED50S/840 PSD WB WH	220-240 V	910629141226	4MX900 491 LED40S/840 PSU WB SI	220 to 240 V
910629131626	4MX900 LED40S/840 PSD WB SI L1200	220 to 240 V	910629141326	4MX900 491 LED40S/840 PSU MB SI	220 to 240 V
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	220 to 240 V	910629141626	4MX900 491 LED40S/830 PSU WB SI	220 to 240 V
910629136426	4MX900 LED60S/840 PSD WB SI L1800	220 to 240 V	910629147226	4MX900 LED90S/840 PSD A30 SI L1800	220 to 240 V
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	220 to 240 V	910629172926	4MX900 LED40S/840 PSU WB SI L1200	220 to 240 V
910629136826	4MX900 LED60S/830 PSD WB SI L1800	220 to 240 V	910629177526	4MX900 581 LED50S/840 PSU A30 SI	220 to 240 V

General Information (1/2)

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	Emergency lighting			Lamp family code	Embedded control	Number of gear units
				ENEC mark	Glow-wire test				
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	120 °	Emergency lighting 1 hour duration 300 lm	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit	
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	Constant light output	1 unit	
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	Constant light output	1 unit	
910629132426	4MX900 LED40S/840 PSD WB WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit	
910629132526	4MX900 LED40S/840 PSD MB WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit	
910629132626	4MX900 LED40S/840 PSD NB WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit	
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit	
910629132826	4MX900 LED40S/830 PSD WB WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit	
910629137226	4MX900 LED60S/840 PSD WB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629137326	4MX900 LED60S/840 PSD MB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629137426	4MX900 LED60S/840 PSD NB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629137626	4MX900 LED60S/830 PSD WB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629137726	4MX900 LED60S/830 PSD MB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit	
910629138826	4MX900 LED90S/840 PSD WB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit	
910629138926	4MX900 LED90S/840 PSD MB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit	
910629139026	4MX900 LED90S/840 PSD NB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit	

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629139226	4MX900 LED90S/830 PSD WB WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629140426	4MX900 581 LED40S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629140526	4MX900 581 LED40S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629140926	4MX900 581 LED40S/830 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629142026	4MX900 491 LED40S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629142126	4MX900 491 LED40S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629142426	4MX900 491 LED40S/830 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629143226	4MX900 LED40S/840 PSU WB WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629144426	4MX900 491 LED40S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629144526	4MX900 491 LED40S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629144626	4MX900 491 LED40S/840 PSD NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629144826	4MX900 491 LED50S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629144926	4MX900 491 LED50S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629145026	4MX900 491 LED50S/840 PSD NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit
910629145626	4MX900 581 LED40S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629145726	4MX900 581 LED50S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629145826	4MX900 491 LED40S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629145926	4MX900 491 LED50S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629146026	4MX900 581 LED50S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629146126	4MX900 581 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910629146426	4MX900 491 LED50S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629146526	4MX900 491 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629146626	4MX900 491 LED50S/840 PSU NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629148126	4MX900 491 LED40S/830 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629148226	4MX900 491 LED50S/830 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629148326	4MX900 581 LED75S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629148526	4MX900 491 LED75S/840 PSU A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629170326	4MX900 491 LED75S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629170426	4MX900 491 LED75S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629170826	4MX900 581 LED75S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629170926	4MX900 581 LED75S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171026	4MX900 581 LED75S/840 PSU NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171326	4MX900 491 LED75S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171426	4MX900 491 LED75S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171526	4MX900 491 LED75S/840 PSD NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	-	-	-	-	LED75S	-	-
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171826	4MX900 491 LED75S/840 PSD A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629171926	4MX900 581 LED75S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629172026	4MX900 581 LED75S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629172126	4MX900 581 LED75S/840 PSD NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629172426	4MX900 581 LED75S/840 PSD A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910629173226	4MX900 581 LED50S/840 PSD A30 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629177426	4MX900 491 LED75S/830 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED75S	-	1 unit
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	Constant light output	1 unit
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460309	4MX900 581 LED40S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460310	4MX900 581 LED40S/840 PSD NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460311	4MX900 581 LED40S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460327	4MX916 491 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460328	4MX916 491 LED50S/840 PSU NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460329	4MX916 491 LED50S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460343	4MX916 581 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460344	4MX916 581 LED50S/840 PSU NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460359	4MX933 491 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460360	4MX933 491 LED50S/840 PSU NB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460361	4MX933 491 LED50S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460375	4MX933 581 LED50S/840 PSU MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460377	4MX933 581 LED50S/840 PSU WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit

Maxos LED Performer

Order Code	Full Product Name	Beam angle of light source	Emergency lighting	ENEC mark	Glow-wire test	Lamp family code	Embedded control	Number of gear units
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	-	-	1 unit
910629173126	4MX900 581 LED50S/840 PSD MB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629177026	4MX900 581 LED50S/840 PSD WB WH	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit
910629131626	4MX900 LED40S/840 PSD WB SI L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629136426	4MX900 LED60S/840 PSD WB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit
910629136826	4MX900 LED60S/830 PSD WB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit
910629136926	4MX900 LED60S/830 PSD MB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED60S	-	1 unit
910629138026	4MX900 LED90S/840 PSD WB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629138126	4MX900 LED90S/840 PSD MB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629138426	4MX900 LED90S/830 PSD WB SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629141226	4MX900 491 LED40S/840 PSU WB SI	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629141326	4MX900 491 LED40S/840 PSU MB SI	120 °	-	-	Temperature 650 °C, duration 30 s	LED40S	-	-
910629141626	4MX900 491 LED40S/830 PSU WB SI	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED90S	-	1 unit
910629172926	4MX900 LED40S/840 PSU WB SI L1200	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED40S	-	1 unit
910629177526	4MX900 581 LED50S/840 PSU A30 SI	120 °	-	ENEC mark	Temperature 650 °C, duration 30 s	LED50S	-	1 unit

General Information (2/2)

Order Code	Full Product Name	Number of light sources	Optic type	Product Family Code	Order Code	Full Product Name	Number of light sources	Optic type	Product Family Code
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	1 pc	Wide beam	4MX916	910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	1 pc	Wide beam	4MX900

Maxos LED Performer

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	1 pc	Medium beam	4MX900
910629132426	4MX900 LED40S/840 PSD WB WH L1200	1 pc	Wide beam	4MX900
910629132526	4MX900 LED40S/840 PSD MB WH L1200	1 pc	Medium beam	4MX900
910629132626	4MX900 LED40S/840 PSD NB WH L1200	1 pc	Narrow beam	4MX900
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	1 pc	Double asymmetric optic 20°	4MX900
910629132826	4MX900 LED40S/830 PSD WB WH L1200	1 pc	Wide beam	4MX900
910629137226	4MX900 LED60S/840 PSD WB WH L1800	1 pc	Wide beam	4MX900
910629137326	4MX900 LED60S/840 PSD MB WH L1800	1 pc	Medium beam	4MX900
910629137426	4MX900 LED60S/840 PSD NB WH L1800	1 pc	Narrow beam	4MX900
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	1 pc	Double asymmetric optic 20°	4MX900
910629137626	4MX900 LED60S/830 PSD WB WH L1800	1 pc	Wide beam	4MX900
910629137726	4MX900 LED60S/830 PSD MB WH L1800	1 pc	Medium beam	4MX900
910629138826	4MX900 LED90S/840 PSD WB WH L1800	1 pc	Wide beam	4MX900
910629138926	4MX900 LED90S/840 PSD MB WH L1800	1 pc	Medium beam	4MX900
910629139026	4MX900 LED90S/840 PSD NB WH L1800	1 pc	Narrow beam	4MX900
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	1 pc	Double asymmetric optic 20°	4MX900
910629139226	4MX900 LED90S/830 PSD WB WH L1800	1 pc	Wide beam	4MX900
910629140426	4MX900 581 LED40S/840 PSU WB WH	1 pc	Wide beam	4MX900
910629140526	4MX900 581 LED40S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629140926	4MX900 581 LED40S/830 PSU MB WH	1 pc	Medium beam	4MX900
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	1 pc	Double asymmetric optic 20°	4MX900
910629142026	4MX900 491 LED40S/840 PSU WB WH	1 pc	Wide beam	4MX900

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910629142126	4MX900 491 LED40S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629142426	4MX900 491 LED40S/830 PSU WB WH	1 pc	Wide beam	4MX900
910629143226	4MX900 LED40S/840 PSU WB WH L1200	1 pc	Wide beam	4MX900
910629144426	4MX900 491 LED40S/840 PSD WB WH	1 pc	Wide beam	4MX900
910629144526	4MX900 491 LED40S/840 PSD MB WH	1 pc	Medium beam	4MX900
910629144626	4MX900 491 LED40S/840 PSD NB WH	1 pc	Narrow beam	4MX900
910629144826	4MX900 491 LED50S/840 PSD WB WH	1 pc	Wide beam	4MX900
910629144926	4MX900 491 LED50S/840 PSD MB WH	1 pc	Medium beam	4MX900
910629145026	4MX900 491 LED50S/840 PSD NB WH	1 pc	Narrow beam	4MX900
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	1 pc	Double asymmetric optic 20°	4MX900
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629145626	4MX900 581 LED40S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629145726	4MX900 581 LED50S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629145826	4MX900 491 LED40S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629145926	4MX900 491 LED50S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629146026	4MX900 581 LED50S/840 PSU WB WH	1 pc	Wide beam	4MX900

Maxos LED Performer

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910629146126	4MX900 581 LED50S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629146426	4MX900 491 LED50S/840 PSU WB WH	1 pc	Wide beam	4MX900
910629146526	4MX900 491 LED50S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629146626	4MX900 491 LED50S/840 PSU NB WH	1 pc	Narrow beam	4MX900
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629148126	4MX900 491 LED40S/830 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629148226	4MX900 491 LED50S/830 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629148326	4MX900 581 LED75S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629148526	4MX900 491 LED75S/840 PSU A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	1 pc	Double asymmetric optic 30°	4MX900
910629170326	4MX900 491 LED75S/840 PSU WB WH	1 pc	Wide beam	4MX900
910629170426	4MX900 491 LED75S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629170826	4MX900 581 LED75S/840 PSU WB WH	1 pc	Wide beam	4MX900
910629170926	4MX900 581 LED75S/840 PSU MB WH	1 pc	Medium beam	4MX900
910629171026	4MX900 581 LED75S/840 PSU NB WH	1 pc	Narrow beam	4MX900

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910629171326	4MX900 491 LED75S/840 PSD WB WH	1 pc	Wide beam	4MX900
910629171426	4MX900 491 LED75S/840 PSD MB WH	1 pc	Medium beam	4MX900
910629171526	4MX900 491 LED75S/840 PSD NB WH	1 pc	Narrow beam	4MX900
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	1 pc	Double asymmetric optic 30°	4MX900
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	1 pc	Double asymmetric optic 20°	4MX900
910629171826	4MX900 491 LED75S/840 PSD A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629171926	4MX900 581 LED75S/840 PSD WB WH	1 pc	Wide beam	4MX900
910629172026	4MX900 581 LED75S/840 PSD MB WH	1 pc	Medium beam	4MX900
910629172126	4MX900 581 LED75S/840 PSD NB WH	1 pc	Narrow beam	4MX900
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	1 pc	Double asymmetric optic 30°	4MX900
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	1 pc	Double asymmetric optic 20°	4MX900
910629172426	4MX900 581 LED75S/840 PSD A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629173226	4MX900 581 LED50S/840 PSD A30 WH	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629177426	4MX900 491 LED75S/830 PSD WB WH	1 pc	Wide beam	4MX900
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	-	Wide beam	4MX900
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	-	Double asymmetric optic 20°	4MX900

Maxos LED Performer

Order Code	Full Product Name	Number of light		Product Family
		sources	Optic type	Code
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	-	Medium beam	4MX900
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	-	Narrow beam	4MX900
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX900
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX900
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX900
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX900
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	-	Double asymmetric optic 20°	4MX900
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	-	Narrow beam	4MX900
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	-	Wide beam	4MX900
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX900
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	-	Medium beam	4MX900
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	-	Narrow beam	4MX900
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	-	Wide beam	4MX900
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	-	Double asymmetric optic 20°	4MX900
910500460309	4MX900 581 LED40S/840 PSD MB WH	-	Medium beam	4MX900
910500460310	4MX900 581 LED40S/840 PSD NB WH	-	Narrow beam	4MX900

Order Code	Full Product Name	Number of light		Product Family
		sources	Optic type	Code
910500460311	4MX900 581 LED40S/840 PSD WB WH	-	Wide beam	4MX900
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	-	Double asymmetric optic 20°	4MX900
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	-	Double asymmetric optic 20°	4MX900
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	-	Medium beam	4MX900
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX900
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX900
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX900
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX900
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	-	Double asymmetric optic 20°	4MX900
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	-	Narrow beam	4MX900
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX900
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	-	Medium beam	4MX900
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	-	Narrow beam	4MX900
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	-	Wide beam	4MX900
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	-	Double asymmetric optic 20°	4MX916
910500460327	4MX916 491 LED50S/840 PSU MB WH	-	Medium beam	4MX916

Maxos LED Performer

Order Code	Full Product Name	Number of light		Product Family
		sources	Optic type	Code
910500460328	4MX916 491 LED50S/840 PSU NB WH	-	Narrow beam	4MX916
910500460329	4MX916 491 LED50S/840 PSU WB WH	-	Wide beam	4MX916
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX916
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX916
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX916
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX916
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	-	Double asymmetric optic 20°	4MX916
910500460343	4MX916 581 LED50S/840 PSU MB WH	-	Medium beam	4MX916
910500460344	4MX916 581 LED50S/840 PSU NB WH	-	Narrow beam	4MX916
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX916
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX916
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX916
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX916
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX916
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	-	Medium beam	4MX916
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	-	Narrow beam	4MX916

Order Code	Full Product Name	Number of light		Product Family
		sources	Optic type	Code
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	-	Wide beam	4MX916
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	-	Double asymmetric optic 20°	4MX933
910500460359	4MX933 491 LED50S/840 PSU MB WH	-	Medium beam	4MX933
910500460360	4MX933 491 LED50S/840 PSU NB WH	-	Narrow beam	4MX933
910500460361	4MX933 491 LED50S/840 PSU WB WH	-	Wide beam	4MX933
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX933
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX933
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX933
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX933
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX933
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	-	Medium beam	4MX933
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	-	Narrow beam	4MX933
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	-	Wide beam	4MX933
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	-	Double asymmetric optic 20°	4MX933
910500460375	4MX933 581 LED50S/840 PSU MB WH	-	Medium beam	4MX933
910500460377	4MX933 581 LED50S/840 PSU WB WH	-	Wide beam	4MX933

Maxos LED Performer

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX933
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	-	Medium beam	4MX933
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	-	Narrow beam	4MX933
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	-	Wide beam	4MX933
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	-	Double asymmetric optic 20°	4MX933
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	-	Medium beam	4MX933
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	-	Narrow beam	4MX933
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	-	Wide beam	4MX933
910629173126	4MX900 581 LED50S/840 PSD MB WH	-	Medium beam	4MX900
910629177026	4MX900 581 LED50S/840 PSD WB WH	-	Wide beam	4MX900
910629131626	4MX900 LED40S/840 PSD WB SI L1200	1 pc	Wide beam	4MX900

Order Code	Full Product Name	Number of light		Product Family Code
		sources	Optic type	
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	1 pc	Double asymmetric optic 20°	4MX900
910629136426	4MX900 LED60S/840 PSD WB SI L1800	1 pc	Wide beam	4MX900
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	1 pc	Double asymmetric optic 20°	4MX900
910629136826	4MX900 LED60S/830 PSD WB SI L1800	1 pc	Wide beam	4MX900
910629136926	4MX900 LED60S/830 PSD MB SI L1800	1 pc	Medium beam	4MX900
910629138026	4MX900 LED90S/840 PSD WB SI L1800	1 pc	Wide beam	4MX900
910629138126	4MX900 LED90S/840 PSD MB SI L1800	1 pc	Medium beam	4MX900
910629138426	4MX900 LED90S/830 PSD WB SI L1800	1 pc	Wide beam	4MX900
910629141226	4MX900 491 LED40S/840 PSU WB SI	1 pc	Wide beam	4MX900
910629141326	4MX900 491 LED40S/840 PSU MB SI	1 pc	Medium beam	4MX900
910629141626	4MX900 491 LED40S/830 PSU WB SI	1 pc	Wide beam	4MX900
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	1 pc	Asymmetrical mirror axis angle 30°	4MX900
910629172926	4MX900 LED40S/840 PSU WB SI L1200	1 pc	Wide beam	4MX900
910629177526	4MX900 581 LED50S/840 PSU A30 SI	1 pc	Asymmetrical mirror axis angle 30°	4MX900

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color		Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
				Rendering Index	Initial LED				
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	(0.43, 0.40) SDCM <3.5	3000 K	≥80	115 lm/W	7500 lm	+/-10%	65.5 W	
910500457793	4MX900 491 LED40S/840 PSD- CLO WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W	
910500458125	4MX900 581 LED75S/840 PSD- CLO MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W	
910629132426	4MX900 LED40S/840 PSD WB WH L1200	(0.38, 0.38) SDCM <3.5	4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W	
910629132526	4MX900 LED40S/840 PSD MB WH L1200	(0.38, 0.38) SDCM <3.5	4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W	
910629132626	4MX900 LED40S/840 PSD NB WH L1200	(0.38, 0.38) SDCM <3.5	4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W	

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W
910629132826	4MX900 LED40S/830 PSD WB WH L1200	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629137226	4MX900 LED60S/840 PSD WB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629137326	4MX900 LED60S/840 PSD MB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629137426	4MX900 LED60S/840 PSD NB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629137626	4MX900 LED60S/830 PSD WB WH L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	136 lm/W	6000 lm	+/-10%	44 W
910629137726	4MX900 LED60S/830 PSD MB WH L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	136 lm/W	6000 lm	+/-10%	44 W
910629138826	4MX900 LED90S/840 PSD WB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629138926	4MX900 LED90S/840 PSD MB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629139026	4MX900 LED90S/840 PSD NB WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629139226	4MX900 LED90S/830 PSD WB WH L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	127 lm/W	9000 lm	+/-10%	71 W
910629140426	4MX900 581 LED40S/840 PSU WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629140526	4MX900 581 LED40S/840 PSU MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629140926	4MX900 581 LED40S/830 PSU MB WH	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	125 lm/W	4000 lm	+/-10%	32 W
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	125 lm/W	4000 lm	+/-10%	32 W
910629142026	4MX900 491 LED40S/840 PSU WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629142126	4MX900 491 LED40S/840 PSU MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629142426	4MX900 491 LED40S/830 PSU WB WH	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	125 lm/W	4000 lm	+/-10%	32 W
910629143226	4MX900 LED40S/840 PSU WB WH L1200	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W
910629144426	4MX900 491 LED40S/840 PSD WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629144526	4MX900 491 LED40S/840 PSD MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629144626	4MX900 491 LED40S/840 PSD NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629144826	4MX900 491 LED50S/840 PSD WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910629144926	4MX900 491 LED50S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629145026	4MX900 491 LED50S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629145126	4MX900 491 LED50S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629145326	4MX900 LED40S/840 PSD A30 WH L1200	(0.38, 0.38) SDCM <3.5	4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W
910629145526	4MX900 LED60S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5	4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629145626	4MX900 581 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629145726	4MX900 581 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629145826	4MX900 491 LED40S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910629145926	4MX900 491 LED50S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629146026	4MX900 581 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629146126	4MX900 581 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629146426	4MX900 491 LED50S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629146526	4MX900 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629146626	4MX900 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629147026	4MX900 LED90S/840 PSD A30 WH L1800	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629147826	4MX900 LED90S/830 PSD A30 WH L1800	(0.43, 0.40) SDCM <3.5	3000 K	≥80	127 lm/W	9000 lm	+/-10%	71 W
910629148126	4MX900 491 LED40S/830 PSU A30 WH	(0.43, 0.40) SDCM <3.5	3000 K	≥80	125 lm/W	4000 lm	+/-10%	32 W
910629148226	4MX900 491 LED50S/830 PSU A30 WH	(0.43, 0.40) SDCM <3.5	3000 K	≥80	135 lm/W	5000 lm	+/-10%	37 W
910629148326	4MX900 581 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629148526	4MX900 491 LED75S/840 PSU A30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629170126	4MX900 491 LED50S/840 PSU DA30 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629170326	4MX900 491 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629170426	4MX900 491 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629170826	4MX900 581 LED75S/840 PSU WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629170926	4MX900 581 LED75S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910629171026	4MX900 581 LED75S/840 PSU NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171326	4MX900 491 LED75S/840 PSD WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171426	4MX900 491 LED75S/840 PSD MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171526	4MX900 491 LED75S/840 PSD NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171626	4MX900 491 LED75S/840 PSD DA30 WH	(0.38, 0.38)	SDCM <3 4000 K	-	116 lm/W	7200 lm	-	62 W
910629171726	4MX900 491 LED75S/840 PSD DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171826	4MX900 491 LED75S/840 PSD A30 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629171926	4MX900 581 LED75S/840 PSD WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629172026	4MX900 581 LED75S/840 PSD MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629172126	4MX900 581 LED75S/840 PSD NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629172426	4MX900 581 LED75S/840 PSD A30 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910629173226	4MX900 581 LED50S/840 PSD A30 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629177426	4MX900 491 LED75S/830 PSD WB WH	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	125 lm/W	7500 lm	+/-10%	60 W
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910500460309	4MX900 581 LED40S/840 PSD MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910500460310	4MX900 581 LED40S/840 PSD NB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910500460311	4MX900 581 LED40S/840 PSD WB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	7500 lm	+/-10%	56 W
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460327	4MX916 491 LED50S/840 PSU MB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460328	4MX916 491 LED50S/840 PSU NB WH	(0.38, 0.38) SDCM <3.5	4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticy	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910500460329	4MX916 491 LED50S/840 PSU WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460343	4MX916 581 LED50S/840 PSU MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460344	4MX916 581 LED50S/840 PSU NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460359	4MX933 491 LED50S/840 PSU MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460360	4MX933 491 LED50S/840 PSU NB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460361	4MX933 491 LED50S/840 PSU WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460375	4MX933 581 LED50S/840 PSU MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460377	4MX933 581 LED50S/840 PSU WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	125 lm/W	5000 lm	+/-10%	40 W
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	122 lm/W	7500 lm	+/-10%	61.5 W
910629173126	4MX900 581 LED50S/840 PSD MB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629177026	4MX900 581 LED50S/840 PSD WB WH	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W
910629131626	4MX900 LED40S/840 PSD WB SI L1200	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W
910629136426	4MX900 LED60S/840 PSD WB SI L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	145 lm/W	6000 lm	+/-10%	41.5 W
910629136826	4MX900 LED60S/830 PSD WB SI L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	136 lm/W	6000 lm	+/-10%	44 W
910629136926	4MX900 LED60S/830 PSD MB SI L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	136 lm/W	6000 lm	+/-10%	44 W
910629138026	4MX900 LED90S/840 PSD WB SI L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629138126	4MX900 LED90S/840 PSD MB SI L1800	(0.38, 0.38)	SDCM <3.5 4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W
910629138426	4MX900 LED90S/830 PSD WB SI L1800	(0.43, 0.40)	SDCM <3.5 3000 K	≥80	127 lm/W	9000 lm	+/-10%	71 W

Maxos LED Performer

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Init. Color		Initial LED luminaire efficacy	Initial luminous flux	Luminous flux tolerance	Initial input power
				Rendering Index	Initial LED				
910629141226	4MX900 491 LED40S/840 PSU WB SI	(0.38, 0.38) SDCM <3.5	4000 K	≥80	133 lm/W	4000 lm	+/-10%	30 W	
910629141326	4MX900 491 LED40S/840 PSU MB SI	(0.38, 0.38) SDCM <3	4000 K	-	133 lm/W	4000 lm	+/-10%	30 W	
910629141626	4MX900 491 LED40S/830 PSU WB SI	(0.43, 0.40) SDCM <3.5	3000 K	≥80	125 lm/W	4000 lm	+/-10%	32 W	
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	(0.38, 0.38) SDCM <3.5	4000 K	≥80	134 lm/W	9000 lm	+/-10%	67 W	
910629172926	4MX900 LED40S/840 PSU WB SI L1200	(0.38, 0.38) SDCM <3.5	4000 K	≥80	143 lm/W	4000 lm	+/-10%	28 W	
910629177526	4MX900 581 LED50S/840 PSU A30 SI	(0.38, 0.38) SDCM <3.5	4000 K	≥80	141 lm/W	5000 lm	+/-10%	35.5 W	

Mechanical and Housing

Order Code	Full Product Name	Trunking		Order Code	Full Product Name	Trunking	
		Color	length			Color	length
910500457256	4MX916 581 LED75S/830 PSD WB WH C-2R	White	581	910629145126	4MX900 491 LED50S/840 PSD DA20 WH	White	491
910500457793	4MX900 491 LED40S/840 PSD-CLO WB WH	White	491	910629145326	4MX900 LED40S/840 PSD A30 WH L1200	White	-
910500458125	4MX900 581 LED75S/840 PSD-CLO MB WH	White	581	910629145526	4MX900 LED60S/840 PSD A30 WH L1800	White	-
910629132426	4MX900 LED40S/840 PSD WB WH L1200	White	-	910629145626	4MX900 581 LED40S/840 PSU A30 WH	White	581
910629132526	4MX900 LED40S/840 PSD MB WH L1200	White	-	910629145726	4MX900 581 LED50S/840 PSU A30 WH	White	581
910629132626	4MX900 LED40S/840 PSD NB WH L1200	White	-	910629145826	4MX900 491 LED40S/840 PSU A30 WH	White	491
910629132726	4MX900 LED40S/840 PSD DA20 WH L1200	White	-	910629145926	4MX900 491 LED50S/840 PSU A30 WH	White	491
910629132826	4MX900 LED40S/830 PSD WB WH L1200	White	-	910629146026	4MX900 581 LED50S/840 PSU WB WH	White	581
910629137226	4MX900 LED60S/840 PSD WB WH L1800	White	-	910629146126	4MX900 581 LED50S/840 PSU MB WH	White	581
910629137326	4MX900 LED60S/840 PSD MB WH L1800	White	-	910629146426	4MX900 491 LED50S/840 PSU WB WH	White	491
910629137426	4MX900 LED60S/840 PSD NB WH L1800	White	-	910629146526	4MX900 491 LED50S/840 PSU MB WH	White	491
910629137526	4MX900 LED60S/840 PSD DA20 WH L1800	White	-	910629146626	4MX900 491 LED50S/840 PSU NB WH	White	491
910629137626	4MX900 LED60S/830 PSD WB WH L1800	White	-	910629147026	4MX900 LED90S/840 PSD A30 WH L1800	White	-
910629137726	4MX900 LED60S/830 PSD MB WH L1800	White	-	910629147826	4MX900 LED90S/830 PSD A30 WH L1800	White	-
910629138826	4MX900 LED90S/840 PSD WB WH L1800	White	-	910629148126	4MX900 491 LED40S/830 PSU A30 WH	White	491
910629138926	4MX900 LED90S/840 PSD MB WH L1800	White	-	910629148226	4MX900 491 LED50S/830 PSU A30 WH	White	491
910629139026	4MX900 LED90S/840 PSD NB WH L1800	White	-	910629148326	4MX900 581 LED75S/840 PSU A30 WH	White	581
910629139126	4MX900 LED90S/840 PSD DA20 WH L1800	White	-	910629148526	4MX900 491 LED75S/840 PSU A30 WH	White	491
910629139226	4MX900 LED90S/830 PSD WB WH L1800	White	-	910629170126	4MX900 491 LED50S/840 PSU DA30 WH	White	491
910629140426	4MX900 581 LED40S/840 PSU WB WH	White	581	910629170326	4MX900 491 LED75S/840 PSU WB WH	White	491
910629140526	4MX900 581 LED40S/840 PSU MB WH	White	581	910629170426	4MX900 491 LED75S/840 PSU MB WH	White	491
910629140926	4MX900 581 LED40S/830 PSU MB WH	White	581	910629170826	4MX900 581 LED75S/840 PSU WB WH	White	581
910629141126	4MX900 581 LED40S/830 PSU DA20 WH	White	581	910629170926	4MX900 581 LED75S/840 PSU MB WH	White	581
910629142026	4MX900 491 LED40S/840 PSU WB WH	White	491	910629171026	4MX900 581 LED75S/840 PSU NB WH	White	581
910629142126	4MX900 491 LED40S/840 PSU MB WH	White	491	910629171326	4MX900 491 LED75S/840 PSD WB WH	White	491
910629142426	4MX900 491 LED40S/830 PSU WB WH	White	491	910629171426	4MX900 491 LED75S/840 PSD MB WH	White	491
910629143226	4MX900 LED40S/840 PSU WB WH L1200	White	-	910629171526	4MX900 491 LED75S/840 PSD NB WH	White	491
910629144426	4MX900 491 LED40S/840 PSD WB WH	White	491	910629171626	4MX900 491 LED75S/840 PSD DA30 WH	White	491
910629144526	4MX900 491 LED40S/840 PSD MB WH	White	491	910629171726	4MX900 491 LED75S/840 PSD DA20 WH	White	491
910629144626	4MX900 491 LED40S/840 PSD NB WH	White	491	910629171826	4MX900 491 LED75S/840 PSD A30 WH	White	491
910629144826	4MX900 491 LED50S/840 PSD WB WH	White	491	910629171926	4MX900 581 LED75S/840 PSD WB WH	White	581
910629144926	4MX900 491 LED50S/840 PSD MB WH	White	491	910629172026	4MX900 581 LED75S/840 PSD MB WH	White	581
910629145026	4MX900 491 LED50S/840 PSD NB WH	White	491	910629172126	4MX900 581 LED75S/840 PSD NB WH	White	581

Maxos LED Performer

Order Code	Full Product Name	Color	Trunking	
			length	
910629172226	4MX900 581 LED75S/840 PSD DA30 WH	White	581	
910629172326	4MX900 581 LED75S/840 PSD DA20 WH	White	581	
910629172426	4MX900 581 LED75S/840 PSD A30 WH	White	581	
910629173226	4MX900 581 LED50S/840 PSD A30 WH	White	581	
910629177426	4MX900 491 LED75S/830 PSD WB WH	White	491	
910500458678	4MX900 491 LED50S/840 PSD-CLO WB WH	White	491	
910500460293	4MX900 491 LED50S/840 PSD-CLO DA20 WH	White	-	
910500460294	4MX900 491 LED50S/840 PSD-CLO MB WH	White	-	
910500460295	4MX900 491 LED50S/840 PSD-CLO NB WH	White	-	
910500460296	4MX900 491 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460297	4MX900 491 LED50S/840 PSD MB WH C-2R	White	-	
910500460298	4MX900 491 LED50S/840 PSD NB WH C-2R	White	-	
910500460299	4MX900 491 LED50S/840 PSD WB WH C-2R	White	-	
910500460301	4MX900 491 LED75S/840 PSD-CLO DA20 WH	White	-	
910500460302	4MX900 491 LED75S/840 PSD-CLO NB WH	White	-	
910500460303	4MX900 491 LED75S/840 PSD-CLO WB WH	White	-	
910500460304	4MX900 491 LED75S/840 PSD DA20 WH C-2R	White	-	
910500460305	4MX900 491 LED75S/840 PSD MB WH C-2R	White	-	
910500460306	4MX900 491 LED75S/840 PSD NB WH C-2R	White	-	
910500460307	4MX900 491 LED75S/840 PSD WB WH C-2R	White	-	
910500460308	4MX900 581 LED40S/840 PSD DA20 WH	White	-	
910500460309	4MX900 581 LED40S/840 PSD MB WH	White	-	
910500460310	4MX900 581 LED40S/840 PSD NB WH	White	-	
910500460311	4MX900 581 LED40S/840 PSD WB WH	White	-	
910500460312	4MX900 581 LED50S/840 PSD DA20 WH	White	-	
910500460313	4MX900 581 LED50S/840 PSD-CLO DA20 WH	White	-	
910500460314	4MX900 581 LED50S/840 PSD-CLO MB WH	White	-	
910500460316	4MX900 581 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460317	4MX900 581 LED50S/840 PSD MB WH C-2R	White	-	
910500460318	4MX900 581 LED50S/840 PSD NB WH C-2R	White	-	
910500460319	4MX900 581 LED50S/840 PSD WB WH C-2R	White	-	
910500460320	4MX900 581 LED75S/840 PSD-CLO DA20 WH	White	-	
910500460321	4MX900 581 LED75S/840 PSD-CLO NB WH	White	-	
910500460322	4MX900 581 LED75S/840 PSD DA20 WH C-2R	White	-	
910500460323	4MX900 581 LED75S/840 PSD MB WH C-2R	White	-	
910500460324	4MX900 581 LED75S/840 PSD NB WH C-2R	White	-	
910500460325	4MX900 581 LED75S/840 PSD WB WH C-2R	White	-	
910500460326	4MX916 491 LED50S/840 PSU DA20 WH	White	-	
910500460327	4MX916 491 LED50S/840 PSU MB WH	White	-	
910500460328	4MX916 491 LED50S/840 PSU NB WH	White	-	
910500460329	4MX916 491 LED50S/840 PSU WB WH	White	-	
910500460330	4MX916 491 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460331	4MX916 491 LED50S/840 PSD MB WH C-2R	White	-	
910500460332	4MX916 491 LED50S/840 PSD NB WH C-2R	White	-	
910500460333	4MX916 491 LED50S/840 PSD WB WH C-2R	White	-	
910500460342	4MX916 581 LED50S/840 PSU DA20 WH	White	-	
910500460343	4MX916 581 LED50S/840 PSU MB WH	White	-	
910500460344	4MX916 581 LED50S/840 PSU NB WH	White	-	

Order Code	Full Product Name	Color	Trunking	
			length	
910500460346	4MX916 581 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460347	4MX916 581 LED50S/840 PSD MB WH C-2R	White	-	
910500460348	4MX916 581 LED50S/840 PSD NB WH C-2R	White	-	
910500460349	4MX916 581 LED50S/840 PSD WB WH C-2R	White	-	
910500460354	4MX916 581 LED75S/840 PSD DA20 WH C-2R	White	-	
910500460355	4MX916 581 LED75S/840 PSD MB WH C-2R	White	-	
910500460356	4MX916 581 LED75S/840 PSD NB WH C-2R	White	-	
910500460357	4MX916 581 LED75S/840 PSD WB WH C-2R	White	-	
910500460358	4MX933 491 LED50S/840 PSU DA20 WH	White	-	
910500460359	4MX933 491 LED50S/840 PSU MB WH	White	-	
910500460360	4MX933 491 LED50S/840 PSU NB WH	White	-	
910500460361	4MX933 491 LED50S/840 PSU WB WH	White	-	
910500460362	4MX933 491 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460363	4MX933 491 LED50S/840 PSD MB WH C-2R	White	-	
910500460364	4MX933 491 LED50S/840 PSD NB WH C-2R	White	-	
910500460365	4MX933 491 LED50S/840 PSD WB WH C-2R	White	-	
910500460370	4MX933 491 LED75S/840 PSD DA20 WH C-2R	White	-	
910500460371	4MX933 491 LED75S/840 PSD MB WH C-2R	White	-	
910500460372	4MX933 491 LED75S/840 PSD NB WH C-2R	White	-	
910500460373	4MX933 491 LED75S/840 PSD WB WH C-2R	White	-	
910500460374	4MX933 581 LED50S/840 PSU DA20 WH	White	-	
910500460375	4MX933 581 LED50S/840 PSU MB WH	White	-	
910500460377	4MX933 581 LED50S/840 PSU WB WH	White	-	
910500460378	4MX933 581 LED50S/840 PSD DA20 WH C-2R	White	-	
910500460379	4MX933 581 LED50S/840 PSD MB WH C-2R	White	-	
910500460380	4MX933 581 LED50S/840 PSD NB WH C-2R	White	-	
910500460381	4MX933 581 LED50S/840 PSD WB WH C-2R	White	-	
910500460386	4MX933 581 LED75S/840 PSD DA20 WH C-2R	White	-	
910500460387	4MX933 581 LED75S/840 PSD MB WH C-2R	White	-	
910500460388	4MX933 581 LED75S/840 PSD NB WH C-2R	White	-	
910500460389	4MX933 581 LED75S/840 PSD WB WH C-2R	White	-	
910629173126	4MX900 581 LED50S/840 PSD MB WH	White	581	
910629177026	4MX900 581 LED50S/840 PSD WB WH	White	581	
910629131626	4MX900 LED40S/840 PSD WB SI L1200	Silver	-	
910629131926	4MX900 LED40S/840 PSD DA20 SI L1200	Silver	-	
910629136426	4MX900 LED60S/840 PSD WB SI L1800	Silver	-	
910629136726	4MX900 LED60S/840 PSD DA20 SI L1800	Silver	-	
910629136826	4MX900 LED60S/830 PSD WB SI L1800	Silver	-	
910629136926	4MX900 LED60S/830 PSD MB SI L1800	Silver	-	
910629138026	4MX900 LED90S/840 PSD WB SI L1800	Silver	-	
910629138126	4MX900 LED90S/840 PSD MB SI L1800	Silver	-	
910629138426	4MX900 LED90S/830 PSD WB SI L1800	Silver	-	
910629141226	4MX900 491 LED40S/840 PSU WB SI	Silver	491	
910629141326	4MX900 491 LED40S/840 PSU MB SI	Silver	491	
910629141626	4MX900 491 LED40S/830 PSU WB SI	Silver	491	
910629147226	4MX900 LED90S/840 PSD A30 SI L1800	Silver	-	
910629172926	4MX900 LED40S/840 PSU WB SI L1200	Silver	-	
910629177526	4MX900 581 LED50S/840 PSU A30 SI	Silver	581	

Maxos LED Performer

