



Maxos LED Performer – efficiënte en nauwkeurige lijnverlichting.

Maxos LED Performer 4MX900

Klanten willen energie besparen en kosten verlagen in vergelijking met wat ze gewend zijn bij conventionele verlichting. Tegelijkertijd zijn er uitstekende verlichtingsomstandigheden nodig: in industriële omgevingen om veiligheid en productiviteit te waarborgen en in winkelomgevingen om de producten te laten opvallen en klanten aan te trekken. Maxos LED Performer is een uiterst flexibele oplossing die een laag energieverbruik en diverse bundelvormen biedt bij een uitstekende prijs-kwaliteitsverhouding. Maxos LED Performer biedt een diffuus en gelijkmatig lichtbeeld en is hierdoor bij uitstek geschikt voor retail-toepassingen.

Voordelen

- Energiebesparing 40% vergeleken met TL-D lichtlijnen
- Optiek met diverse lichtbundels : WB, NB, DA, A
- Past op bestaande Maxos lichtlijnen, ook beschikbaar voor TTX400 lichtlijnen

Kenmerken

- Laag energieverbruik in vergelijking met fluorescentielampen (besparingen tot ca. 40%)
- Uitstekende bundelvorm voor minder strooilicht en exacte lichtverdeling in het horizontale en verticale vlak
- Philips LED-modules (Fortimo)
- Kan gemonteerd worden op nieuwe of bestaande Maxos- en TTX400 lichtlijnen

Maxos LED Performer 4MX900

Toepassing





- Supermarkten
- Bouwmarkten
- Magazijnen
- Productieruimten

Versions



IPPR1 4MX900i 0001.JPG

Maatschets



Maxos LED Performer 4MX900

Productgegevens

IPDP_4MX900i_0001-Detail
photo



IPDP_4MX900i_0003-Detail
photo



IPDP_4MX900i_0011-Detail
photo



Maxos LED Performer 4MX900

Algemene informatie	
CE-markering	Ja
Driver/VSA inbegrepen	Ja
ENEC-markering	ENEC-markering
Brandbaarheidsmarkering	-
Gloeidraadtest	Temperatuur 650 °C, duur 30 s
Lichtbron vervangbaar	Nee
Aantal VSA's	1 unit
Code productfamilie	4MX900
Gegevens lichttechniek	
Bundelhoek van lichtbron	120 graden
Gecorreleerde kleurtemperatuur (nom)	4000 K
Kleurweergave-index (CRI)	≥80
Bedrijfs- en elektrische gegevens	
Ingangsspanning	220 tot 240 V
Ingangsfrequentie	50 to 60 Hz
Operationele temperatuur	
Omgevingstemperatuurbereik	-20 tot +40 °C
Keurmerken en classificaties	
Beschermingsklasse IEC	Veiligheidsklasse I
IK-classificatie	IK02
Beschermingsklasse	IP 40
Initiële prestaties (conform IEC)	
Aanvankelijke kleurkwaliteit	(0.38, 0.38) SDCM <3.5
Tolerantie lichtstroom	+/-10%
Toepassingsomstandigheden	
Geschikt voor willekeurige schakeling	Niet van toepassing

Algemene informatie

Order Code	Full Product Name	Type lichtbron	Ingebouwde regeling
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	-	-
8718696879672	4MX900 581 LED75S/840 PSD-CLO MB WH	LED75S	Constante lichtopbrengst
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	LED90S	-
4030732664610	4MX900 LED90S/840 PSD MB WH L1800	LED90S	-
4030732664627	4MX900 LED90S/840 PSD NB WH L1800	LED90S	-
4030732664634	4MX900 LED90S/840 PSD DA20 WH L1800	LED90S	-
4030732666249	4MX900 491 LED40S/840 PSD WB WH	LED40S	-
4030732666256	4MX900 491 LED40S/840 PSD MB WH	LED40S	-
4030732666263	4MX900 491 LED40S/840 PSD NB WH	LED40S	-
4030732666287	4MX900 491 LED50S/840 PSD WB WH	LED50S	-
4030732666294	4MX900 491 LED50S/840 PSD MB WH	LED50S	-
4030732666300	4MX900 491 LED50S/840 PSD NB WH	LED50S	-
4030732666317	4MX900 491 LED50S/840 PSD DA20 WH	LED50S	-
4030732666331	4MX900 LED40S/840 PSD A30 WH L1200	LED40S	-
4030732666355	4MX900 LED60S/840 PSD A30 WH L1800	LED60S	-
4030732666386	4MX900 491 LED40S/840 PSU A30 WH	LED40S	-
4030732666447	4MX900 491 LED50S/840 PSU WB WH	LED50S	-
4030732666812	4MX900 LED90S/840 PSD A30 WH L1800	LED90S	-
4030732667116	4MX900 491 LED75S/840 PSU A30 WH	LED75S	-
4030732667956	4MX900 581 LED75S/840 PSU WB WH	LED75S	-
4030732667963	4MX900 581 LED75S/840 PSU MB WH	LED75S	-
4030732668007	4MX900 491 LED75S/840 PSD WB WH	LED75S	-
4030732668052	4MX900 491 LED75S/840 PSD A30 WH	LED75S	-
4030732668069	4MX900 581 LED75S/840 PSD WB WH	LED75S	-
4030732664368	4MX900 LED60S/840 PSD WB SI L1800	LED60S	-
4030732664528	4MX900 LED90S/840 PSD WB SI L1800	LED90S	-
4030732664535	4MX900 LED90S/840 PSD MB SI L1800	LED90S	-
4030732664849	4MX900 491 LED40S/840 PSU WB SI	LED40S	-

Gegevens lichttechniek

Order Code	Full Product Name	Lichtrendement (gespec.) (nom.)	Aantal		
			Lichtstroom	lichtbronnen	Optiektype
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	149 lm/W	7.500 lm	-	Brede bundel
8718696879672	4MX900 581 LED75S/840 PSD-	149 lm/W	7.500 lm	1	Middelbrede bundel
Order Code	Full Product Name	Lichtrendement (gespec.) (nom.)	Aantal		
			Lichtstroom	lichtbronnen	Optiektype
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	150 lm/W	9.000 lm	1	Brede bundel
4030732664610	4MX900 LED90S/840 PSD	150 lm/W	9.000 lm	1	Middelbrede bundel

Maxos LED Performer 4MX900

Order Code	Full Product	Lichtrendement (gespec.)		Aantal	
	Name	(nom.)	Lichtstroom	lichtbronnen	Optiektype
	MB WH L1800				
4030732664627	4MX900 LED90S/ 840 PSD NB WH L1800	150 lm/W	9.000 lm	1	Smalle bundel
4030732664634	4MX900 LED90S/ 840 PSD DA20 WH L1800	150 lm/W	9.000 lm	1	Dubbel asymmetrische optiek 20°
4030732664629	4MX900 491 LED40S/ 840 PSD WB WH	159 lm/W	4.000 lm	1	Brede bundel
4030732666256	4MX900 491 LED40S/ 840 PSD MB WH	159 lm/W	4.000 lm	1	Middelbrede bundel
4030732666263	4MX900 491 LED40S/ 840 PSD NB WH	159 lm/W	4.000 lm	1	Smalle bundel
4030732666287	4MX900 491 LED50S/ 840 PSD WB WH	155 lm/W	5.000 lm	1	Brede bundel
4030732666294	4MX900 491 LED50S/ 840 PSD MB WH	155 lm/W	5.000 lm	1	Middelbrede bundel
4030732666300	4MX900 491 LED50S/ 840 PSD NB WH	155 lm/W	5.000 lm	1	Smalle bundel
4030732666317	4MX900 491 LED50S/ 840 PSD DA20 WH	155 lm/W	5.000 lm	1	Dubbel asymmetrische optiek 20°

Order Code	Full Product	Lichtrendement (gespec.)		Aantal	
	Name	(nom.)	Lichtstroom	lichtbronnen	Optiektype
4030732666331	4MX900 LED40S/ 840 PSD A30 WH L1200	154 lm/W	4.000 lm	1	Spiegel met asymmetrische ashoek 30°
4030732666355	4MX900 LED60S/ 840 PSD A30 WH L1800	161 lm/W	6.000 lm	1	Spiegel met asymmetrische ashoek 30°
4030732666386	4MX900 491 LED40S/ 840 PSU A30 WH	159 lm/W	4.000 lm	1	Spiegel met asymmetrische ashoek 30°
4030732666447	4MX900 491 LED50S/ 840 PSU WB WH	155 lm/W	5.000 lm	1	Brede bundel
4030732666812	4MX900 LED90S/ 840 PSD A30 WH L1800	150 lm/W	9.000 lm	1	Spiegel met asymmetrische ashoek 30°
4030732667116	4MX900 491 LED75S/ 840 PSU A30 WH	149 lm/W	7.500 lm	1	Spiegel met asymmetrische ashoek 30°
4030732667956	4MX900 581 LED75S/ 840 PSU WB WH	149 lm/W	7.500 lm	1	Brede bundel
4030732667963	4MX900 581 LED75S/ 840 PSU MB WH	149 lm/W	7.500 lm	1	Middelbrede bundel
4030732668007	4MX900 491 LED75S/ 840 PSD WB WH	149 lm/W	7.500 lm	1	Brede bundel
4030732668052	4MX900 491 LED75S/ 840 PSD A30 WH	149 lm/W	7.500 lm	1	Spiegel met asymmetrische ashoek 30°

Maxos LED Performer 4MX900

	Full Product	Lichtrendement (gespec.)	Aantal			
Order Code	Name	(nom.)	Lichtstroom	lichtbronnen	Optiektype	
4030732668069	4MX900	149 lm/W	7.500 lm	1	Brede bundel	
	581					
	LED75S/					
	840 PSD					
	WB WH					
	4030732664368	4MX900	161 lm/W	6.000 lm	1	Brede bundel
	LED60S/					
	840 PSD					
	WB SI					
	L1800					
	4030732664528	4MX900	150 lm/W	9.000 lm	1	Brede bundel
	LED90S/					
	840 PSD					

Bedrijfs- en elektrische gegevens

Order Code	Full Product Name	Energieverbruik
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	50,2 W
8718696879672	4MX900 581 LED75S/840 PSD-CLO MB WH	50,2 W
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	60,1 W
4030732664610	4MX900 LED90S/840 PSD MB WH L1800	60,1 W
4030732664627	4MX900 LED90S/840 PSD NB WH L1800	60,1 W
4030732664634	4MX900 LED90S/840 PSD DA20 WH L1800	60,1 W
4030732666249	4MX900 491 LED40S/840 PSD WB WH	25,2 W
4030732666256	4MX900 491 LED40S/840 PSD MB WH	25,2 W
4030732666263	4MX900 491 LED40S/840 PSD NB WH	25,2 W
4030732666287	4MX900 491 LED50S/840 PSD WB WH	32,2 W
4030732666294	4MX900 491 LED50S/840 PSD MB WH	32,2 W
4030732666300	4MX900 491 LED50S/840 PSD NB WH	32,2 W
4030732666317	4MX900 491 LED50S/840 PSD DA20 WH	32,2 W
4030732666331	4MX900 LED40S/840 PSD A30 WH L1200	25,9 W

Dimbaarheid en regelsystemen

Order Code	Full Product Name	Dimbaar
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	Ja
8718696879672	4MX900 581 LED75S/840 PSD-CLO MB WH	Ja
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	Ja
4030732664610	4MX900 LED90S/840 PSD MB WH L1800	Ja
4030732664627	4MX900 LED90S/840 PSD NB WH L1800	Ja
4030732664634	4MX900 LED90S/840 PSD DA20 WH L1800	Ja
4030732666249	4MX900 491 LED40S/840 PSD WB WH	Ja
4030732666256	4MX900 491 LED40S/840 PSD MB WH	Ja
4030732666263	4MX900 491 LED40S/840 PSD NB WH	Ja
4030732666287	4MX900 491 LED50S/840 PSD WB WH	Ja
4030732666294	4MX900 491 LED50S/840 PSD MB WH	Ja
4030732666300	4MX900 491 LED50S/840 PSD NB WH	Ja
4030732666317	4MX900 491 LED50S/840 PSD DA20 WH	Ja
4030732666331	4MX900 LED40S/840 PSD A30 WH L1200	Ja

Order Code	Full Product	Lichtrendement (gespec.)	Aantal		
	Name	(nom.)	Lichtstroom	lichtbronnen	Optiektype
4030732664535	4MX900	150 lm/W	9.000 lm	1	Middelbrede bundel
	LED90S/				
	840 PSD				
	MB SI				
4030732664849	4MX900	159 lm/W	4.000 lm	1	Brede bundel
	491				
	LED40S/				
	840 PSU				

Order Code	Full Product Name	Energieverbruik
4030732666355	4MX900 LED60S/840 PSD A30 WH L1800	37,3 W
4030732666386	4MX900 491 LED40S/840 PSU A30 WH	25,2 W
4030732666447	4MX900 491 LED50S/840 PSU WB WH	32,2 W
4030732666812	4MX900 LED90S/840 PSD A30 WH L1800	60,1 W
4030732667116	4MX900 491 LED75S/840 PSU A30 WH	50,2 W
4030732667956	4MX900 581 LED75S/840 PSU WB WH	50,2 W
4030732667963	4MX900 581 LED75S/840 PSU MB WH	50,2 W
4030732668007	4MX900 491 LED75S/840 PSD WB WH	50,2 W
4030732668052	4MX900 491 LED75S/840 PSD A30 WH	50,2 W
4030732668069	4MX900 581 LED75S/840 PSD WB WH	50,2 W
4030732664368	4MX900 LED60S/840 PSD WB SI L1800	37,3 W
4030732664528	4MX900 LED90S/840 PSD WB SI L1800	60,1 W
4030732664535	4MX900 LED90S/840 PSD MB SI L1800	60,1 W
4030732664849	4MX900 491 LED40S/840 PSU WB SI	25,2 W

Order Code	Full Product Name	Dimbaar
4030732666355	4MX900 LED60S/840 PSD A30 WH L1800	Ja
4030732666386	4MX900 491 LED40S/840 PSU A30 WH	Nee
4030732666447	4MX900 491 LED50S/840 PSU WB WH	Nee
4030732666812	4MX900 LED90S/840 PSD A30 WH L1800	Ja
4030732667116	4MX900 491 LED75S/840 PSU A30 WH	Nee
4030732667956	4MX900 581 LED75S/840 PSU WB WH	Nee
4030732667963	4MX900 581 LED75S/840 PSU MB WH	Nee
4030732668007	4MX900 491 LED75S/840 PSD WB WH	Ja
4030732668052	4MX900 491 LED75S/840 PSD A30 WH	Ja
4030732668069	4MX900 581 LED75S/840 PSD WB WH	Ja
4030732664368	4MX900 LED60S/840 PSD WB SI L1800	Ja
4030732664528	4MX900 LED90S/840 PSD WB SI L1800	Ja
4030732664535	4MX900 LED90S/840 PSD MB SI L1800	Ja
4030732664849	4MX900 491 LED40S/840 PSU WB SI	Nee

Maxos LED Performer 4MX900

Eigenschappen behuizing en afmetingen

Order Code	Full Product Name	Kleur behuizing
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	Wit
8718696879672	4MX900 581 LED75S/840 PSD-CLO MB WH	Wit
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	Wit
4030732664610	4MX900 LED90S/840 PSD MB WH L1800	Wit
4030732664627	4MX900 LED90S/840 PSD NB WH L1800	Wit
4030732664634	4MX900 LED90S/840 PSD DA20 WH L1800	Wit
4030732666249	4MX900 491 LED40S/840 PSD WB WH	Wit
4030732666256	4MX900 491 LED40S/840 PSD MB WH	Wit
4030732666263	4MX900 491 LED40S/840 PSD NB WH	Wit
4030732666287	4MX900 491 LED50S/840 PSD WB WH	Wit
4030732666294	4MX900 491 LED50S/840 PSD MB WH	Wit
4030732666300	4MX900 491 LED50S/840 PSD NB WH	Wit
4030732666317	4MX900 491 LED50S/840 PSD DA20 WH	Wit
4030732666331	4MX900 LED40S/840 PSD A30 WH L1200	Wit


Order Code	Full Product Name	Kleur behuizing
4030732666355	4MX900 LED60S/840 PSD A30 WH L1800	Wit
4030732666386	4MX900 491 LED40S/840 PSU A30 WH	Wit
4030732666447	4MX900 491 LED50S/840 PSU WB WH	Wit
4030732666812	4MX900 LED90S/840 PSD A30 WH L1800	Wit
4030732667116	4MX900 491 LED75S/840 PSU A30 WH	Wit
4030732667956	4MX900 581 LED75S/840 PSU WB WH	Wit
4030732667963	4MX900 581 LED75S/840 PSU MB WH	Wit
4030732668007	4MX900 491 LED75S/840 PSD WB WH	Wit
4030732668052	4MX900 491 LED75S/840 PSD A30 WH	Wit
4030732668069	4MX900 581 LED75S/840 PSD WB WH	Wit
4030732664368	4MX900 LED60S/840 PSD WB SI L1800	Zilver
4030732664528	4MX900 LED90S/840 PSD WB SI L1800	Zilver
4030732664535	4MX900 LED90S/840 PSD MB SI L1800	Zilver
4030732664849	4MX900 491 LED40S/840 PSU WB SI	Zilver

Toepassingsomstandigheden


Order Code	Full Product Name	Maximaal dimniveau
8718696976746	4MX900 491 LED75S/840 PSD WB WH C-2R	1%
8718696879672	4MX900 581 LED75S/840 PSD-CLO MB WH	1%
4030732664603	4MX900 LED90S/840 PSD WB WH L1800	1%
4030732664610	4MX900 LED90S/840 PSD MB WH L1800	1%
4030732664627	4MX900 LED90S/840 PSD NB WH L1800	1%
4030732664634	4MX900 LED90S/840 PSD DA20 WH L1800	1%
4030732666249	4MX900 491 LED40S/840 PSD WB WH	1%
4030732666256	4MX900 491 LED40S/840 PSD MB WH	1%
4030732666263	4MX900 491 LED40S/840 PSD NB WH	1%
4030732666287	4MX900 491 LED50S/840 PSD WB WH	1%
4030732666294	4MX900 491 LED50S/840 PSD MB WH	1%
4030732666300	4MX900 491 LED50S/840 PSD NB WH	1%
4030732666317	4MX900 491 LED50S/840 PSD DA20 WH	1%
4030732666331	4MX900 LED40S/840 PSD A30 WH L1200	1%

Order Code	Full Product Name	Maximaal dimniveau
4030732666355	4MX900 LED60S/840 PSD A30 WH L1800	1%
4030732666386	4MX900 491 LED40S/840 PSU A30 WH	Niet van toepassing
4030732666447	4MX900 491 LED50S/840 PSU WB WH	Niet van toepassing
4030732666812	4MX900 LED90S/840 PSD A30 WH L1800	1%
4030732667116	4MX900 491 LED75S/840 PSU A30 WH	Niet van toepassing
4030732667956	4MX900 581 LED75S/840 PSU WB WH	Niet van toepassing
4030732667963	4MX900 581 LED75S/840 PSU MB WH	Niet van toepassing
4030732668007	4MX900 491 LED75S/840 PSD WB WH	1%
4030732668052	4MX900 491 LED75S/840 PSD A30 WH	1%
4030732668069	4MX900 581 LED75S/840 PSD WB WH	1%
4030732664368	4MX900 LED60S/840 PSD WB SI L1800	1%
4030732664528	4MX900 LED90S/840 PSD WB SI L1800	1%
4030732664535	4MX900 LED90S/840 PSD MB SI L1800	1%
4030732664849	4MX900 491 LED40S/840 PSU WB SI	Niet van toepassing


Polar Wide Diagrams



IFPS_4MX900 491 1xLED40S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/830 PSD DA20-
Polar Normal (separate)




IFPS_4MX900 491 1xLED40S/830 PSD MB-
Polar Normal (separate)

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED40S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED40S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD DA20-
Polar Normal (separate)**

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED50S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSD NB-
Polar Normal (separate)**

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 491 1xLED71S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD DA20-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 491 1xLED75S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/830 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**



IFPS_4MX900 581 1xLED50S/840 PSU MB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED48S/840 PSD NB-
Polar Normal (separate)




IFPS_4MX900 L1800 1xLED60S/830 PSD MB-
Polar Normal (separate)

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 L1800 1xLED60S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED60S/840 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED85S/830 PSD MB-
Polar Normal (separate)**



**IFPS_4MX900 L1800 1xLED85S/830 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 L1800 1xLED90S/840 PSD NB-
Polar Normal (separate)**

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED40S/830 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSD NB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/830 PSU WB-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED40S/840 PSD
A30-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED40S/840 PSD NB-
Polar Normal (separate)**

Maxos LED Performer 4MX900


Polar Wide Diagrams




IFPS_4MX900 G3 491 1xLED40S/840 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSD A30-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSD NB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSD WB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/830 PSU WB-
Polar Normal (separate)



IFPS_4MX900 G3 491 1xLED50S/840 PSD
DA20-Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD MB-
Polar Normal (separate)




IFPS_4MX900 G3 491 1xLED50S/840 PSD NB-
Polar Normal (separate)

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED50S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED50S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSD
DA20-Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED71S/830 PSU A30-
Polar Normal (separate)**



**IFPS_4MX900 G3 491 1xLED75S/840 PSD A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 491 1xLED75S/840 PSD WB-
Polar Normal (separate)**

Maxos LED Performer 4MX900


Polar Wide Diagrams




**IFPS_4MX900 G3 491 1xLED75S/840 PSU A30-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSD WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED40S/840 PSU WB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/830 PSU MB-
Polar Normal (separate)**




**IFPS_4MX900 G3 581 1xLED50S/840 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED71S/830 PSD WB-
Polar Normal (separate)**






**IFPS_4MX900 G3 581 1xLED71S/830 PSU MB-
Polar Normal (separate)**



**IFPS_4MX900 G3 581 1xLED75S/840 PSD WB-
Polar Normal (separate)**

Maxos LED Performer 4MX900




Polar Wide Diagrams



**IFPS_4MX900 G3 581 1xLED75S/840 PSU MB-
Polar Normal (separate)**

**IFPS_4MX900 G3 581 1xLED75S/840 PSU WB-
Polar Normal (separate)**

**IFPS_4MX900 G3 L1800 1xLED60S/830 PSD
WB-Polar Normal (separate)**



**IFPS_4MX900 G3 L1800 1xLED60S/840 PSD
WB-Polar Normal (separate)**

**IFPS_4MX900 G3 L1800 1xLED85S/830 PSD
WB-Polar Normal (separate)**

**IFPS_4MX900 G3 L1800 1xLED90S/840 PSD
NB-Polar Normal (separate)**

