



LED Marker BBG150/151/152 – Reliable landscape lighting for harmonious city living

LED Marker

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple design with reliable lighting performance, this low-cost white-light LED marker delivers a glare-free soft light effect.

Benefits

- Reliable, robust design
- Easy installation and maintenance-free
- Environmentally friendly: no hazardous substances (no mercury, no lead) or UV

Features

- Low-power white-light LED light source, available in a choice of warm white (3000 K) or neutral white (4000 K)
- Integrated driver and equipped mounting box
- Long lifetime of 25,000 hours (70% lumen maintenance)
- IP67 protection and IK10 impact resistance

LED Marker

Application

- Parks and gardens
- Squares, plazas
- Residential areas

Specifications

Type	BBG150 (rectangle version) BBG151 (square version) BBG152 (round version)
Light source	30 x LED-LB
Light colour	Warm white, 3000 K Neutral white, 4000 K
Power consumption	< 4 W
Driver current	20 mA
Inrush current	0.035 A
Power/data supply	220-240 V / 50-60 Hz Integrated
Driver	Integrated in independent driver box
Optic	Wide beam
Optical cover	Translucent diffuse tempering glass

Connection	Push-in connector in 3 poles accepting wires 3 core x > 1.0 mm
Cable gland	1 x M16
Material	Housing: aluminium Diffuser: tempering glass Gasket: silicone rubber, heat-resistant Surface cover: stainless steel
Colour	Housing: grey, RAL 7043 Cover: stainless
Installation	In ground recessed mounting Operating temperature: - 20 °C < T
Maintenance	No internal cleaning required
Lifetime	25.000 hours, 70% lumen maintenance at T
Remarks	No adjustability possible

Versions



LED Marker BBG150 pedestrian luminaire



LED Marker BBG151 pedestrian luminaire



LED Marker BBG152 pedestrian luminaire

LED Marker

Approval and Application

Mech. impact protection code IK10

Controls and Dimming

Dimmable No

General Information

CE mark CE mark

Optical cover/lens type Front-glass
uplighting version

Driver included Yes

Flammability mark For mounting on
normally flammable
surfaces

Lamp family code LED-LP

Light source replaceable No

Number of gear units 1 unit

Number of light sources 30 pcs

Mechanical and Housing

Colour Dark Grey

General Information

Order Code	Full Product Name	Light source colour
911401177980	BBG150 LED50/WW PSU 220-240V IP67	830 warm white
911401178680	BBG151 LED50/WW PSU 220-240V IP67	830 warm white
911401723801	BBG152 LED50/NW PSU 220-240V IP67	740 neutral white
911401723901	BBG152 LED50/WW PSU 220-240V IP67	830 warm white

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401177980	BBG150 LED50/WW PSU 220-240V IP67	3000 K	>80	50 lm
911401178680	BBG151 LED50/WW PSU 220-240V IP67	3000 K	>80	50 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401723801	BBG152 LED50/NW PSU 220-240V IP67	4000 K	>70	50 lm
911401723901	BBG152 LED50/WW PSU 220-240V IP67	3000 K	>80	55 lm

