



DecoScene LED – magical light from below

DecoScene LED BBP623

Whether floodlighting a piece of architecture or creating accent effects, for many designers the ideal luminaire would be invisible. With their recessed housings, in-ground floodlights are about as close as it gets to this ideal situation. DecoScene LED has been designed to deliver the optimal upward lighting effect – from high-powered floodlighting to more subtle effects such as accent lighting. Its unique collimating optic delivers a uniform light output. Round housing fits snugly into paving, concrete or grass, leaving the surface flush and unobtrusive during the day. The combination of the LED technology and best-in-class optics makes DecoScene LED a totally flexible solution – easy to install, no matter where, and creating a perfect lighting effect.

Benefits

- Best-in-class optical efficacy.
- No glue used: allows serviceability and greater recyclability at end-of-life.
- Design facilitates use with conventional DecoScene products and integration into projects.

Features

- Two types of white (2700 or 4000 K)
- Choice of three different circular beams from narrow 12° to wide 40°
- Asymmetrical optic for wall-washing effects on façades

Application

- Classical and modern buildings
- Bridges and structures
- Monuments and sculptures
- Parks and gardens