



DayZone – innovative design meets sustainability

DayZone

For general office lighting, customers want to capture the benefits LED technology has to offer – sustainability and fresh, high-impact design, without compromising visual comfort. Our DayZone recessed LED luminaire delivers high-quality functional lighting with an energy efficiency that matches or even outperforms traditional fluorescent systems. But what makes DayZone really shine is its impressive visual comfort. Our innovative use of LED technology has created a luminaire that breaks away from fluorescent lighting designs of the past to offer a striking appearance and light effect. Glare control and color consistency are compliant with future office norms. DayZone is available in square versions and, to ensure a better fit in plaster ceiling applications, in a round housing.

Benefits

- Inspiring design
- Sustainable solution
- Visual comfort

Features

- Lumen package enabling 500 lux using conventional luminaire spacing
- Dedicated MLO optic design
- Special patented light-mixing chamber
- Round housing available for plaster ceiling applications

Application

- Offices
- Retail
- Hospitality
- Healthcare


Specifications

Type	BBS560 (module size: 600 mm)
	BBS562 (module size: 625 mm)
	BBS567 (module size: 675 mm)
	BBS561 (round housing)
Ceiling type	Exposed- and symmetrical concealed T-bar ceiling and plaster (board) ceiling
Ceiling grid	Module size in length: 600 x 600 mm
	Module size in length: 625 x 625 mm
	Module size in length: 675 x 675 mm
Light source	Philips DayZone LED module
Power (steady state in W, +/- 10%)	4000 K: 51 W (LED35S) 3000 K: 55 W (LED35S)
Beam angle	90°


Specifications

Dimming	Compatible with DALI controllers
Controls system input	DALI
Optical cover	OLC micro-lens optic, partial (AC-MLO-C)
	OLC micro-lens optic, full (AC-MLO)*
	OLC micro-lens optic, partial (PC-MLO-C)
	OLC micro-lens optic, full (PC-MLO)*
	*not for BBS561
Options	Emergency lighting (integrated): 3 hours (EL3)*
	Lighting controls: Actilume multi-controller (ACL)*
	Compatible with DALI (only relating to dimmable driver PSD)
	Euro fuse (FU) included
	*not for BBS561
Materials	Housing: zinc-coated steel
	Rim: post lacquered
	Optical cover: acrylic (AC-MLO), polycarbonate (PC-MLO)
Color	White (WH), silver grey (SI)
	Standard RAL colors available on request

Product details




DayZone offers inspiring design featuring a dedicated MLO optic




Special patented mixing chamber concept delivers overhead glare control through LED shielding and color consistency throughout the fixture by means of highly reflective coating technology


Product details




DayZone only outer zone lit




MLO cover can be opened for easy servicing



Connection block 2 x T-BST14 (Wieland)




Connection block T-GST18 (Wieland)




DayZone both inner- and outer zone lit



DayZone with Actilume sensor



DayZone recessed round BBS561 with white rim



MLO cover can be opened for easy servicing

Accessories

Brackets for plaster ceilings

Ordercode 910403202503,
910403203803, 910403204103



Brackets for concealed ceilings with
T-bar 38 mm

Ordercode 910403202603



Brackets for concealed ceilings

Ordercode 910403202703

