



ColorGraz MX4 Powercore – linear exterior LED wall grazing with intelligent color light

ColorGraz MX4 Powercore

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

Benefits

- Even illumination and color mixing at distances greater than 152 mm from fixture lens, with no shadows in between fixtures when used end-to-end
- Light output of more than 600/500 lumens per 300 mm/foot (RGBW/RGBA full intensity)
- Incorporates Powercore technology to directly accept 100-277 V AC line voltage

Features


- Five standard beam angles
- Individual control of each 300 mm (1 foot) segment
- 100-277 V auto-ranging Powercore technology
- Chromasync technology provides consistent output unit-to-unit and white light output control
- Simple push-and-click connectors

ColorGraze MX4 Powercore

Application

- Interior: nightclubs, bars, hotels, casinos, churches, stores
- Exterior: facades, surfaces, structures

Dimensional drawing



Product	A	B
BCS559 10x60 RGBA L305	134 mm	305 mm
BCS559 9 RGBA L305	134 mm	305 mm
BCS559 60x30 RGBW L305	134 mm	305 mm
BCS559 10x60 RGBA L1219	1049 mm	1219 mm
BCS559 15x30 RGBA L1219	1049 mm	1219 mm
BCS559 9 RGBW L305	134 mm	305 mm
BCS559 60x30 RGBA L1219	1049 mm	1219 mm
BCS559 10x60 RGBW L305	134 mm	305 mm
BCS559 9 RGBA L1219	1049 mm	1219 mm
BCS559 30x60 RGBA L305	134 mm	305 mm
BCS559 60x30 RGBA L305	134 mm	305 mm
BCS559 15x30 RGBW L305	134 mm	305 mm
BCS559 15x30 RGBW L1219	1049 mm	1219 mm
BCS559 15x30 RGBA L305	134 mm	305 mm
BCS559 9 RGBW L1219	1049 mm	1219 mm
BCS559 30x60 RGBW L1219	1049 mm	1219 mm
BCS559 10x60 RGBW L1219	1049 mm	1219 mm
BCS559 60x30 RGBW L1219	1049 mm	1219 mm
BCS559 30x60 RGBA L1219	1049 mm	1219 mm
BCS559 30x60 RGBW L305	134 mm	305 mm

Product details

Graze Powercore Detail photo



Graze Powercore Detail photo



ColorGraze MX4 Powercore

