



# ColorGraz MX4 Powercore – linear exterior LED wall grazing with intelligent color light

## ColorGraz MX4 Powercore

High-output luminaire for high-intensity multi-story façade and surface illumination at minimal setback; RGBW and RGBA options provide an expanded color palette and white light capability in one fixture.

### Benefits

- Even illumination and color mixing at distances greater than 152 mm from fixture lens, with no shadows in between fixtures when used end-to-end
- Light output of more than 600/500 lumens per 300 mm/foot (RGBW/RGBA full intensity)
- Incorporates Powercore technology to directly accept 100-277 V AC line voltage

### Features

- Five standard beam angles
- Individual control of each 300 mm (1 foot) segment
- 100-277 V auto-ranging Powercore technology
- Chromasync technology provides consistent output unit-to-unit and white light output control
- Simple push-and-click connectors

# ColorGraze MX4 Powercore


## Application

- Interior: nightclubs, bars, hotels, casinos, churches, stores
- Exterior: facades, surfaces, structures

## Versions



## Dimensional drawing



Product	A	B
BCS559 10x60 RGBA L1219	1049 mm	1219 mm
BCS559 15x30 RGBA L305	134 mm	305 mm

## Product details



Graze Powercore Detail photo



Graze Powercore Detail photo

## ColorGraze MX4 Powercore

