



ClearWay – economical LED performance

ClearWay

LED technology represents a breakthrough in lighting in many different respects. The light quality provided by LEDs, for example, has made our roads safer, while the tremendous efficacy of LEDs is helping cities reduce their energy bills. At Philips, we believe we can make even more roads safer, and help more municipalities achieve their goal of reducing energy consumption. That's why we have developed ClearWay – a LED road luminaire that is affordable yet does not compromise on light quality and energy efficiency.

Benefits

- Low initial investment
- Based on LEDGINE O
- Significant energy savings

Features

- Dedicated design for LED technology
- Long lifetime
- Low energy consumption compared to conventional luminaires

Application

- Major roads
- Residential roads and streets

Specifications

Type	BGP303
Light source	Integral LED-module
Power (+/-10%)	13 to 87 W (depending on version)
Luminous flux	Nominal: 1800 to 12,000 lm (depending on the version) System: 1600 to 10,100 lm (depending on the version)
Luminaire efficacy	116 to 133 lm/W (depending on the version)

Correlated Color	4000 K
Temperature	(3000 K upon request)
Color Rendering Index	>70 >80 for 3000 K
Useful life	100,000 hours min L87B10 at 250C ambient temperature (depending on version)

Operating temperature range	-30 to +35 °C
Driver	Built-in (self-ballasted LED-module)
Power/Data supply	PSU, PSR, PSD
Mains voltage	220-240 V / 50-60 Hz
Optic	Distribution Narrow (DN10); Distribution Medium (DM11), Distribution Medium (DM50); Distribution Wide (DW10) Other optics upon request
Optical cover	Glass, flat
Material	Housing: high-pressure, die-cast aluminum

Color	Grey (RAL 7035)
Maintenance	Opening with screw
Installation	Side entry : Ø 42/60 or 76 Post top : Ø 42/60 or 76 Recommended mounting height: 4 to 12 m Standard tilt angle post top: 5° Adjustable tilt angle: Post top 42-60 and 76: 0, 5°, 10°, 15° Side entry 42-60: -15°, -10°, -5°, 0, 5°, 10°, 15° Adjustable light distribution: N/A Max SCx: 0,029 m²

Versions



ClearWay BGP303 road-lighting luminaire



ClearWay BGP303 road-lighting luminaire

Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Philips standard surge protection level

General Information

Light source color	740 neutral white
Optical cover/lens type	Flat glass
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Product Family Code	BGP303

Initial Performance (IEC Compliant)

Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>70

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

Mechanical and Housing

Color	Gray
-------	------

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	0% (digital)
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	0% (digital)
910925864635	BGP303 LED18-4S/740 PSU I DM11 76	0% (digital)
910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	Not applicable
910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	Not applicable
910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	Not applicable
910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	Not applicable
910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	Not applicable
910925864870	BGP303 LED25-4S/740 PSU I DM11 76	Not applicable
910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	Not applicable
910925864872	BGP303 LED35-4S/740 PSU I DM11 76	Not applicable
910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	Not applicable
910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	Not applicable
910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	Not applicable
910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	Not applicable
910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	Not applicable
910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	Not applicable
910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	Not applicable
910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	Not applicable
910925864873	BGP303 LED69-4S/740 PSU I DM11 76	Not applicable
910925864874	BGP303 LED120-4S/740 PSU I DM11 76	Not applicable
910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	Not applicable
910925864876	BGP303 LED99-4S/740 PSU I DX10 76	Not applicable
910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	Not applicable
910925864878	BGP303 LED120-4S/740 PSU I DX10 76	Not applicable

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	Yes	910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	Yes
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	Yes	910925864635	BGP303 LED18-4S/740 PSU I DM11 76	-
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	Yes	910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	No
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	Yes	910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	No
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	Yes	910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	No
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	Yes	910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	No
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	Yes	910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	No
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	Yes	910925864870	BGP303 LED25-4S/740 PSU I DM11 76	No
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	Yes	910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	No
910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	Yes	910925864872	BGP303 LED35-4S/740 PSU I DM11 76	No
910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	Yes	910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	No

Order Code	Full Product Name	Dimmable
910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	No
910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	No
910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	No
910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	No
910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	No
910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	No
910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	No

Order Code	Full Product Name	Dimmable
910925864873	BGP303 LED69-4S/740 PSU I DM11 76	No
910925864874	BGP303 LED120-4S/740 PSU I DM11 76	No
910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	No
910925864876	BGP303 LED99-4S/740 PSU I DX10 76	No
910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	No
910925864878	BGP303 LED120-4S/740 PSU I DX10 76	No

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	CE mark	Coating	Country version
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	150° x 62°	-	-	NO
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	150° x 62°	-	-	NO
910925864635	BGP303 LED18-4S/740 PSU I DM11 76	150° x 62°	-	-	-
910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	150° x 62°	CE mark	-	-
910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	150° x 62°	CE mark	-	-
910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	150° x 62°	CE mark	-	-

Order Code	Full Product Name	Luminaire light beam spread	CE mark	Coating	Country version
910925864870	BGP303 LED25-4S/740 PSU I DM11 76	150° x 62°	CE mark	-	-
910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	150° x 62°	CE mark	-	-
910925864872	BGP303 LED35-4S/740 PSU I DM11 76	150° x 62°	CE mark	-	-
910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	150° x 62°	CE mark	-	-
910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	150° x 62°	CE mark	-	-
910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	150° x 62°	CE mark	-	-
910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	150° x 62°	CE mark	-	-
910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	150° x 62°	CE mark	-	-
910925864873	BGP303 LED69-4S/740 PSU I DM11 76	150° x 62°	CE mark	-	-
910925864874	BGP303 LED120-4S/740 PSU I DM11 76	-	CE mark	-	-
910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	-	CE mark	-	-
910925864876	BGP303 LED99-4S/740 PSU I DX10 76	-	CE mark	-	-
910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	-	CE mark	-	-
910925864878	BGP303 LED120-4S/740 PSU I DX10 76	-	CE mark	-	-

General Information (2/2)

Order Code	Full Product Name	Gear	Gland material	Glow-wire test	Lamp family code	Lamp version	Number of light sources	Optic type	Standard RAL color
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED18	4S	1 pc	Distribution medium	Light gray
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED25	4S	1 pc	Distribution medium	Light gray
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED35	4S	1 pc	Distribution medium	Light gray
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED54	4S	1 pc	Distribution medium	Light gray
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED69	4S	1 pc	Distribution medium	Light gray
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED99	4S	1 pc	Distribution medium	Light gray
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED18	4S	1 pc	Distribution medium 50	Light gray
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED25	4S	1 pc	Distribution medium	Light gray
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED35	4S	1 pc	Distribution medium	Light gray
910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED54	4S	1 pc	Distribution medium	Light gray
910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED69	4S	1 pc	Distribution medium	Light gray
910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	EBD	Cable gland plastic	Temperature 960 °C, duration 5 s	LED99	4S	1 pc	Distribution medium	Light gray
910925864635	BGP303 LED18-4S/740 PSU I DM11 76	EB	Cable gland plastic	Temperature 960 °C, duration 5 s	LED18	4S	1 pc	Distribution medium 11	Light gray
910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	-	-	-	LED25	-	-	Distribution medium 11	-
910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	-	-	-	LED35	-	-	Distribution medium 11	-
910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	-	-	-	LED25	-	-	Distribution medium 11	-
910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	-	-	-	LED35	-	-	Distribution medium 11	-
910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	-	-	-	LED18	-	-	Distribution medium 11	-
910925864870	BGP303 LED25-4S/740 PSU I DM11 76	-	-	-	LED25	-	-	Distribution medium 11	-
910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	-	-	-	LED35	-	-	Distribution medium 11	-
910925864872	BGP303 LED35-4S/740 PSU I DM11 76	-	-	-	LED35	-	-	Distribution medium 11	-
910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	-	-	-	LED54	-	-	Distribution medium 11	-
910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	-	-	-	LED84	-	-	Distribution medium 11	-
910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	-	-	-	LED99	-	-	Distribution medium 11	-
910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	-	-	-	LED120	-	-	Distribution medium 11	-
910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	-	-	-	LED54	-	-	Distribution medium 11	-
910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	-	-	-	LED84	-	-	Distribution medium 11	-

Order Code	Full Product Name	Gear	Gland material	Glow-wire test	Lamp family code	Lamp version	Number of light sources	Optic type	Standard RAL color
910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	-	-	-	LED99	-	-	Distribution medium 11	-
910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	-	-	-	LED120	-	-	Distribution medium 11	-
910925864873	BGP303 LED69-4S/740 PSU I DM11 76	-	-	-	LED69	-	-	Distribution medium 11	-
910925864874	BGP303 LED120-4S/740 PSU I DM11 76	-	-	-	LED120	-	-	Distribution extra wide 10	-
910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	-	-	-	LED99	-	-	Distribution extra wide 10	-
910925864876	BGP303 LED99-4S/740 PSU I DX10 76	-	-	-	LED99	-	-	Distribution extra wide 10	-
910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	-	-	-	LED120	-	-	Distribution extra wide 10	-
910925864878	BGP303 LED120-4S/740 PSU I DX10 76	-	-	-	LED120	-	-	Distribution extra wide 10	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux	Order Code	Full Product Name	Initial luminous flux
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	1602 lm	910925864870	BGP303 LED25-4S/740 PSU I DM11 76	2225 lm
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	2225 lm	910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	3115 lm
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	3115 lm	910925864872	BGP303 LED35-4S/740 PSU I DM11 76	3115 lm
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	4752 lm	910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	4752 lm
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	6160 lm	910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	-
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	8700 lm	910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	8700 lm
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	1602 lm	910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	-
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	2225 lm	910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	4752 lm
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	3115 lm	910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	-
910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	4752 lm	910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	8700 lm
910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	6160 lm	910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	-
910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	8700 lm	910925864873	BGP303 LED69-4S/740 PSU I DM11 76	6160 lm
910925864635	BGP303 LED18-4S/740 PSU I DM11 76	1602 lm	910925864874	BGP303 LED120-4S/740 PSU I DM11 76	-
910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	2225 lm	910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	8700 lm
910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	3115 lm	910925864876	BGP303 LED99-4S/740 PSU I DX10 76	8700 lm
910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	2225 lm	910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	-
910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	3115 lm	910925864878	BGP303 LED120-4S/740 PSU I DX10 76	-
910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	1602 lm			

Mechanical and Housing

Order Code	Full Product Name	Length	Order Code	Full Product Name	Length
910925452112	BGP303 LED18-4S/740 PSR I DM50 D9 STD 42	-	910925452122	BGP303 LED54-4S/740 PSR II DM50 D9 STD 4	-
910925452113	BGP303 LED25-4S/740 PSR I DM50 D9 STD 42	-	910925452123	BGP303 LED69-4S/740 PSR II DM50 D9 STD 4	-
910925452114	BGP303 LED35-4S/740 PSR I DM50 D9 STD 42	-	910925452124	BGP303 LED99-4S/740 PSR II DM50 D9 STD 4	-
910925452115	BGP303 LED54-4S/740 PSR I DM50 D9 STD 42	-	910925864635	BGP303 LED18-4S/740 PSU I DM11 76	-
910925452116	BGP303 LED69-4S/740 PSR I DM50 D9 STD 42	-	910925864857	BGP303 LED25-4S/740 PSU II DM11 C450CE 4	600 mm
910925452117	BGP303 LED99-4S/740 PSR I DM50 D9 STD 42	-	910925864858	BGP303 LED35-4S/740 PSU II DM11 C450CE 4	600 mm
910925452119	BGP303 LED18-4S/740 PSR II DM50 D9 STD 4	-	910925864863	BGP303 LED25-4S/740 PSU I DM11 C450CE 42	600 mm
910925452120	BGP303 LED25-4S/740 PSR II DM50 D9 STD 4	-	910925864864	BGP303 LED35-4S/740 PSU I DM11 C450CE 42	600 mm
910925452121	BGP303 LED35-4S/740 PSR II DM50 D9 STD 4	-	910925864869	BGP303 LED18-4S/740 PSU I DM11 42/60	600 mm

Order Code	Full Product Name	Length
910925864870	BGP303 LED25-4S/740 PSU I DM11 76	600 mm
910925864871	BGP303 LED35-4S/740 PSU I DM11 42/60	600 mm
910925864872	BGP303 LED35-4S/740 PSU I DM11 76	600 mm
910925864859	BGP303 LED54-4S/740 PSU II DM11 C450CE 4	600 mm
910925864860	BGP303 LED84-4S/740 PSU II DM11 C450CE 4	600 mm
910925864861	BGP303 LED99-4S/740 PSU II DM11 C450CE 4	600 mm
910925864862	BGP303 LED120-4S/740 PSU II DM11 C450CE	600 mm
910925864865	BGP303 LED54-4S/740 PSU I DM11 C450CE 42	600 mm
910925864866	BGP303 LED84-4S/740 PSU I DM11 C450CE 42	600 mm

Order Code	Full Product Name	Length
910925864867	BGP303 LED99-4S/740 PSU I DM11 C450CE 42	600 mm
910925864868	BGP303 LED120-4S/740 PSU I DM11 C450CE 4	600 mm
910925864873	BGP303 LED69-4S/740 PSU I DM11 76	600 mm
910925864874	BGP303 LED120-4S/740 PSU I DM11 76	600 mm
910925864875	BGP303 LED99-4S/740 PSU I DX10 42/60	600 mm
910925864876	BGP303 LED99-4S/740 PSU I DX10 76	600 mm
910925864877	BGP303 LED120-4S/740 PSU I DX10 42/60	600 mm
910925864878	BGP303 LED120-4S/740 PSU I DX10 76	600 mm

