




Selenium LED – simply efficient

Selenium LED

Selenium LED is a cost-effective road-lighting luminaire, which delivers over 60% energy saving compared with conventional solutions. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. The LEDGINE technology inside the luminaire ensures an efficient and uniform light distribution, covering the widest possible range of applications. And installation and maintenance could not be simpler: connectors and driver are directly accessible, without the use of tools.

Benefits

- Simplicity – limited configurations
- Efficient, without compromising on light quality
- Easy installation and maintenance

Features

- LEDGINE technology inside
- Flat glass
- Direct access to connectors and driver; no tools required

Application

- Roads: intra and inter-urban motorized traffic /major roads
- Streets: mixed traffic
- Car parks, roundabouts

Specifications

Type	BGP340
Light source	Integral LED-module
Power (+/-10%)	29 to 94 W
Luminous flux	3680 to 11,040 lm


Luminaire efficacy	>105 lm/W
Correlated Color	4000 K
Temperature	
Color Rendering Index	> 76

Selenium LED

Lumen maintenance at median useful life*	min L80
75000 h	
Control gear failure rate at median useful life	7.5%
75000 h	
Performance Ambient Temperature Tq	+25 °C
Operating temperature range	-30 to +45 °C
Driver	Separate (non-self ballasted LED-module)
Mains voltage	220-240 V / 50-60 Hz
Inrush current	80 A / 150 µS
Dimming	Dynadimmer Mains dimming Dimming via Telemanagement RF
Controls system input	1-10 V and DALI
Options	RF Antenne Photocell Constant Light Output (CLO) Nemasocket Mains dimming (D13) Marine salt protected coating (MSP) Surge protection up to 10 kV Stand alone dimming via Dynadimmer (DDF) External dimming: DALI or 1-10 V (D7 or D9) Knife connector (KC)


Optic	Medium beam
Optical cover	Glass, flat
Material	Housing: high-pressure, die-cast aluminum Optics: plastic (PC) Gasket: silicone rubber, heat resistant Cover: glass, thermally hardened
Color	RAL7035 Other RAL colors available on request
Connection	Wieland
Maintenance	Opening by one clip
Installation	Post top mounting: Ø 60 / 76 mm Side entry mounting: Ø 34 / 60 mm Reversible spigot for side-entry and post-top Recommended mounting height: 5 to 12 m Standard tilt angle post top: 5° Adjustable tilt angle: 0°, 5° and 15° Max SCx: 0.077 m²

Versions




Selenium LED BGP340 road-lighting luminaire


Product details




OPDP_BGP340i_0001-Detail photo






OPDP_BGP340i_0003-Detail photo



OPDP_BGP340i_0005-Detail photo




OPDP_BGP340i_0007-Detail photo



OPDP_BGP340i_0017-Detail photo

Product details



OPDP_BGP340i_0019-Detail
photo

Approval and Application

Mech. impact protection code IK08

General Information

Luminaire light beam spread 160°

CE mark CE mark

Light source color 740 neutral white

Optical cover/lens type Flat glass

Driver included Yes

Flammability mark -

Glow-wire test Temperature 960 °C, duration 5 s

Light source replaceable Yes

Lamp version 3S

Number of gear units 1 unit

Number of light sources 1 pc

Optic type Distribution medium

Product Family Code BGP340

Initial Performance (IEC Compliant)

Init. Corr. Color Temperature 4000 K

Init. Color Rendering Index ≥70

Light Technical

Standard tilt angle side entry 0°

Standard tilt angle posttop 0°

Upward light output ratio 0

Mechanical and Housing

Color Aluminum and gray

Application Conditions

Order Code	Full Product Name	Maximum dim level
910925438542	BGP340 LED37--3S/740 PSU I DM 48/60	-
910925438543	BGP340 LED55--3S/740 PSU I DM 48/60	-
910925438544	BGP340 LED74--3S/740 PSU I DM 48/60	-
910925438545	BGP340 LED92--3S/740 PSU I DM 48/60	-
910925438546	BGP340 LED110--3S/740 PSU I DM 48/60	-
910925438547	BGP340 LED37--3S/740 PSU II DM 48/60	-
910925438548	BGP340 LED55--3S/740 PSU II DM 48/60	-
910925438549	BGP340 LED74--3S/740 PSU II DM 48/60	-
910925438550	BGP340 LED92--3S/740 PSU II DM 48/60	-
910925438551	BGP340 LED110--3S/740 PSU II DM 48/60	-
910925438570	BGP340 LED92--3S/740 PSR I DM DDF1 48/60	10%
910925438571	BGP340 LED110--3S/740 PSR I DM DDF1 48/6	10%
910925438572	BGP340 LED37--3S/740 PSR II DM DDF1 48/6	10%
910925438573	BGP340 LED55--3S/740 PSR II DM DDF1 48/6	10%
910925438574	BGP340 LED74--3S/740 PSR II DM DDF1 48/6	10%
910925438575	BGP340 LED92--3S/740 PSR II DM DDF1 48/6	10%
910925438576	BGP340 LED110--3S/740 PSR II DM DDF1 48/	10%
910925438577	BGP340 LED37--3S/740 PSR I DM DDF2 48/60	10%
910925438578	BGP340 LED55--3S/740 PSR I DM DDF2 48/60	10%
910925438579	BGP340 LED74--3S/740 PSR I DM DDF2 48/60	10%
910925438580	BGP340 LED92--3S/740 PSR I DM DDF2 48/60	10%
910925438581	BGP340 LED110--3S/740 PSR I DM DDF2 48/6	10%
910925438582	BGP340 LED37--3S/740 PSR II DM DDF2 48/6	10%
910925438583	BGP340 LED55--3S/740 PSR II DM DDF2 48/6	10%
910925438584	BGP340 LED74--3S/740 PSR II DM DDF2 48/6	10%
910925438585	BGP340 LED92--3S/740 PSR II DM DDF2 48/6	10%
910925438586	BGP340 LED110--3S/740 PSR II DM DDF2 48/	10%
910925438588	BGP340 LED55--3S/740 PSR I DM DDF3 48/60	10%
910925438591	BGP340 LED110--3S/740 PSR I DM DDF3 48/6	10%
910925438594	BGP340 LED74--3S/740 PSR II DM DDF3 48/6	10%
910925438595	BGP340 LED92--3S/740 PSR II DM DDF3 48/6	10%
910925438596	BGP340 LED110--3S/740 PSR II DM DDF3 48/	10%
910925438611	BGP340 LED37--3S/740 PSU II DM MSP 48/60	-
910925438612	BGP340 LED55--3S/740 PSU II DM MSP 48/60	-
910925438615	BGP340 LED110--3S/740 PSU II DM MSP 48/6	-
910925438616	BGP340 LED37--3S/740 PSR II DM LS-8 48/6	10%
910925438617	BGP340 LED55--3S/740 PSR II DM LS-8 48/6	10%

Order Code	Full Product Name	Maximum dim level
910925438618	BGP340 LED74--3S/740 PSR II DM LS-8 48/6	10%
910925438619	BGP340 LED92--3S/740 PSR II DM LS-8 48/6	10%
910925438620	BGP340 LED110--3S/740 PSR II DM LS-8 48/	10%
910925439106	BGP340 LED42--3S/740 II CLO-DDF2 SRG 48/	10%
910925439107	BGP340 LED55--3S/740 II CLO-DDF2 SRG 48/	10%
910925439109	BGP340 LED92--3S/740 II CLO-DDF2 SRG 48/	10%
910925439110	BGP340 LED110--3S/740 II CLO-DDF2 SRG 48	10%

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/ Differential)
910925438542	BGP340 LED37--3S/740 PSU I DM 48/60	6/4 kV
910925438543	BGP340 LED55--3S/740 PSU I DM 48/60	6/4 kV
910925438544	BGP340 LED74--3S/740 PSU I DM 48/60	6/4 kV
910925438545	BGP340 LED92--3S/740 PSU I DM 48/60	6/4 kV
910925438546	BGP340 LED110--3S/740 PSU I DM 48/60	6/4 kV
910925438547	BGP340 LED37--3S/740 PSU II DM 48/60	6/4 kV
910925438548	BGP340 LED55--3S/740 PSU II DM 48/60	6/4 kV
910925438549	BGP340 LED74--3S/740 PSU II DM 48/60	6/4 kV
910925438550	BGP340 LED92--3S/740 PSU II DM 48/60	6/4 kV
910925438551	BGP340 LED110--3S/740 PSU II DM 48/60	6/4 kV
910925438570	BGP340 LED92--3S/740 PSR I DM DDF1 48/60	6/4 kV
910925438571	BGP340 LED110--3S/740 PSR I DM DDF1 48/6	6/4 kV
910925438572	BGP340 LED37--3S/740 PSR II DM DDF1 48/6	6/4 kV
910925438573	BGP340 LED55--3S/740 PSR II DM DDF1 48/6	6/4 kV
910925438574	BGP340 LED74--3S/740 PSR II DM DDF1 48/6	6/4 kV
910925438575	BGP340 LED92--3S/740 PSR II DM DDF1 48/6	6/4 kV
910925438576	BGP340 LED110--3S/740 PSR II DM DDF1 48/	6/4 kV
910925438577	BGP340 LED37--3S/740 PSR I DM DDF2 48/60	6/4 kV
910925438578	BGP340 LED55--3S/740 PSR I DM DDF2 48/60	6/4 kV
910925438579	BGP340 LED74--3S/740 PSR I DM DDF2 48/60	6/4 kV
910925438580	BGP340 LED92--3S/740 PSR I DM DDF2 48/60	6/4 kV
910925438581	BGP340 LED110--3S/740 PSR I DM DDF2 48/6	6/4 kV
910925438582	BGP340 LED37--3S/740 PSR II DM DDF2 48/6	6/4 kV
910925438583	BGP340 LED55--3S/740 PSR II DM DDF2 48/6	6/4 kV

Order Code	Full Product Name	Surge Protection (Common/ Differential)
910925438584	BGP340 LED74--3S/740 PSR II DM DDF2 48/6	6/4 kV
910925438585	BGP340 LED92--3S/740 PSR II DM DDF2 48/6	6/4 kV
910925438586	BGP340 LED110--3S/740 PSR II DM DDF2 48/	6/4 kV
910925438588	BGP340 LED55--3S/740 PSR I DM DDF3 48/60	6/4 kV
910925438591	BGP340 LED110--3S/740 PSR I DM DDF3 48/6	6/4 kV
910925438594	BGP340 LED74--3S/740 PSR II DM DDF3 48/6	6/4 kV
910925438595	BGP340 LED92--3S/740 PSR II DM DDF3 48/6	6/4 kV
910925438596	BGP340 LED110--3S/740 PSR II DM DDF3 48/	6/4 kV
910925438611	BGP340 LED37--3S/740 PSU II DM MSP 48/60	6/4 kV
910925438612	BGP340 LED55--3S/740 PSU II DM MSP 48/60	6/4 kV
910925438615	BGP340 LED110--3S/740 PSU II DM MSP 48/6	6/4 kV
910925438616	BGP340 LED37--3S/740 PSR II DM LS-8 48/6	6/4 kV
910925438617	BGP340 LED55--3S/740 PSR II DM LS-8 48/6	6/4 kV
910925438618	BGP340 LED74--3S/740 PSR II DM LS-8 48/6	6/4 kV
910925438619	BGP340 LED92--3S/740 PSR II DM LS-8 48/6	6/4 kV
910925438620	BGP340 LED110--3S/740 PSR II DM LS-8 48/	6/4 kV
910925439106	BGP340 LED42--3S/740 II CLO-DDF2 SRG 48/	Philips standard surge protection level
910925439107	BGP340 LED55--3S/740 II CLO-DDF2 SRG 48/	Philips standard surge protection level
910925439109	BGP340 LED92--3S/740 II CLO-DDF2 SRG 48/	Philips standard surge protection level
910925439110	BGP340 LED110--3S/740 II CLO-DDF2 SRG 48	Philips standard surge protection level

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925438542	BGP340 LED37--3S/740 PSU I DM 48/60	No
910925438543	BGP340 LED55--3S/740 PSU I DM 48/60	No
910925438544	BGP340 LED74--3S/740 PSU I DM 48/60	No
910925438545	BGP340 LED92--3S/740 PSU I DM 48/60	No
910925438546	BGP340 LED110--3S/740 PSU I DM 48/60	No
910925438547	BGP340 LED37--3S/740 PSU II DM 48/60	No
910925438548	BGP340 LED55--3S/740 PSU II DM 48/60	No
910925438549	BGP340 LED74--3S/740 PSU II DM 48/60	No

Order Code	Full Product Name	Dimmable
910925438550	BGP340 LED92--3S/740 PSU II DM 48/60	No
910925438551	BGP340 LED110--3S/740 PSU II DM 48/60	No
910925438570	BGP340 LED92--3S/740 PSR I DM DDF1 48/60	Yes
910925438571	BGP340 LED110--3S/740 PSR I DM DDF1 48/6	Yes
910925438572	BGP340 LED37--3S/740 PSR II DM DDF1 48/6	Yes
910925438573	BGP340 LED55--3S/740 PSR II DM DDF1 48/6	Yes
910925438574	BGP340 LED74--3S/740 PSR II DM DDF1 48/6	Yes
910925438575	BGP340 LED92--3S/740 PSR II DM DDF1 48/6	Yes

Selenium LED

Order Code	Full Product Name	Dimmable
910925438576	BGP340 LED110--3S/740 PSR II DM DDF1 48/	Yes
910925438577	BGP340 LED37--3S/740 PSR I DM DDF2 48/60	Yes
910925438578	BGP340 LED55--3S/740 PSR I DM DDF2 48/60	Yes
910925438579	BGP340 LED74--3S/740 PSR I DM DDF2 48/60	Yes
910925438580	BGP340 LED92--3S/740 PSR I DM DDF2 48/60	Yes
910925438581	BGP340 LED110--3S/740 PSR I DM DDF2 48/6	Yes
910925438582	BGP340 LED37--3S/740 PSR II DM DDF2 48/6	Yes
910925438583	BGP340 LED55--3S/740 PSR II DM DDF2 48/6	Yes
910925438584	BGP340 LED74--3S/740 PSR II DM DDF2 48/6	Yes
910925438585	BGP340 LED92--3S/740 PSR II DM DDF2 48/6	Yes
910925438586	BGP340 LED110--3S/740 PSR II DM DDF2 48/	Yes
910925438588	BGP340 LED55--3S/740 PSR I DM DDF3 48/60	Yes
910925438591	BGP340 LED110--3S/740 PSR I DM DDF3 48/6	Yes
910925438594	BGP340 LED74--3S/740 PSR II DM DDF3 48/6	Yes

Order Code	Full Product Name	Dimmable
910925438595	BGP340 LED92--3S/740 PSR II DM DDF3 48/6	Yes
910925438596	BGP340 LED110--3S/740 PSR II DM DDF3 48/	Yes
910925438611	BGP340 LED37--3S/740 PSU II DM MSP 48/60	No
910925438612	BGP340 LED55--3S/740 PSU II DM MSP 48/60	No
910925438615	BGP340 LED110--3S/740 PSU II DM MSP 48/6	No
910925438616	BGP340 LED37--3S/740 PSR II DM LS-8 48/6	Yes
910925438617	BGP340 LED55--3S/740 PSR II DM LS-8 48/6	Yes
910925438618	BGP340 LED74--3S/740 PSR II DM LS-8 48/6	Yes
910925438619	BGP340 LED92--3S/740 PSR II DM LS-8 48/6	Yes
910925438620	BGP340 LED110--3S/740 PSR II DM LS-8 48/	Yes
910925439106	BGP340 LED42--3S/740 II CLO-DDF2 SRG 48/	Yes
910925439107	BGP340 LED55--3S/740 II CLO-DDF2 SRG 48/	Yes
910925439109	BGP340 LED92--3S/740 II CLO-DDF2 SRG 48/	Yes
910925439110	BGP340 LED110--3S/740 II CLO-DDF2 SRG 48	Yes

General Information

Order Code	Full Product Name	Coating	Lamp family code
910925438542	BGP340 LED37--3S/740 PSU I DM 48/60	-	LED37
910925438543	BGP340 LED55--3S/740 PSU I DM 48/60	-	LED55
910925438544	BGP340 LED74--3S/740 PSU I DM 48/60	-	LED74
910925438545	BGP340 LED92--3S/740 PSU I DM 48/60	-	LED92
910925438546	BGP340 LED110--3S/740 PSU I DM 48/60	-	LED110
910925438547	BGP340 LED37--3S/740 PSU II DM 48/60	-	LED37
910925438548	BGP340 LED55--3S/740 PSU II DM 48/60	-	LED55
910925438549	BGP340 LED74--3S/740 PSU II DM 48/60	-	LED74
910925438550	BGP340 LED92--3S/740 PSU II DM 48/60	-	LED92
910925438551	BGP340 LED110--3S/740 PSU II DM 48/60	-	LED110
910925438570	BGP340 LED92--3S/740 PSR I DM DDF1 48/60	-	LED92
910925438571	BGP340 LED110--3S/740 PSR I DM DDF1 48/6	-	LED110
910925438572	BGP340 LED37--3S/740 PSR II DM DDF1 48/6	-	LED37
910925438573	BGP340 LED55--3S/740 PSR II DM DDF1 48/6	-	LED55
910925438574	BGP340 LED74--3S/740 PSR II DM DDF1 48/6	-	LED74
910925438575	BGP340 LED92--3S/740 PSR II DM DDF1 48/6	-	LED92
910925438576	BGP340 LED110--3S/740 PSR II DM DDF1 48/	-	LED110
910925438577	BGP340 LED37--3S/740 PSR I DM DDF2 48/60	-	LED37
910925438578	BGP340 LED55--3S/740 PSR I DM DDF2 48/60	-	LED55
910925438579	BGP340 LED74--3S/740 PSR I DM DDF2 48/60	-	LED74
910925438580	BGP340 LED92--3S/740 PSR I DM DDF2 48/60	-	LED92

Order Code	Full Product Name	Coating	Lamp family code
910925438581	BGP340 LED110--3S/740 PSR I DM DDF2 48/6	-	LED110
910925438582	BGP340 LED37--3S/740 PSR II DM DDF2 48/6	-	LED37
910925438583	BGP340 LED55--3S/740 PSR II DM DDF2 48/6	-	LED55
910925438584	BGP340 LED74--3S/740 PSR II DM DDF2 48/6	-	LED74
910925438585	BGP340 LED92--3S/740 PSR II DM DDF2 48/6	-	LED92
910925438586	BGP340 LED110--3S/740 PSR II DM DDF2 48/	-	LED110
910925438588	BGP340 LED55--3S/740 PSR I DM DDF3 48/60	-	LED55
910925438591	BGP340 LED110--3S/740 PSR I DM DDF3 48/6	-	LED110
910925438594	BGP340 LED74--3S/740 PSR II DM DDF3 48/6	-	LED74
910925438595	BGP340 LED92--3S/740 PSR II DM DDF3 48/6	-	LED92
910925438596	BGP340 LED110--3S/740 PSR II DM DDF3 48/	-	LED110
910925438611	BGP340 LED37--3S/740 PSU II DM MSP 48/60	Marine salt protected coating	LED37
910925438612	BGP340 LED55--3S/740 PSU II DM MSP 48/60	Marine salt protected coating	LED55
910925438615	BGP340 LED110--3S/740 PSU II DM MSP 48/6	Marine salt protected coating	LED110

Selenium LED

Order Code	Full Product Name	Coating	Lamp family code
910925438616	BGP340 LED37--3S/740 PSR II DM LS-8 48/6	-	LED37
910925438617	BGP340 LED55--3S/740 PSR II DM LS-8 48/6	-	LED55
910925438618	BGP340 LED74--3S/740 PSR II DM LS-8 48/6	-	LED74
910925438619	BGP340 LED92--3S/740 PSR II DM LS-8 48/6	-	LED92
910925438620	BGP340 LED110--3S/740 PSR II DM LS-8 48/	-	LED110

Order Code	Full Product Name	Coating	Lamp family code
910925439106	BGP340 LED42--3S/740 II CLO-DDF2 SRG 48/	-	LED42
910925439107	BGP340 LED55--3S/740 II CLO-DDF2 SRG 48/	-	LED55
910925439109	BGP340 LED92--3S/740 II CLO-DDF2 SRG 48/	-	LED92
910925439110	BGP340 LED110--3S/740 II CLO-DDF2 SRG 48	-	LED110

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
910925438542	BGP340 LED37--3S/740 PSU I DM 48/60	3254 lm
910925438543	BGP340 LED55--3S/740 PSU I DM 48/60	4792 lm
910925438544	BGP340 LED74--3S/740 PSU I DM 48/60	6407 lm
910925438545	BGP340 LED92--3S/740 PSU I DM 48/60	7906 lm
910925438546	BGP340 LED110--3S/740 PSU I DM 48/60	9381 lm
910925438547	BGP340 LED37--3S/740 PSU II DM 48/60	3254 lm
910925438548	BGP340 LED55--3S/740 PSU II DM 48/60	4792 lm
910925438549	BGP340 LED74--3S/740 PSU II DM 48/60	6407 lm
910925438550	BGP340 LED92--3S/740 PSU II DM 48/60	7906 lm
910925438551	BGP340 LED110--3S/740 PSU II DM 48/60	9381 lm
910925438570	BGP340 LED92--3S/740 PSR I DM DDF1 48/60	7906 lm
910925438571	BGP340 LED110--3S/740 PSR I DM DDF1 48/6	9381 lm
910925438572	BGP340 LED37--3S/740 PSR II DM DDF1 48/6	3254 lm
910925438573	BGP340 LED55--3S/740 PSR II DM DDF1 48/6	4792 lm
910925438574	BGP340 LED74--3S/740 PSR II DM DDF1 48/6	6407 lm
910925438575	BGP340 LED92--3S/740 PSR II DM DDF1 48/6	7906 lm
910925438576	BGP340 LED110--3S/740 PSR II DM DDF1 48/	9381 lm
910925438577	BGP340 LED37--3S/740 PSR I DM DDF2 48/60	3254 lm
910925438578	BGP340 LED55--3S/740 PSR I DM DDF2 48/60	4792 lm
910925438579	BGP340 LED74--3S/740 PSR I DM DDF2 48/60	6407 lm
910925438580	BGP340 LED92--3S/740 PSR I DM DDF2 48/60	7906 lm
910925438581	BGP340 LED110--3S/740 PSR I DM DDF2 48/6	9381 lm

Order Code	Full Product Name	Initial luminous flux
910925438582	BGP340 LED37--3S/740 PSR II DM DDF2 48/6	3254 lm
910925438583	BGP340 LED55--3S/740 PSR II DM DDF2 48/6	4792 lm
910925438584	BGP340 LED74--3S/740 PSR II DM DDF2 48/6	6407 lm
910925438585	BGP340 LED92--3S/740 PSR II DM DDF2 48/6	7906 lm
910925438586	BGP340 LED110--3S/740 PSR II DM DDF2 48/	9381 lm
910925438588	BGP340 LED55--3S/740 PSR I DM DDF3 48/60	4792 lm
910925438591	BGP340 LED110--3S/740 PSR I DM DDF3 48/6	9381 lm
910925438594	BGP340 LED74--3S/740 PSR II DM DDF3 48/6	6407 lm
910925438595	BGP340 LED92--3S/740 PSR II DM DDF3 48/6	7906 lm
910925438596	BGP340 LED110--3S/740 PSR II DM DDF3 48/	9381 lm
910925438611	BGP340 LED37--3S/740 PSU II DM MSP 48/60	3254 lm
910925438612	BGP340 LED55--3S/740 PSU II DM MSP 48/60	4792 lm
910925438615	BGP340 LED110--3S/740 PSU II DM MSP 48/6	9381 lm
910925438616	BGP340 LED37--3S/740 PSR II DM LS-8 48/6	3254 lm
910925438617	BGP340 LED55--3S/740 PSR II DM LS-8 48/6	4792 lm
910925438618	BGP340 LED74--3S/740 PSR II DM LS-8 48/6	6407 lm
910925438619	BGP340 LED92--3S/740 PSR II DM LS-8 48/6	7906 lm
910925438620	BGP340 LED110--3S/740 PSR II DM LS-8 48/	9381 lm
910925439106	BGP340 LED42--3S/740 II CLO-DDF2 SRG 48/	3681 lm
910925439107	BGP340 LED55--3S/740 II CLO-DDF2 SRG 48/	4792 lm
910925439109	BGP340 LED92--3S/740 II CLO-DDF2 SRG 48/	7906 lm
910925439110	BGP340 LED110--3S/740 II CLO-DDF2 SRG 48	9381 lm

