



# MileWide<sup>2</sup> – design meets efficiency

## MileWide<sup>2</sup> Large

Many municipal authorities are embracing the benefits of contemporary outdoor lighting. These include a more attractive urban environment and increased comfort, safety and security for the public. Not to mention the positive impact on environmental protection and city branding. Together with Holscher Design, Philips has developed MileWide<sup>2</sup>, the successor to the highly popular MileWide family. Featuring a range of dedicated masts and brackets, the pure, clean design of MileWide<sup>2</sup> integrates perfectly with today's and tomorrow's cityscape. With its high-quality finish and high level of lighting performance, MileWide<sup>2</sup> is suitable for a wide range of applications, ranging from traffic roads to city centers. Multi-layer optics provide a uniform light distribution and reduced glare, enabling direct replacement of HID solutions without compromising on spacing, mounting height or light quality.

### Benefits

- Consistency and continuity of family design
- Complete solution with dedicated masts and brackets
- Significant energy savings (up to 80% compared to HPL) without compromising on quality of light

### Features

- Dedicated total solution based on clean-design, high-finish MileWide family
- Designed for LED – no compromise
- Exceptionally high performance and good glare control
- Different optics available – suitable for a wide range of applications
- "Plug-and-play"

## MileWide<sup>2</sup> Large

### Application

- Residential streets
- Walking, cycling and running paths
- Main roads
- Motorways
- Car parks

