

**PHILIPS**

**Lighting**



# The optimized TCO solution for general areas and recreational sports projects

## ClearFlood

ClearFlood is a range of floodlights that enables you to choose the exact lumen rating that you need for your specific application. Designed around state-of-the-art LEDs and extremely high-efficiency optics, this very competitive solution offers an industry-leading lux per euro ratio and significant energy savings. The choice of different optics in the ClearFlood range opens new application possibilities for LEDs. ClearFlood BVP650 is also easy to install and to maintain.

### Benefits

- Optimized total cost of ownership
- Balances initial investment and operational costs
- Easy to install and maintain
- Long lasting


### Features

- All Ledgine O platform light distributions sports fields, transportation areas and car parks)
- Lumen packages up to 40klm, total system efficacy up to 163lm/W
- Toolless access to both light engine and drivers
- Signify Service tag (unique QR identification) for maintenance, installation and spare part information
- Extremely long lifetime up to 100,000 hours L98
- Integrated surge protection (optional extra surge protection device)
- High impact resistance IK09, IP66. Seaside resistant treatment and swimming pool protection options.

## Application


- Harbors, airports, parking lots, logistic hubs, industrial areas
- Outdoor recreational sports fields, like tennis courts, etc
- Indoor multipurpose gymnasiums and swimming pool

## Dimensional drawing



## Product details

ClearFlood-BVP650-DP.tif



## Product details



OPDP\_BVP650i\_0011-Detail  
photo

General Information (1/2)					
Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
912300023506	BVP650 LED80-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
	ALU				
912300023507	BVP650 LED100-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED100	1 unit
	ALU				
912300023508	BVP650 LED120-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED120	1 unit
	ALU				
912300023509	BVP650 LED140-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED140	2 units
	ALU				
912300023510	BVP650 LED160-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED160	2 units
	ALU				
912300023511	BVP650 LED180-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED180	2 units
	ALU				
912300023512	BVP650 LED200-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
	S ALU				
912300023513	BVP650 LED220-4S/740 PSU S	EB	Temperature 960 °C, duration 5 s	LED220	2 units
	ALU				
912300023514	BVP650 LED240-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
	S ALU				
912300023515	BVP650 LED260-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED260	2 units
	S ALU				
912300023516	BVP650 LED280-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED280	2 units
	S ALU				
912300023517	BVP650 LED300-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED300	2 units
	S ALU				
912300023518	BVP650 LED320-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED320	2 units
	S ALU				
912300023519	BVP650 LED340-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED340	2 units
	S ALU				
912300023521	BVP650 LED80-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
	OFA52 ALU				
912300023522	BVP650 LED100-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED100	1 unit
	OFA52 ALU				
912300023523	BVP650 LED120-4S/740 PSU	EB	Temperature 960 °C, duration 5 s	LED120	1 unit
	OFA52 ALU				

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
912300023524	BVP650 LED140-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED140	2 units
912300023525	BVP650 LED160-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED160	2 units
912300023526	BVP650 LED180-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED180	2 units
912300023527	BVP650 LED200-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
912300023528	BVP650 LED220-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED220	2 units
912300023529	BVP650 LED240-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
912300023530	BVP650 LED260-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED260	2 units
912300023531	BVP650 LED280-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED280	2 units
912300023532	BVP650 LED300-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED300	2 units
912300023533	BVP650 LED320-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED320	2 units
912300023534	BVP650 LED340-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED340	2 units
912300023536	BVP650 LED80-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
912300023537	BVP650 LED100-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED100	1 unit
912300023538	BVP650 LED120-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED120	1 unit
912300023539	BVP650 LED140-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED140	2 units
912300023540	BVP650 LED160-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED160	2 units
912300023541	BVP650 LED180-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED180	2 units
912300023542	BVP650 LED200-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
912300023543	BVP650 LED220-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED220	2 units
912300023544	BVP650 LED240-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
912300023545	BVP650 LED260-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED260	2 units
912300023546	BVP650 LED280-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED280	2 units
912300023547	BVP650 LED300-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED300	2 units
912300023548	BVP650 LED320-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED320	2 units
912300023549	BVP650 LED340-4S/740 PSU DX50 ALU	EB	Temperature 960 °C, duration 5 s	LED340	2 units

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
912300023551	BVP650 LED80-4S/740 PSU DW10 ALU	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
912300023557	BVP650 LED200-4S/740 PSU DW10 ALU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
912300023559	BVP650 LED240-4S/740 PSU DW10 ALU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
912300023564	BVP650 LED340-4S/740 PSU DW10 ALU	EB	Temperature 960 °C, duration 5 s	LED340	2 units
912300023566	BVP650 LED80-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
912300023568	BVP650 LED120-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED120	1 unit
912300023570	BVP650 LED160-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED160	2 units
912300023571	BVP650 LED180-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED180	2 units
912300023572	BVP650 LED200-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
912300023573	BVP650 LED220-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED220	2 units
912300023574	BVP650 LED240-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
912300023575	BVP650 LED260-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED260	2 units
912300023576	BVP650 LED280-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED280	2 units
912300023577	BVP650 LED300-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED300	2 units
912300023578	BVP650 LED320-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED320	2 units
912300023579	BVP650 LED340-4S/740 PSU DX10 ALU	EB	Temperature 960 °C, duration 5 s	LED340	2 units
912300023581	BVP650 LED80-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED80	1 unit
912300023582	BVP650 LED100-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED100	1 unit
912300023583	BVP650 LED120-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED120	1 unit
912300023584	BVP650 LED140-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED140	2 units
912300023586	BVP650 LED180-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED180	2 units
912300023587	BVP650 LED200-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED200	2 units
912300023588	BVP650 LED220-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED220	2 units
912300023589	BVP650 LED240-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED240	2 units
912300023593	BVP650 LED320-4S/740 PSU DM10 ALU	EB	Temperature 960 °C, duration 5 s	LED320	2 units

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
912300023684	BVP650 LED360-4S/740 S ALU PSU	EB	Temperature 960 °C, duration 5 s	LED360	2 units
912300023685	BVP650 LED380-4S/740 S ALU PSU	EB	Temperature 960 °C, duration 5 s	LED380	2 units
912300023686	BVP650 LED400-4S/740 S ALU PSU	EB	Temperature 960 °C, duration 5 s	LED400	2 units
912300023687	BVP650 LED360-4S/740 OFA52 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED360	2 units
912300023688	BVP650 LED380-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED380	2 units
912300023689	BVP650 LED400-4S/740 PSU OFA52 ALU	EB	Temperature 960 °C, duration 5 s	LED400	2 units
912300023690	BVP650 LED360-4S/740 DX50 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED360	2 units
912300023691	BVP650 LED380-4S/740 DX50 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED380	2 units
912300023692	BVP650 LED400-4S/740 DX50 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED400	2 units
912300023696	BVP650 LED360-4S/740 DX10 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED360	2 units
912300023697	BVP650 LED380-4S/740 DX10 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED380	2 units
912300023698	BVP650 LED400-4S/740 DX10 ALU PSU	EB	Temperature 960 °C, duration 5 s	LED400	2 units
912300023947	BVP650 LED420-4S/740 S ALU PSU	-	-	LED420	2 units
912300023948	BVP650 LED420-4S/740 OFA52 ALU PSU	-	-	LED420	2 units
912300023949	BVP650 LED420-4S/740 DX50 ALU PSU	-	-	LED420	2 units
912300023950	BVP650 LED420-4S/740 DX51 ALU PSU	-	-	LED420	2 units
912300023951	BVP650 LED420-4S/740 DX10 ALU PSU	-	-	LED420	2 units
912300023954	BVP650 LED440-4S/740 S ALU PSU	-	-	LED440	2 units
912300023955	BVP650 LED440-4S/740 OFA52 ALU PSU	-	-	LED440	2 units
912300023956	BVP650 LED440-4S/740 DX50 ALU PSU	-	-	LED440	2 units
912300023957	BVP650 LED440-4S/740 DX51 ALU PSU	-	-	LED440	2 units
912300023958	BVP650 LED440-4S/740 DX10 ALU PSU	-	-	LED440	2 units
912300023959	BVP650 LED440-4S/740 DW10 ALU PSU	-	-	LED440	2 units
912300023994	BVP650 LED360-4S/740 DX60 ALU PSU	-	-	LED360	2 units
912300023995	BVP650 LED380-4S/740 DX60 ALU PSU	-	-	LED380	2 units

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Number of gear units
912300023996	BVP650 LED400-4S/740 DX60 ALU PSU	-	-	LED400	2 units
912300023997	BVP650 LED420-4S/740 DX60 ALU PSU	-	-	LED420	2 units
912300023998	BVP650 LED440-4S/740 DX60 ALU PSU	-	-	LED440	2 units
912300024729	BVP650 T35 1xLED380-4S/740 OFA52 D9	-	-	LED380	2 units

### General Information (2/2)

Order Code	Full Product Name	Service tag	Order Code	Full Product Name	Service tag
912300023506	BVP650 LED80-4S/740 PSU S ALU	Yes	912300023546	BVP650 LED280-4S/740 PSU DX50 ALU	-
912300023507	BVP650 LED100-4S/740 PSU S ALU	-	912300023547	BVP650 LED300-4S/740 PSU DX50 ALU	-
912300023508	BVP650 LED120-4S/740 PSU S ALU	-	912300023548	BVP650 LED320-4S/740 PSU DX50 ALU	-
912300023509	BVP650 LED140-4S/740 PSU S ALU	-	912300023549	BVP650 LED340-4S/740 PSU DX50 ALU	-
912300023510	BVP650 LED160-4S/740 PSU S ALU	-	912300023551	BVP650 LED80-4S/740 PSU DW10 ALU	-
912300023511	BVP650 LED180-4S/740 PSU S ALU	-	912300023557	BVP650 LED200-4S/740 PSU DW10 ALU	-
912300023512	BVP650 LED200-4S/740 PSU S ALU	-	912300023559	BVP650 LED240-4S/740 PSU DW10 ALU	-
912300023513	BVP650 LED220-4S/740 PSU S ALU	-	912300023564	BVP650 LED340-4S/740 PSU DW10 ALU	-
912300023514	BVP650 LED240-4S/740 PSU S ALU	-	912300023566	BVP650 LED80-4S/740 PSU DX10 ALU	-
912300023515	BVP650 LED260-4S/740 PSU S ALU	-	912300023568	BVP650 LED120-4S/740 PSU DX10 ALU	-
912300023516	BVP650 LED280-4S/740 PSU S ALU	-	912300023570	BVP650 LED160-4S/740 PSU DX10 ALU	-
912300023517	BVP650 LED300-4S/740 PSU S ALU	-	912300023571	BVP650 LED180-4S/740 PSU DX10 ALU	-
912300023518	BVP650 LED320-4S/740 PSU S ALU	-	912300023572	BVP650 LED200-4S/740 PSU DX10 ALU	-
912300023519	BVP650 LED340-4S/740 PSU S ALU	-	912300023573	BVP650 LED220-4S/740 PSU DX10 ALU	-
912300023521	BVP650 LED80-4S/740 PSU OFA52 ALU	-	912300023574	BVP650 LED240-4S/740 PSU DX10 ALU	-
912300023522	BVP650 LED100-4S/740 PSU OFA52 ALU	-	912300023575	BVP650 LED260-4S/740 PSU DX10 ALU	-
912300023523	BVP650 LED120-4S/740 PSU OFA52 ALU	-	912300023576	BVP650 LED280-4S/740 PSU DX10 ALU	-
912300023524	BVP650 LED140-4S/740 PSU OFA52 ALU	-	912300023577	BVP650 LED300-4S/740 PSU DX10 ALU	-
912300023525	BVP650 LED160-4S/740 PSU OFA52 ALU	-	912300023578	BVP650 LED320-4S/740 PSU DX10 ALU	-
912300023526	BVP650 LED180-4S/740 PSU OFA52 ALU	-	912300023579	BVP650 LED340-4S/740 PSU DX10 ALU	-
912300023527	BVP650 LED200-4S/740 PSU OFA52 ALU	-	912300023581	BVP650 LED80-4S/740 PSU DM10 ALU	-
912300023528	BVP650 LED220-4S/740 PSU OFA52 ALU	-	912300023582	BVP650 LED100-4S/740 PSU DM10 ALU	-
912300023529	BVP650 LED240-4S/740 PSU OFA52 ALU	-	912300023583	BVP650 LED120-4S/740 PSU DM10 ALU	-
912300023530	BVP650 LED260-4S/740 PSU OFA52 ALU	-	912300023584	BVP650 LED140-4S/740 PSU DM10 ALU	-
912300023531	BVP650 LED280-4S/740 PSU OFA52 ALU	-	912300023586	BVP650 LED180-4S/740 PSU DM10 ALU	-
912300023532	BVP650 LED300-4S/740 PSU OFA52 ALU	-	912300023587	BVP650 LED200-4S/740 PSU DM10 ALU	-
912300023533	BVP650 LED320-4S/740 PSU OFA52 ALU	-	912300023588	BVP650 LED220-4S/740 PSU DM10 ALU	-
912300023534	BVP650 LED340-4S/740 PSU OFA52 ALU	-	912300023589	BVP650 LED240-4S/740 PSU DM10 ALU	-
912300023536	BVP650 LED80-4S/740 PSU DX50 ALU	-	912300023593	BVP650 LED320-4S/740 PSU DM10 ALU	-
912300023537	BVP650 LED100-4S/740 PSU DX50 ALU	-	912300023684	BVP650 LED360-4S/740 S ALU PSU	-
912300023538	BVP650 LED120-4S/740 PSU DX50 ALU	-	912300023685	BVP650 LED380-4S/740 S ALU PSU	-
912300023539	BVP650 LED140-4S/740 PSU DX50 ALU	-	912300023686	BVP650 LED400-4S/740 S ALU PSU	-
912300023540	BVP650 LED160-4S/740 PSU DX50 ALU	-	912300023687	BVP650 LED360-4S/740 OFA52 ALU PSU	-
912300023541	BVP650 LED180-4S/740 PSU DX50 ALU	-	912300023688	BVP650 LED380-4S/740 PSU OFA52 ALU	-
912300023542	BVP650 LED200-4S/740 PSU DX50 ALU	-	912300023689	BVP650 LED400-4S/740 PSU OFA52 ALU	-
912300023543	BVP650 LED220-4S/740 PSU DX50 ALU	-	912300023690	BVP650 LED360-4S/740 DX50 ALU PSU	-
912300023544	BVP650 LED240-4S/740 PSU DX50 ALU	-	912300023691	BVP650 LED380-4S/740 DX50 ALU PSU	-
912300023545	BVP650 LED260-4S/740 PSU DX50 ALU	-	912300023692	BVP650 LED400-4S/740 DX50 ALU PSU	-

Order Code	Full Product Name	Service tag
912300023696	BVP650 LED360-4S/740 DX10 ALU PSU	-
912300023697	BVP650 LED380-4S/740 DX10 ALU PSU	-
912300023698	BVP650 LED400-4S/740 DX10 ALU PSU	-
912300023947	BVP650 LED420-4S/740 S ALU PSU	-
912300023948	BVP650 LED420-4S/740 OFA52 ALU PSU	-
912300023949	BVP650 LED420-4S/740 DX50 ALU PSU	-
912300023950	BVP650 LED420-4S/740 DX51 ALU PSU	-
912300023951	BVP650 LED420-4S/740 DX10 ALU PSU	-
912300023954	BVP650 LED440-4S/740 S ALU PSU	-
912300023955	BVP650 LED440-4S/740 OFA52 ALU PSU	-

Order Code	Full Product Name	Service tag
912300023956	BVP650 LED440-4S/740 DX50 ALU PSU	-
912300023957	BVP650 LED440-4S/740 DX51 ALU PSU	-
912300023958	BVP650 LED440-4S/740 DX10 ALU PSU	-
912300023959	BVP650 LED440-4S/740 DW10 ALU PSU	-
912300023994	BVP650 LED360-4S/740 DX60 ALU PSU	-
912300023995	BVP650 LED380-4S/740 DX60 ALU PSU	-
912300023996	BVP650 LED400-4S/740 DX60 ALU PSU	-
912300023997	BVP650 LED420-4S/740 DX60 ALU PSU	-
912300023998	BVP650 LED440-4S/740 DX60 ALU PSU	-
912300024729	BVP650 T35 1xLED380-4S/740 OFA52 D9	-

## Light Technical

Order Code	Name	Luminaire		Number		Optic type
		Full Product	light beam spread	Luminous Flux	of light sources	
912300023506	BVP650	72° x 22°	7,200 lm	48	Symmetrical	
	LED80-4S/740					
	PSU S ALU					
912300023507	BVP650	72° x 22°	8,800 lm	64	Symmetrical	
	LED100-4S/740					
	PSU S ALU					
912300023508	BVP650	72° x 22°	10,500 lm	64	Symmetrical	
	LED120-4S/740					
	PSU S ALU					
912300023509	BVP650	140° x 70°	12,500 lm	82	Symmetrical	
	LED140-4S/740					
	PSU S ALU					
912300023510	BVP650	140° x 70°	14,000 lm	82	Symmetrical	
	LED160-4S/740					
	PSU S ALU					
912300023511	BVP650	130° x 97°	16,000 lm	82	Symmetrical	
	LED180-4S/740					
	PSU S ALU					
912300023512	BVP650	130° x 97°	17,500 lm	82	Symmetrical	
	LED200-4S/740					
	PSU S ALU					
912300023513	BVP650	108° x 113°	19,500 lm	82	Symmetrical	
	LED220-4S/740					
	PSU S ALU					
912300023514	BVP650	108° x 113°	21,000 lm	120	Symmetrical	
	LED240-4S/740					
	PSU S ALU					
912300023515	BVP650	86° x 188°	23,000 lm	120	Symmetrical	
	LED260-4S/740					
	PSU S ALU					
912300023516	BVP650	86° x 188°	24,000 lm	120	Symmetrical	
	LED280-4S/740					
	PSU S ALU					
912300023517	BVP650	88° x 187°	26,000 lm	120	Symmetrical	
	LED300-4S/740					
	PSU S ALU					

Order Code	Name	Luminaire		Number		Optic type
		Full Product	light beam spread	Luminous Flux	of light sources	
912300023518	BVP650	88° x 187°	28,000 lm	120	Symmetrical	
	LED320-4S/740					
	PSU S ALU					
912300023519	BVP650	72° x 22°	29,000 lm	120	Symmetrical	
	LED340-4S/740					
	PSU S ALU					
912300023521	BVP650	72° x 22°	7,000 lm	48	Optiflux	
	LED80-4S/740					
	PSU OFA52 ALU					
912300023522	BVP650	88° x 157°	8,800 lm	64	Optiflux	
	LED100-4S/740					
	PSU OFA52 ALU					
912300023523	BVP650	88° x 157°	10,500 lm	64	Optiflux	
	LED120-4S/740					
	PSU OFA52 ALU					
912300023524	BVP650	140° x 70°	12,500 lm	82	Optiflux	
	LED140-4S/740					
	PSU OFA52 ALU					
912300023525	BVP650	140° x 70°	14,000 lm	82	Optiflux	
	LED160-4S/740					
	PSU OFA52 ALU					
912300023526	BVP650	130° x 97°	15,500 lm	82	Optiflux	
	LED180-4S/740					
	PSU OFA52 ALU					
912300023527	BVP650	130° x 97°	17,500 lm	82	Optiflux	
	LED200-4S/740					
	PSU OFA52 ALU					
912300023528	BVP650	108° x 113°	19,000 lm	82	Optiflux	
	LED220-4S/740					
	PSU OFA52 ALU					
912300023529	BVP650	108° x 113°	21,000 lm	120	Optiflux	
	LED240-4S/740					
	PSU OFA52 ALU					
912300023530	BVP650	86° x 188°	23,000 lm	120	Optiflux	
	LED260-4S/740					
	PSU OFA52 ALU					

Order Code	Full Product Name	Luminaire		Number	
		light beam spread	Luminous Flux	of light sources	Optic type outdoor
912300023531	BVP650	86° x 188°	24,000 lm	120	Optiflux
	LED280-4S/740				asymmetrical
	PSU OFA52 ALU				axis angle 52°
912300023532	BVP650	88° x 187°	26,000 lm	120	Optiflux
	LED300-4S/740				asymmetrical
	PSU OFA52 ALU				axis angle 52°
912300023533	BVP650	88° x 187°	28,000 lm	120	Optiflux
	LED320-4S/740				asymmetrical
	PSU OFA52 ALU				axis angle 52°
912300023534	BVP650	72° x 22°	29,000 lm	120	Optiflux
	LED340-4S/740				asymmetrical
	PSU OFA52 ALU				axis angle 52°
912300023536	BVP650	72° x 22°	6,800 lm	48	Distribution
	LED80-4S/740				extra wide 50
	PSU DX50 ALU				
912300023537	BVP650	86° x 188°	8,400 lm	64	Distribution
	LED100-4S/740				extra wide 50
	PSU DX50 ALU				
912300023538	BVP650	86° x 188°	10,000 lm	64	Distribution
	LED120-4S/740				extra wide 50
	PSU DX50 ALU				
912300023539	BVP650	140° x 70°	12,000 lm	82	Distribution
	LED140-4S/740				extra wide 50
	PSU DX50 ALU				
912300023540	BVP650	140° x 70°	13,500 lm	82	Distribution
	LED160-4S/740				extra wide 50
	PSU DX50 ALU				
912300023541	BVP650	130° x 97°	15,000 lm	82	Distribution
	LED180-4S/740				extra wide 50
	PSU DX50 ALU				
912300023542	BVP650	130° x 97°	17,000 lm	82	Distribution
	LED200-4S/740				extra wide 50
	PSU DX50 ALU				
912300023543	BVP650	108° x 113°	18,500 lm	82	Distribution
	LED220-4S/740				extra wide 50
	PSU DX50 ALU				
912300023544	BVP650	108° x 113°	20,000 lm	120	Distribution
	LED240-4S/740				extra wide 50
	PSU DX50 ALU				
912300023545	BVP650	86° x 188°	22,000 lm	120	Distribution
	LED260-4S/740				extra wide 50
	PSU DX50 ALU				
912300023546	BVP650	86° x 188°	23,000 lm	120	Distribution
	LED280-4S/740				extra wide 50
	PSU DX50 ALU				
912300023547	BVP650	88° x 187°	25,000 lm	120	Distribution
	LED300-4S/740				extra wide 50
	PSU DX50 ALU				

Order Code	Full Product Name	Luminaire		Number	
		light beam spread	Luminous Flux	of light sources	Optic type outdoor
912300023548	BVP650	88° x 187°	27,000 lm	120	Distribution extra wide 50
	LED320-4S/740				
	PSU DX50 ALU				
912300023549	BVP650	72° x 22°	28,000 lm	120	Distribution extra wide 50
	LED340-4S/740				
	PSU DW10 ALU				
912300023551	BVP650	72° x 22°	7,000 lm	48	Distribution wide 10
	LED80-4S/740				
	PSU DW10 ALU				
912300023557	BVP650	130° x 97°	17,500 lm	82	Distribution wide 10
	LED200-4S/740				
	PSU DW10 ALU				
912300023559	BVP650	108° x 113°	21,000 lm	120	Distribution wide 10
	LED240-4S/740				
	PSU DW10 ALU				
912300023564	BVP650	72° x 22°	29,000 lm	120	Distribution wide 10
	LED340-4S/740				
	PSU DW10 ALU				
912300023566	BVP650	72° x 22°	6,800 lm	48	Distribution extra wide 10
	LED80-4S/740				
	PSU DX10 ALU				
912300023568	BVP650	108° x 113°	10,000 lm	64	Distribution extra wide 10
	LED120-4S/740				
	PSU DX10 ALU				
912300023570	BVP650	140° x 70°	13,500 lm	82	Distribution extra wide 10
	LED160-4S/740				
	PSU DX10 ALU				
912300023571	BVP650	130° x 97°	15,000 lm	82	Distribution extra wide 10
	LED180-4S/740				
	PSU DX10 ALU				
912300023572	BVP650	130° x 97°	16,500 lm	82	Distribution extra wide 10
	LED200-4S/740				
	PSU DX10 ALU				
912300023573	BVP650	108° x 113°	18,500 lm	82	Distribution extra wide 10
	LED220-4S/740				
	PSU DX10 ALU				
912300023574	BVP650	108° x 113°	20,000 lm	120	Distribution extra wide 10
	LED240-4S/740				
	PSU DX10 ALU				
912300023575	BVP650	86° x 188°	22,000 lm	120	Distribution extra wide 10
	LED260-4S/740				
	PSU DX10 ALU				
912300023576	BVP650	86° x 188°	23,000 lm	120	Distribution extra wide 10
	LED280-4S/740				
	PSU DX10 ALU				
912300023577	BVP650	88° x 187°	25,000 lm	120	Distribution extra wide 10
	LED300-4S/740				
	PSU DX10 ALU				

Order Code	Full Product Name	Luminaire		Number		Optic type
		light beam spread	Luminous Flux	of light sources	outdoor	
912300023578	BVP650	88° x 187°	26,000 lm	120	Distribution	Optiflux asymmetrical axis angle 52°
	LED320-4S/740				extra wide 10	
	PSU DX10 ALU					
912300023579	BVP650	72° x 22°	28,000 lm	120	Distribution	Distribution extra wide 50
	LED340-4S/740				extra wide 10	
	PSU DX10 ALU					
912300023581	BVP650	72° x 22°	7,000 lm	48	Distribution	Distribution extra wide 50
	LED80-4S/740				medium 10	
	PSU DM10 ALU					
912300023582	BVP650	140° x 70°	8,800 lm	64	Distribution	Distribution extra wide 50
	LED100-4S/740				medium 10	
	PSU DM10 ALU					
912300023583	BVP650	140° x 70°	10,500 lm	64	Distribution	Distribution extra wide 10
	LED120-4S/740				medium 10	
	PSU DM10 ALU					
912300023584	BVP650	140° x 70°	12,000 lm	82	Distribution	Distribution extra wide 10
	LED140-4S/740				medium 10	
	PSU DM10 ALU					
912300023586	BVP650	130° x 97°	15,500 lm	82	Distribution	Distribution extra wide 10
	LED180-4S/740				medium 10	
	PSU DM10 ALU					
912300023587	BVP650	130° x 97°	17,000 lm	82	Distribution	Symmetrical
	LED200-4S/740				medium 10	
	PSU DM10 ALU					
912300023588	BVP650	108° x 113°	19,000 lm	82	Distribution	Optiflux asymmetrical axis angle 52°
	LED220-4S/740				medium 10	
	PSU DM10 ALU					
912300023589	BVP650	108° x 113°	21,000 lm	120	Distribution	Distribution extra wide 50
	LED240-4S/740				medium 10	
	PSU DM10 ALU					
912300023593	BVP650	88° x 187°	28,000 lm	120	Distribution	Distribution extra wide 51
	LED320-4S/740				medium 10	
	PSU DM10 ALU					
912300023684	BVP650	83° x 130°	31,000 lm	120	Symmetrical	Distribution extra wide 10
	LED360-4S/740					
	S ALU PSU					
912300023685	BVP650	83° x 130°	33,000 lm	120	Symmetrical	Symmetrical
	LED380-4S/740					
	S ALU PSU					
912300023686	BVP650	83° x 130°	34,000 lm	120	Symmetrical	Optiflux asymmetrical axis angle 52°
	LED400-4S/740					
	S ALU PSU					
912300023687	BVP650	86° x 188°	31,000 lm	120	Optiflux	Distribution extra wide 50
	LED360-4S/740				asymmetrical	
	OFA52 ALU PSU				axis angle 52°	
912300023688	BVP650	83° x 130°	32,000 lm	120	Optiflux	Optiflux asymmetrical axis angle 51
	LED380-4S/740				asymmetrical	
	PSU OFA52 ALU				axis angle 52°	

Order Code	Full Product Name	Luminaire		Number		Optic type
		light beam spread	Luminous Flux	of light sources	outdoor	
912300023689	BVP650	83° x 130°	34,000 lm	120	Optiflux	Optiflux asymmetrical axis angle 52°
	LED400-4S/740					
	PSU OFA52 ALU					
912300023690	BVP650	83° x 130°	30,000 lm	120	Distribution	Distribution extra wide 50
	LED360-4S/740					
	DX50 ALU PSU					
912300023691	BVP650	83° x 130°	31,000 lm	120	Distribution	Distribution extra wide 50
	LED380-4S/740					
	DX50 ALU PSU					
912300023692	BVP650	140° x 70°	32,000 lm	120	Distribution	Distribution extra wide 50
	LED400-4S/740					
	DX50 ALU PSU					
912300023696	BVP650	108° x 113°	29,000 lm	120	Distribution	Distribution extra wide 10
	LED360-4S/740					
	DX10 ALU PSU					
912300023697	BVP650	88° x 187°	31,000 lm	120	Distribution	Distribution extra wide 10
	LED380-4S/740					
	DX10 ALU PSU					
912300023698	BVP650	140° x 70°	32,000 lm	120	Distribution	Distribution extra wide 10
	LED400-4S/740					
	DX10 ALU PSU					
912300023947	BVP650	70° x 21°	36,000 lm	-	Symmetrical	Optiflux asymmetrical axis angle 52°
	LED420-4S/740					
	S ALU PSU					
912300023948	BVP650	39° - 11° x	35,000 lm	-	Optiflux	Optiflux asymmetrical axis angle 52°
	LED420-4S/740	98°				
	OFA52 ALU PSU					
912300023949	BVP650	17° - 5° x	34,000 lm	-	Distribution	Distribution extra wide 50
	LED420-4S/740	132°				
	DX50 ALU PSU					
912300023950	BVP650	14° - 5° x	21,000 lm	-	Distribution	Distribution extra wide 51
	LED420-4S/740	132°				
	DX51 ALU PSU					
912300023951	BVP650	20° - 4° x	34,000 lm	-	Distribution	Distribution extra wide 10
	LED420-4S/740	150°				
	DX10 ALU PSU					
912300023954	BVP650	70° x 21°	38,000 lm	-	Symmetrical	Optiflux asymmetrical axis angle 52°
	LED440-4S/740					
	S ALU PSU					
912300023955	BVP650	39° - 11° x	37,000 lm	-	Optiflux	Optiflux asymmetrical axis angle 52°
	LED440-4S/740	98°				
	OFA52 ALU PSU					
912300023956	BVP650	17° - 5° x	36,000 lm	-	Distribution	Distribution extra wide 50
	LED440-4S/740	132°				
	DX50 ALU PSU					
912300023957	BVP650	14° - 5° x	22,000 lm	-	Distribution	Optiflux asymmetrical axis angle 51
	LED440-4S/740	132°				
	DX51 ALU PSU					

Order Code	Full Product Name	Luminaire		Number	
		light beam spread	Luminous Flux	of light sources	Optic type
		20° - 4° x	36,000 lm	-	Distribution
912300023958	BVP650 LED440-4S/740	150°			extra wide 10
	DX10 ALU PSU				
912300023959	BVP650 LED440-4S/740	52° - 7° x 151°	37,000 lm - 151°	- wide 10	Distribution extra wide 60
	DW10 ALU PSU				
912300023994	BVP650 LED360-4S/740	8° - 26° x 82°	32,000 lm - 82°	- extra wide 60	Distribution extra wide 60
	DX60 ALU PSU				
912300023995	BVP650 LED380-4S/740	8° - 26° x 82°	34,000 lm - 82°	- extra wide 60	Distribution extra wide 60
	DX60 ALU PSU				

Order Code	Full Product Name	Luminaire		Number	
		light beam spread	Luminous Flux	of light sources	Optic type
912300023996	BVP650 LED400-4S/740	8° - 26° x 82°	35,000 lm - 82°	- extra wide 60	Distribution extra wide 60
	DX60 ALU PSU				
912300023997	BVP650 LED420-4S/740	8° - 26° x 82°	37,000 lm - 82°	- extra wide 60	Distribution extra wide 60
	DX60 ALU PSU				
912300023998	BVP650 LED440-4S/740	8° - 26° x 82°	39,000 lm - 82°	- extra wide 60	Distribution extra wide 60
	DX60 ALU PSU				
912300024729	BVP650 T35 1xLED380-4S/740 OFA52 D9	72° x 22°	32,000 lm - 0 OFA52 D9	- axis angle 52°	Optiflux asymmetrical axis angle 52°

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
912300023506	BVP650 LED80-4S/740 PSU S ALU	47 W
912300023507	BVP650 LED100-4S/740 PSU S ALU	57 W
912300023508	BVP650 LED120-4S/740 PSU S ALU	70 W
912300023509	BVP650 LED140-4S/740 PSU S ALU	82 W
912300023510	BVP650 LED160-4S/740 PSU S ALU	95 W
912300023511	BVP650 LED180-4S/740 PSU S ALU	108 W
912300023512	BVP650 LED200-4S/740 PSU S ALU	122 W
912300023513	BVP650 LED220-4S/740 PSU S ALU	134 W
912300023514	BVP650 LED240-4S/740 PSU S ALU	140 W
912300023515	BVP650 LED260-4S/740 PSU S ALU	152 W
912300023516	BVP650 LED280-4S/740 PSU S ALU	166 W
912300023517	BVP650 LED300-4S/740 PSU S ALU	178 W
912300023518	BVP650 LED320-4S/740 PSU S ALU	192 W
912300023519	BVP650 LED340-4S/740 PSU S ALU	205 W
912300023521	BVP650 LED80-4S/740 PSU OFA52 ALU	47 W
912300023522	BVP650 LED100-4S/740 PSU OFA52 ALU	57 W
912300023523	BVP650 LED120-4S/740 PSU OFA52 ALU	70 W
912300023524	BVP650 LED140-4S/740 PSU OFA52 ALU	82 W
912300023525	BVP650 LED160-4S/740 PSU OFA52 ALU	95 W
912300023526	BVP650 LED180-4S/740 PSU OFA52 ALU	108 W
912300023527	BVP650 LED200-4S/740 PSU OFA52 ALU	122 W
912300023528	BVP650 LED220-4S/740 PSU OFA52 ALU	134 W
912300023529	BVP650 LED240-4S/740 PSU OFA52 ALU	140 W
912300023530	BVP650 LED260-4S/740 PSU OFA52 ALU	152 W
912300023531	BVP650 LED280-4S/740 PSU OFA52 ALU	166 W
912300023532	BVP650 LED300-4S/740 PSU OFA52 ALU	178 W
912300023533	BVP650 LED320-4S/740 PSU OFA52 ALU	192 W
912300023534	BVP650 LED340-4S/740 PSU OFA52 ALU	205 W
912300023536	BVP650 LED80-4S/740 PSU DX50 ALU	47 W
912300023537	BVP650 LED100-4S/740 PSU DX50 ALU	57 W
912300023538	BVP650 LED120-4S/740 PSU DX50 ALU	70 W
912300023539	BVP650 LED140-4S/740 PSU DX50 ALU	82 W
912300023540	BVP650 LED160-4S/740 PSU DX50 ALU	95 W
912300023541	BVP650 LED180-4S/740 PSU DX50 ALU	108 W

Order Code	Full Product Name	Power Consumption
912300023542	BVP650 LED200-4S/740 PSU DX50 ALU	122 W
912300023543	BVP650 LED220-4S/740 PSU DX50 ALU	134 W
912300023544	BVP650 LED240-4S/740 PSU DX50 ALU	140 W
912300023545	BVP650 LED260-4S/740 PSU DX50 ALU	152 W
912300023546	BVP650 LED280-4S/740 PSU DX50 ALU	166 W
912300023547	BVP650 LED300-4S/740 PSU DX50 ALU	178 W
912300023548	BVP650 LED320-4S/740 PSU DX50 ALU	192 W
912300023549	BVP650 LED340-4S/740 PSU DX50 ALU	205 W
912300023551	BVP650 LED80-4S/740 PSU DW10 ALU	47 W
912300023557	BVP650 LED200-4S/740 PSU DW10 ALU	122 W
912300023559	BVP650 LED240-4S/740 PSU DW10 ALU	140 W
912300023564	BVP650 LED340-4S/740 PSU DW10 ALU	205 W
912300023566	BVP650 LED80-4S/740 PSU DX10 ALU	47 W
912300023568	BVP650 LED120-4S/740 PSU DX10 ALU	70 W
912300023570	BVP650 LED160-4S/740 PSU DX10 ALU	95 W
912300023571	BVP650 LED180-4S/740 PSU DX10 ALU	108 W
912300023572	BVP650 LED200-4S/740 PSU DX10 ALU	122 W
912300023573	BVP650 LED220-4S/740 PSU DX10 ALU	134 W
912300023574	BVP650 LED240-4S/740 PSU DX10 ALU	140 W
912300023575	BVP650 LED260-4S/740 PSU DX10 ALU	152 W
912300023576	BVP650 LED280-4S/740 PSU DX10 ALU	166 W
912300023577	BVP650 LED300-4S/740 PSU DX10 ALU	178 W
912300023578	BVP650 LED320-4S/740 PSU DX10 ALU	192 W
912300023579	BVP650 LED340-4S/740 PSU DX10 ALU	205 W
912300023581	BVP650 LED80-4S/740 PSU DM10 ALU	47 W
912300023582	BVP650 LED100-4S/740 PSU DM10 ALU	57 W
912300023583	BVP650 LED120-4S/740 PSU DM10 ALU	70 W
912300023584	BVP650 LED140-4S/740 PSU DM10 ALU	82 W
912300023586	BVP650 LED180-4S/740 PSU DM10 ALU	108 W
912300023587	BVP650 LED200-4S/740 PSU DM10 ALU	122 W
912300023588	BVP650 LED220-4S/740 PSU DM10 ALU	134 W
912300023589	BVP650 LED240-4S/740 PSU DM10 ALU	140 W
912300023593	BVP650 LED320-4S/740 PSU DM10 ALU	192 W
912300023684	BVP650 LED360-4S/740 S ALU PSU	220 W

Order Code	Full Product Name	Power Consumption
912300023685	BVP650 LED380-4S/740 S ALU PSU	235 W
912300023686	BVP650 LED400-4S/740 S ALU PSU	250 W
912300023687	BVP650 LED360-4S/740 OFA52 ALU PSU	220 W
912300023688	BVP650 LED380-4S/740 PSU OFA52 ALU	235 W
912300023689	BVP650 LED400-4S/740 PSU OFA52 ALU	250 W
912300023690	BVP650 LED360-4S/740 DX50 ALU PSU	220 W
912300023691	BVP650 LED380-4S/740 DX50 ALU PSU	235 W
912300023692	BVP650 LED400-4S/740 DX50 ALU PSU	250 W
912300023696	BVP650 LED360-4S/740 DX10 ALU PSU	220 W
912300023697	BVP650 LED380-4S/740 DX10 ALU PSU	235 W
912300023698	BVP650 LED400-4S/740 DX10 ALU PSU	250 W
912300023947	BVP650 LED420-4S/740 S ALU PSU	265 W
912300023948	BVP650 LED420-4S/740 OFA52 ALU PSU	265 W
912300023949	BVP650 LED420-4S/740 DX50 ALU PSU	265 W

Order Code	Full Product Name	Power Consumption
912300023950	BVP650 LED420-4S/740 DX51 ALU PSU	265 W
912300023951	BVP650 LED420-4S/740 DX10 ALU PSU	265 W
912300023954	BVP650 LED440-4S/740 S ALU PSU	280 W
912300023955	BVP650 LED440-4S/740 OFA52 ALU PSU	280 W
912300023956	BVP650 LED440-4S/740 DX50 ALU PSU	280 W
912300023957	BVP650 LED440-4S/740 DX51 ALU PSU	280 W
912300023958	BVP650 LED440-4S/740 DX10 ALU PSU	280 W
912300023959	BVP650 LED440-4S/740 DW10 ALU PSU	280 W
912300023994	BVP650 LED360-4S/740 DX60 ALU PSU	220 W
912300023995	BVP650 LED380-4S/740 DX60 ALU PSU	235 W
912300023996	BVP650 LED400-4S/740 DX60 ALU PSU	250 W
912300023997	BVP650 LED420-4S/740 DX60 ALU PSU	265 W
912300023998	BVP650 LED440-4S/740 DX60 ALU PSU	280 W
912300024729	BVP650 T35 1xLED380-4S/740 OFA52 D9	235 W

## Controls and Dimming

Order Code	Full Product Name	Dimmable
912300023506	BVP650 LED80-4S/740 PSU S ALU	No
912300023507	BVP650 LED100-4S/740 PSU S ALU	No
912300023508	BVP650 LED120-4S/740 PSU S ALU	No
912300023509	BVP650 LED140-4S/740 PSU S ALU	No
912300023510	BVP650 LED160-4S/740 PSU S ALU	No
912300023511	BVP650 LED180-4S/740 PSU S ALU	No
912300023512	BVP650 LED200-4S/740 PSU S ALU	No
912300023513	BVP650 LED220-4S/740 PSU S ALU	No
912300023514	BVP650 LED240-4S/740 PSU S ALU	No
912300023515	BVP650 LED260-4S/740 PSU S ALU	No
912300023516	BVP650 LED280-4S/740 PSU S ALU	No
912300023517	BVP650 LED300-4S/740 PSU S ALU	No
912300023518	BVP650 LED320-4S/740 PSU S ALU	No
912300023519	BVP650 LED340-4S/740 PSU S ALU	No
912300023521	BVP650 LED80-4S/740 PSU OFA52 ALU	No
912300023522	BVP650 LED100-4S/740 PSU OFA52 ALU	No
912300023523	BVP650 LED120-4S/740 PSU OFA52 ALU	No
912300023524	BVP650 LED140-4S/740 PSU OFA52 ALU	No
912300023525	BVP650 LED160-4S/740 PSU OFA52 ALU	No
912300023526	BVP650 LED180-4S/740 PSU OFA52 ALU	No
912300023527	BVP650 LED200-4S/740 PSU OFA52 ALU	No
912300023528	BVP650 LED220-4S/740 PSU OFA52 ALU	No
912300023529	BVP650 LED240-4S/740 PSU OFA52 ALU	No
912300023530	BVP650 LED260-4S/740 PSU OFA52 ALU	No
912300023531	BVP650 LED280-4S/740 PSU OFA52 ALU	No
912300023532	BVP650 LED300-4S/740 PSU OFA52 ALU	No
912300023533	BVP650 LED320-4S/740 PSU OFA52 ALU	No
912300023534	BVP650 LED340-4S/740 PSU OFA52 ALU	No
912300023536	BVP650 LED80-4S/740 PSU DX50 ALU	No
912300023537	BVP650 LED100-4S/740 PSU DX50 ALU	No
912300023538	BVP650 LED120-4S/740 PSU DX50 ALU	No
912300023539	BVP650 LED140-4S/740 PSU DX50 ALU	No
912300023540	BVP650 LED160-4S/740 PSU DX50 ALU	No
912300023541	BVP650 LED180-4S/740 PSU DX50 ALU	No

Order Code	Full Product Name	Dimmable
912300023542	BVP650 LED200-4S/740 PSU DX50 ALU	No
912300023543	BVP650 LED220-4S/740 PSU DX50 ALU	No
912300023544	BVP650 LED240-4S/740 PSU DX50 ALU	No
912300023545	BVP650 LED260-4S/740 PSU DX50 ALU	No
912300023546	BVP650 LED280-4S/740 PSU DX50 ALU	No
912300023547	BVP650 LED300-4S/740 PSU DX50 ALU	No
912300023548	BVP650 LED320-4S/740 PSU DX50 ALU	No
912300023549	BVP650 LED340-4S/740 PSU DX50 ALU	No
912300023551	BVP650 LED80-4S/740 PSU DW10 ALU	No
912300023557	BVP650 LED200-4S/740 PSU DW10 ALU	No
912300023559	BVP650 LED240-4S/740 PSU DW10 ALU	No
912300023564	BVP650 LED340-4S/740 PSU DW10 ALU	No
912300023566	BVP650 LED80-4S/740 PSU DX10 ALU	No
912300023568	BVP650 LED120-4S/740 PSU DX10 ALU	No
912300023570	BVP650 LED160-4S/740 PSU DX10 ALU	No
912300023571	BVP650 LED180-4S/740 PSU DX10 ALU	No
912300023572	BVP650 LED200-4S/740 PSU DX10 ALU	No
912300023573	BVP650 LED220-4S/740 PSU DX10 ALU	No
912300023574	BVP650 LED240-4S/740 PSU DX10 ALU	No
912300023575	BVP650 LED260-4S/740 PSU DX10 ALU	No
912300023576	BVP650 LED280-4S/740 PSU DX10 ALU	No
912300023577	BVP650 LED300-4S/740 PSU DX10 ALU	No
912300023578	BVP650 LED320-4S/740 PSU DX10 ALU	No
912300023579	BVP650 LED340-4S/740 PSU DX10 ALU	No
912300023581	BVP650 LED80-4S/740 PSU DM10 ALU	No
912300023582	BVP650 LED100-4S/740 PSU DM10 ALU	No
912300023583	BVP650 LED120-4S/740 PSU DM10 ALU	No
912300023584	BVP650 LED140-4S/740 PSU DM10 ALU	No
912300023586	BVP650 LED180-4S/740 PSU DM10 ALU	No
912300023587	BVP650 LED200-4S/740 PSU DM10 ALU	No
912300023588	BVP650 LED220-4S/740 PSU DM10 ALU	No
912300023589	BVP650 LED240-4S/740 PSU DM10 ALU	No
912300023593	BVP650 LED320-4S/740 PSU DM10 ALU	No
912300023684	BVP650 LED360-4S/740 S ALU PSU	No

## ClearFlood

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
912300023685	BVP650 LED380-4S/740 S ALU PSU	No	912300023950	BVP650 LED420-4S/740 DX51 ALU PSU	No
912300023686	BVP650 LED400-4S/740 S ALU PSU	No	912300023951	BVP650 LED420-4S/740 DX10 ALU PSU	No
912300023687	BVP650 LED360-4S/740 OFA52 ALU PSU	No	912300023954	BVP650 LED440-4S/740 S ALU PSU	No
912300023688	BVP650 LED380-4S/740 PSU OFA52 ALU	No	912300023955	BVP650 LED440-4S/740 OFA52 ALU PSU	No
912300023689	BVP650 LED400-4S/740 PSU OFA52 ALU	No	912300023956	BVP650 LED440-4S/740 DX50 ALU PSU	No
912300023690	BVP650 LED360-4S/740 DX50 ALU PSU	No	912300023957	BVP650 LED440-4S/740 DX51 ALU PSU	No
912300023691	BVP650 LED380-4S/740 DX50 ALU PSU	No	912300023958	BVP650 LED440-4S/740 DX10 ALU PSU	No
912300023692	BVP650 LED400-4S/740 DX50 ALU PSU	No	912300023959	BVP650 LED440-4S/740 DW10 ALU PSU	No
912300023696	BVP650 LED360-4S/740 DX10 ALU PSU	No	912300023994	BVP650 LED360-4S/740 DX60 ALU PSU	No
912300023697	BVP650 LED380-4S/740 DX10 ALU PSU	No	912300023995	BVP650 LED380-4S/740 DX60 ALU PSU	No
912300023698	BVP650 LED400-4S/740 DX10 ALU PSU	No	912300023996	BVP650 LED400-4S/740 DX60 ALU PSU	No
912300023947	BVP650 LED420-4S/740 S ALU PSU	No	912300023997	BVP650 LED420-4S/740 DX60 ALU PSU	No
912300023948	BVP650 LED420-4S/740 OFA52 ALU PSU	No	912300023998	BVP650 LED440-4S/740 DX60 ALU PSU	No
912300023949	BVP650 LED420-4S/740 DX50 ALU PSU	No	912300024729	BVP650 T35 1xLED380-4S/740 OFA52 D9	Yes

