



Cabana 2 – ultra-convenient

Cabana2 BY150P

Cabana 2 is a functional high-bay indoor luminaire for high-intensity discharge lamps. It is supplied with a reflector, which can be attached to the unit without screws by means of an ingenious bayonet construction. The innovative external beam regulator enables easy lamp adjustment (narrow or wide beam) at the installation site. The external connector means the electrical connection can be made without opening the unit. Two versions are available: the standard version for SON and HPI-P lamps, and a round version for CDM-TMW lamps.

Benefits

- Easy to install
- High optical efficiency

Features

- External beam regulator for easy on-site narrow/wide beam adjustment
- Bayonet construction for attaching the reflector to the housing
- External connector for quick, simple electrical connection without opening the unit

Application

- Industrial halls
- Warehouses
- DIY stores

Specifications

Type	BY150P (SON, HPI-P lamp version)
	BY151P (CDM-TMW lamp version)

Light source	HID:
	- MASTER HPI Plus / E40 / 250, 400 W
	- SON / E40 / 250, 400 W
	- Master CDM-TMW / PGZ18 / 210, 315 W
Lamp included	Yes (K) or No

Cabana2 BY150P

Ballast	HID-Primavision (for CDM lamps)
	Conventional electro-magnetic (SGR) (for SON lamps)
	Conventional electro-magnetic (HGR) (for HPI lamps)
Reflector	Basic (R)
Optical cover	Glass, clear (GC)
Options	Emergency lighting: 1 hour (EL1)
	Auxiliary lighting (AUX) for instant light
Connection	3-pole push-in connector
Material	Housing: die-cast aluminum
	Reflector: anodized aluminum
	Cover: thermally toughened glass

Installation	Installation without removing lamp(s) and cover
	Individual, with hooks or bracket
	Operating temperature: -15°C < Ta < 35°C
Accessories	Glass cover, mounting bracket, reflector
Remarks	All components are in one box (incl accessories), though, the accessories can be ordered separately

Versions



Cabana 2 BY150P high-bay luminaire

Product details

External beam adjuster - in



External beam adjuster - out



Waterproof external connector - open



Waterproof external connector - closed



Cabana2 BY150P

Product details



Clip of the glass cover



Auxiliary lamp in reflector



Emergency lighting lamp in reflector

