



Product Description

MASTER PL-L 4 Pin

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 2 parallel fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Long life and sustainable light output

Features

- 4-pin base without starter and capacitor
- Lamp characteristics are influenced by operating conditions and control gear used
- Lamp performance is governed by temperature of the coolest spot
- Dimming is possible

Application


- Designed for general lighting in shops, offices, hotels and specific task lighting, as well as outdoors in residential areas and parks

Versions



MASTER PL-L 4 Pin

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-L 18W/840/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm
MASTER PL-L 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm
MASTER PL-L 55W/840/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm
MASTER PL-L 55W/830/4P 1CT/25	39.0 mm	18.0 mm	509.2 mm	535 mm	541.6 mm
MASTER PL-L 18W/830/4P 1CT/25	39.0 mm	18.0 mm	194.2 mm	220 mm	226.6 mm
MASTER PL-L 36W/840/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm
MASTER PL-L 36W/840/4P 1CT/25	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	2.0 mg

Controls and Dimming

Dimmable	yes
----------	-----

General Information

Cap-Base	2G11
Life To 50% Failures Preheat (Nom)	20000 h
LSF Preheat 16000 h Rated	82 %
LSF Preheat 20000 h Rated	50 %
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	98 %
LSF Preheat 8000 h Rated	97 %

Light Technical

LLMF 16000 h Rated	90 %
LLMF 20000 h Rated	90 %

Temperature

Design Temperature (Nom)	30 °C
--------------------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927903008370	MASTER PL-L 18W/830/4P 1CT/25	20 kWh
927903008470	MASTER PL-L 18W/840/4P 1CT/25	20 kWh
927903408470	MASTER PL-L 36W/840/4P 1CT/25	40 kWh
927903408472	MASTER PL-L 36W/840/4P 1CT/25	40 kWh
927908708370	MASTER PL-L 55W/830/4P 1CT/25	61 kWh
927908708470	MASTER PL-L 55W/840/4P 1CT/25	61 kWh
927908708472	MASTER PL-L 55W/840/4P 1CT/25	61 kWh

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927903008370	MASTER PL-L 18W/830/4P 1CT/25	0.375 A	18.0 W
927903008470	MASTER PL-L 18W/840/4P 1CT/25	0.375 A	18.0 W
927903408470	MASTER PL-L 36W/840/4P 1CT/25	0.435 A	36.0 W
927903408472	MASTER PL-L 36W/840/4P 1CT/25	0.435 A	36.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
927908708370	MASTER PL-L 55W/830/4P 1CT/25	0.525 A	55 W
927908708470	MASTER PL-L 55W/840/4P 1CT/25	0.525 A	55.0 W
927908708472	MASTER PL-L 55W/840/4P 1CT/25	0.525 A	55.0 W

General Information (1/2)

MASTER PL-L 4 Pin

Order Code	Full Product Name	Life To			
		Life To 10% Failures (Nom)	50% Failures (Nom)	LSF 12000 h Rated	LSF 2000 h Rated
927903008370	MASTER PL-L 18W/830/4P 1CT/25	10000 h	15000 h	80 %	99 %
927903008470	MASTER PL-L 18W/840/4P 1CT/25	10000 h	15000 h	80 %	99 %
927903408470	MASTER PL-L 36W/840/4P 1CT/25	10000 h	15000 h	80 %	99 %
927903408472	MASTER PL-L 36W/840/4P 1CT/25	10000 h	15000 h	80 %	99 %

Order Code	Full Product Name	Life To			
		Life To 10% Failures (Nom)	50% Failures (Nom)	LSF 12000 h Rated	LSF 2000 h Rated
927908708370	MASTER PL-L 55W/830/4P 1CT/25	-	-	-	-
927908708470	MASTER PL-L 55W/840/4P 1CT/25	-	-	-	-
927908708472	MASTER PL-L 55W/840/4P 1CT/25	-	-	-	-

General Information (2/2)

Order Code	Full Product Name	LSF 4000 h Rated	LSF 6000 h Rated	LSF 8000 h Rated	System Description
		927903008370	MASTER PL-L 18W/830/4P 1CT/25	98 %	96 %
927903008470	MASTER PL-L 18W/840/4P 1CT/25	98 %	96 %	94 %	na
927903408470	MASTER PL-L 36W/840/4P 1CT/25	98 %	96 %	94 %	na
927903408472	MASTER PL-L 36W/840/4P 1CT/25	98 %	96 %	94 %	na

Order Code	Full Product Name	LSF 4000 h Rated	LSF 6000 h Rated	LSF 8000 h Rated	System Description
		927908708370	MASTER PL-L 55W/830/4P 1CT/25	-	-
927908708470	MASTER PL-L 55W/840/4P 1CT/25	-	-	-	High Frequency
927908708472	MASTER PL-L 55W/840/4P 1CT/25	-	-	-	High Frequency

Light Technical (1/2)

Order Code	Full Product Name	Colour Code	Colour Designation	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)
				927903008370	MASTER PL-L 18W/830/4P 1CT/25
927903008470	MASTER PL-L 18W/840/4P 1CT/25	840	Cool White (CW)	4000 K	82
927903408470	MASTER PL-L 36W/840/4P 1CT/25	840	Cool White (CW)	4000 K	82
927903408472	MASTER PL-L 36W/840/4P 1CT/25	840	Cool White (CW)	4000 K	82

Order Code	Full Product Name	Colour Code	Colour Designation	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)
				927908708370	MASTER PL-L 55W/830/4P 1CT/25
927908708470	MASTER PL-L 55W/840/4P 1CT/25	840	Cool White (CW)	4000 K	82
927908708472	MASTER PL-L 55W/840/4P 1CT/25	840	Cool White (CW)	4000 K	82

Light Technical (2/2)

Order Code	Full Product Name	LLMF 12000 h Rated	LLMF 2000 h Rated	LLMF 4000 h Rated	LLMF 6000 h Rated	LLMF 8000 h Rated	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
		927903008370	MASTER PL-L 18W/830/4P 1CT/25	90 %	94 %	93 %	92 %	91 %	67 lm/W

MASTER PL-L 4 Pin

Order Code	Full Product Name	LLMF 12000 h Rated	LLMF 2000 h Rated	LLMF 4000 h Rated	LLMF 6000 h Rated	LLMF 8000 h Rated	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
927903008470	MASTER PL-L 18W/840/4P 1CT/25	90 %	94 %	93 %	92 %	91 %	67 lm/W	1200 lm	1200 lm
927903408470	MASTER PL-L 36W/840/4P 1CT/25	90 %	94 %	93 %	92 %	91 %	81 lm/W	2900 lm	2900 lm
927903408472	MASTER PL-L 36W/840/4P 1CT/25	90 %	94 %	93 %	92 %	91 %	81 lm/W	2900 lm	2900 lm
927908708370	MASTER PL-L 55W/830/4P 1CT/25	91 %	95 %	94 %	93 %	92 %	87 lm/W	4800 lm	4800 lm
927908708470	MASTER PL-L 55W/840/4P 1CT/25	91 %	95 %	94 %	93 %	92 %	87 lm/W	4800 lm	4800 lm
927908708472	MASTER PL-L 55W/840/4P 1CT/25	91 %	95 %	94 %	93 %	92 %	87 lm/W	4800 lm	4800 lm

