



# CitySoul – create identity

## CitySoul

CitySoul is a family of modular street-lighting luminaires featuring state-of-the-art lamp and gear technologies – including LED – and offering outstanding optical performance. Its classic design merges well with today's urban environment. The simple, flat, ellipsoidal form of the luminaire creates an elegant light-point. Suitable for side-entry, suspended or post-top installation, and with its adjustable beam and light trespass accessories, this versatile luminaire fits every application. CitySoul comes in two sizes, along with a complete range of dedicated masts and brackets.

### Benefits

- Compact urban lighting luminaire – part of a complete solution that contributes to the identity of the city instead of just providing light points
- Highly versatile range with a wide choice of masts and brackets in every style – modern or classical, single or twin, with the option of a pedestrian mini-luminaire
- Available with mast heights from 4 to 10 m in standard ultra-dark grey or other colors and finishes on request

### Features

- Simple, flat, ellipsoidal housing available in two sizes
- Wide choice of masts and brackets in every style – modern or classical, single or twin; mast heights from 4 to 10 m
- State-of-the-art lamp and gear technologies – including LED
- Suitable for side-entry, suspended or post-top installation
- Adjustable beam, plus light trespass accessories

### Application

- Urban, residential, pedestrian and shopping areas
- Local streets, minor collector roads
- Squares, parks

### Specifications

<b>Type</b>	CGP431
<b>Light source</b>	HID: - 1 x MASTER CosmoWhite CPO-TW / PGZ12 / 45, 60, 90, 140 W - 1 x MASTERColour CDM-T / G12 / 70, 150, 250 W - 1 x MASTER CityWhite CDO-TT / E27 / 50, 70 W - 1 x MASTER CityWhite CDO-TT / E40 / 100, 150, 250 W - 1 x SON-T/ E27 / 50, 70 W - 1 x SON-T/ E40 / 100, 250 W Compact fluorescent: - 1 x MASTER PL-T 4 Pin / GX24q-3 or 4 or 5* / 32, 42 W - *depends on wattage
<b>Lamp included</b>	Yes (K or light color 728, 830, 840 or 942) No
<b>Gear</b>	Electromagnetic (low loss), 230 or 240 V / 50 Hz: - Inductive Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF) - Electronic (EB)
<b>Optic</b>	Open CT-POT (OR) optic for CosmoPolis, CDO and SON lamps Optic for CosmoPolis lamp (OC)

## Specifications

<b>Type</b>	CGP430
<b>Light source</b>	HID: - 1 x MASTER CosmoWhite CPO-TW / PGZ12 / 45, 60, 90 W - 1 x MASTER CityWhite CDO-TT / E27 / 50, 70 W - 1 x MASTER CityWhite CDO-TT / E40 / 100 W - 1 x SON-T/ E27 / 50, 70 W - 1 x SON-T/ E40 / 100 W - 1 x MASTERColour CDM-T / G12 / 35, 70 W Compact fluorescent: - 1 x MASTER PL-T 4 Pin / GX24q-3 or 4 or 5* / 32, 42W - *depends on wattage
<b>Lamp included</b>	Yes (K or light color 728, 830, 840 or 942) No
<b>Gear</b>	Electromagnetic (low loss), 230 or 240 V / 50 Hz:
<b>Inductive</b>	Electronic, 220 - 240 V / 50 - 60 Hz: - Electronic (EB)
<b>Optic</b>	Open CT-POT (OR) optic for CosmoPolis, CDO and SON lamps Optic for CosmoPolis lamp (OC)
<b>Optical cover</b>	Flat glass (FG) Flat glass with DynaClean coating (FGD) Polycarbonate bowl (PC)

## Specifications

<b>Type</b>	CSP431
-------------	--------


<b>Optical cover</b>	Flat glass (FG) Flat glass with DynaClean coating (FGD) Polycarbonate bowl (PC)
<b>Ignitor</b>	Series digital (SUD)
<b>Options</b>	Lighting controls: - Chronosense (CH), dimming switch (SW), photo/minicell (P3)
<b>Materials and finishing</b>	Housing: die-cast aluminum Inner components: glass-reinforced polypropylene
<b>Color</b>	Canopy: Philips dark grey 10714 Frame: silver grey Other RAL or Akzo Futura colors available on request
<b>Installation</b>	Post-top mounting: axial entry Ø 60 / 76 mm (76P) Post-top mounting: tiltable with hinge (76PA) Side-entry mounting: lateral entry Ø 42 - 60 mm (60S) Recommended mounting height: 4 - 10 m, depending on choice of mast and bracket
<b>Accessories</b>	Mounting brackets (ZGP430 MBA)
<b>Main applications</b>	Urban, residential, pedestrian and shopping areas, squares, local streets, minor collector roads, parks

<b>Ignitor</b>	Series digital (SUD)
<b>Options</b>	Lighting controls: - Chronosense (CH), dimming switch (SW), photo/minicell (P3)
<b>Materials and finishing</b>	Housing: die-cast aluminum Inner components: glass-reinforced polypropylene
<b>Color</b>	Canopy: dark grey (GR) Frame: silver grey Other RAL or Akzo Futura colors available on request
<b>Installation</b>	Post-top mounting: axial entry Ø 60 / 76 mm (76P) Post-top mounting: tiltable with hinge (76PA) Side-entry mounting: lateral entry Ø 42 - 60 mm (60S) Recommended mounting height: 4 - 10 m, depending on choice of mast and bracket
<b>Accessories</b>	Mounting brackets (ZGP430 MBA)
<b>Main applications</b>	Urban, residential, pedestrian and shopping areas, squares, local streets, minor collector roads, parks

	- 1 x MASTER CityWhite CDO-TT / E40 / 100, 150, 250 W
	- 1 x SON-T/ E27 / 50, 70 W
	- 1 x SON-T/ E40 / 100, 250 W
	Compact fluorescent:
	- 1 x MASTER PL-T 4 Pin / GX24q-3 or 4 or 5* / 32, 42 W
	- *depends on wattage
<b>Lamp included</b>	Yes (K or light color 728, 830, 840 or 942)
	No
<b>Gear</b>	Electromagnetic (low loss), 230 or 240 V / 50 Hz:
	- Inductive
	Electronic, 220 - 240 V / 50 - 60 Hz:
	- Electronic (EB)
<b>Optic</b>	Open CT-POT (OR) optic for CosmoPolis, CDO and SON lamps
	Optic for CosmoPolis lamp (OC)
<b>Optical cover</b>	Flat glass (FG)
	Flat glass with DynaClean coating (FGD)
	Polycarbonate bowl (PC)

<b>Ignitor</b>	Series digital (SUD)
<b>Options</b>	Lighting controls: - Chronosense (CH), dimming switch (SW), photo/minicell (P3)
<b>Materials and finishing</b>	Housing: die-cast aluminum Inner components: glass-reinforced polypropylene
<b>Color</b>	Canopy: Philips dark grey 10714 Frame: silver grey Other RAL or Akzo Futura colors available on request
<b>Installation</b>	Suspended via 34 mm gas thread pipe Recommended mounting height: 4 - 10 m, depending on choice of mast and bracket
<b>Main applications</b>	Urban, residential, pedestrian and shopping areas, squares, local streets, minor collector roads, parks

## Accessories



Light Trespass louver

Ordercode 910502212718,  
910502212818

