



The affordable LED solution

CorePro LEDtube EM/Mains T8

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Benefits

- Minimizes overall lighting costs
- Offers cheapest and easiest upgrade to LED lighting technology

Features

- Only 50% energy consumption compared to fluorescent tubes
- Lasts two times longer than fluorescent tubes
- Retrofit replacement of existing T8 lamps on electromagnetic (EM) ballast installations

Application


- Parking lots and covered car parks
- Warehouses and coldrooms
- Signage

Warnings and Safety

- –

CorePro LEDtube EM/Mains T8


Versions



LEDtube COR 21W G13

CorePro LEDtube EM/Mains T8

Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 14.5W840	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 14.5W865	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1800mm 21W 840 T8	25.8 mm	28 mm	1,762.6 mm	1,769.7 mm	1,776.8 mm

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm 15.5W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 840 T8 CL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm 15.5W 865 T8 CL	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm HO 18W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm HO 18W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm HO 18W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm HO 18W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm HO 18W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm UO 21.5W 830 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

CorePro LEDtube EM/Mains T8

Dimensional drawing

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1200mm UO 21.5W 840 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1200mm UO 21.5W 865 T8	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
CorePro LEDtube 1500mm 20W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 840 T8 CL	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm 20W 865 T8 CL	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm HO 24W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 31.5W 830 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 31.5W 840 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 1500mm UO 31.5W 865 T8	25.7 mm	28 mm	1,500 mm	1,507.1 mm	1,514.2 mm
CorePro LEDtube 600mm 8W 830 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 840 T8 CL	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm 8W 865 T8 CL	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 830 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

CorePro LEDtube EM/Mains T8

Product	D1	D2	A1	A2	A3
CorePro LEDtube 600mm HO 8W 840 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm
CorePro LEDtube 600mm HO 8W 865 T8	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

General Information	
Cap-Base	G13
Switching Cycle	200,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T8

General Information

Order Code	Full Product Name	Nominal lifetime
32535700	CorePro LEDtube 1200mm 14.5W840	30,000 hour(s)
32537100	CorePro LEDtube 1200mm 14.5W865	30,000 hour(s)
31692800	CorePro LEDtube 1800mm 21W 840 T8	50,000 hour(s)
80611100	CorePro LEDtube 1200mm HO 18W 865 T8	50,000 hour(s)
47558800	CorePro LEDtube 1200mm HO 18W 865 T8	50,000 hour(s)
80613500	CorePro LEDtube 1200mm HO 18W 840 T8	50,000 hour(s)
46958700	CorePro LEDtube 1200mm HO 18W 840 T8	50,000 hour(s)
80615900	CorePro LEDtube 1500mm HO 24W 865 T8	50,000 hour(s)
47560100	CorePro LEDtube 1500mm HO 24W 865 T8	50,000 hour(s)
80617300	CorePro LEDtube 1500mm HO 24W 840 T8	50,000 hour(s)
46960000	CorePro LEDtube 1500mm HO 24W 840 T8	50,000 hour(s)
32531900	CorePro LEDtube 600mm 8W 840 T8	50,000 hour(s)
32533300	CorePro LEDtube 600mm 8W 865 T8	50,000 hour(s)
32539500	CorePro LEDtube 1500mm 20W 840 T8	50,000 hour(s)
32541800	CorePro LEDtube 1500mm 20W 865 T8	50,000 hour(s)
41897400	CorePro LEDtube 1200mm UO 21.5W 840 T8	50,000 hour(s)
41899800	CorePro LEDtube 1200mm UO 21.5W 865 T8	50,000 hour(s)
41901800	CorePro LEDtube 1500mm UO 31.5W 840 T8	50,000 hour(s)
41903200	CorePro LEDtube 1500mm UO 31.5W 865 T8	50,000 hour(s)
42103500	CorePro LEDtube 600mm HO 8W 840 T8	50,000 hour(s)
42105900	CorePro LEDtube 600mm HO 8W 865 T8	50,000 hour(s)
44807000	CorePro LEDtube 1200mm 15.5W 840 T8	50,000 hour(s)
46954900	CorePro LEDtube 1200mm 15.5W 840 T8	50,000 hour(s)
44807000	CorePro LEDtube 1200mm 15.5W 840 T8 CL	50,000 hour(s)
44809400	CorePro LEDtube 1200mm 15.5W 865 T8	50,000 hour(s)
46956300	CorePro LEDtube 1200mm 15.5W 865 T8	50,000 hour(s)
44809400	CorePro LEDtube 1200mm 15.5W 865 T8 CL	50,000 hour(s)
45977900	CorePro LEDtube 600mm 8W 840 T8	50,000 hour(s)
45977900	CorePro LEDtube 600mm 8W 840 T8 CL	50,000 hour(s)
45979300	CorePro LEDtube 600mm 8W 865 T8	50,000 hour(s)
45979300	CorePro LEDtube 600mm 8W 865 T8 CL	50,000 hour(s)
45981600	CorePro LEDtube 1500mm 20W 840 T8	50,000 hour(s)
45981600	CorePro LEDtube 1500mm 20W 840 T8 CL	50,000 hour(s)
45983000	CorePro LEDtube 1500mm 20W 865 T8	50,000 hour(s)
45983000	CorePro LEDtube 1500mm 20W 865 T8 CL	50,000 hour(s)
48638600	CorePro LEDtube 600mm 8W 830 T8	50,000 hour(s)
48640900	CorePro LEDtube 1200mm 15.5W 830 T8	50,000 hour(s)
48642300	CorePro LEDtube 1500mm 20W 830 T8	50,000 hour(s)
48644700	CorePro LEDtube 600mm HO 8W 830 T8	50,000 hour(s)
48646100	CorePro LEDtube 1200mm HO 18W 830 T8	50,000 hour(s)
48648500	CorePro LEDtube 1500mm HO 24W 830 T8	50,000 hour(s)
48650800	CorePro LEDtube 1200mm UO 21.5W 830 T8	50,000 hour(s)
48652200	CorePro LEDtube 1500mm UO 31.5W 830 T8	50,000 hour(s)

CorePro LEDtube EM/Mains T8

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
32535700	CorePro LEDtube 1200mm 14.5W840	240 degree(s)	4000 K	840	1,600 lm
32537100	CorePro LEDtube 1200mm 14.5W865	240 degree(s)	6500 K	865	1,600 lm
31692800	CorePro LEDtube 1800mm 21W 840 T8	160 degree(s)	4000 K	840	3,100 lm
80611100	CorePro LEDtube 1200mm HO 18W 865 T8	240 degree(s)	6500 K	865	2,000 lm
47558800	CorePro LEDtube 1200mm HO 18W 865 T8	240 degree(s)	6500 K	865	2,000 lm
80613500	CorePro LEDtube 1200mm HO 18W 840 T8	240 degree(s)	4000 K	840	2,000 lm
46958700	CorePro LEDtube 1200mm HO 18W 840 T8	240 degree(s)	4000 K	840	2,000 lm
80615900	CorePro LEDtube 1500mm HO 24W 865 T8	240 degree(s)	6500 K	865	2,700 lm
47560100	CorePro LEDtube 1500mm HO 24W 865 T8	240 degree(s)	6500 K	865	2,700 lm
80617300	CorePro LEDtube 1500mm HO 24W 840 T8	240 degree(s)	4000 K	840	2,700 lm
46960000	CorePro LEDtube 1500mm HO 24W 840 T8	240 degree(s)	4000 K	840	2,700 lm
32531900	CorePro LEDtube 600mm 8W 840 T8	240 degree(s)	4000 K	840	800 lm
32533300	CorePro LEDtube 600mm 8W 865 T8	240 degree(s)	6500 K	865	800 lm
32539500	CorePro LEDtube 1500mm 20W 840 T8	240 degree(s)	4000 K	840	2,200 lm
32541800	CorePro LEDtube 1500mm 20W 865 T8	240 degree(s)	6500 K	865	2,200 lm
41897400	CorePro LEDtube 1200mm UO 21.5W 840 T8	240 degree(s)	4000 K	840	2,400 lm
41899800	CorePro LEDtube 1200mm UO 21.5W 865 T8	240 degree(s)	6500 K	865	2,400 lm

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		
			Temperature (Nom)	Color Code	Luminous Flux
41901800	CorePro LEDtube 1500mm UO 31.5W 840 T8	240 degree(s)	4000 K	840	3,500 lm
41903200	CorePro LEDtube 1500mm UO 31.5W 865 T8	240 degree(s)	6500 K	865	3,500 lm
42103500	CorePro LEDtube 600mm HO 8W 840 T8	240 degree(s)	4000 K	840	900 lm
42105900	CorePro LEDtube 600mm HO 8W 865 T8	240 degree(s)	6500 K	865	900 lm
44807000	CorePro LEDtube 1200mm 15.5W 840 T8	240 degree(s)	4000 K	840	1,800 lm
46954900	CorePro LEDtube 1200mm 15.5W 840 T8	240 degree(s)	4000 K	840	1,800 lm
44807000	CorePro LEDtube 1200mm 15.5W 840 T8 CL	240 degree(s)	4000 K	840	1,800 lm
44809400	CorePro LEDtube 1200mm 15.5W 865 T8	240 degree(s)	6500 K	865	1,800 lm
46956300	CorePro LEDtube 1200mm 15.5W 865 T8	240 degree(s)	6500 K	865	1,800 lm
44809400	CorePro LEDtube 1200mm 15.5W 865 T8 CL	240 degree(s)	6500 K	865	1,800 lm
45977900	CorePro LEDtube 600mm 8W 840 T8	240 degree(s)	4000 K	840	800 lm
45977900	CorePro LEDtube 600mm 8W 840 T8 CL	240 degree(s)	4000 K	840	800 lm
45979300	CorePro LEDtube 600mm 8W 865 T8	240 degree(s)	6500 K	865	800 lm
45979300	CorePro LEDtube 600mm 8W 865 T8 CL	240 degree(s)	6500 K	865	800 lm
45981600	CorePro LEDtube 1500mm 20W 840 T8	240 degree(s)	4000 K	840	2,200 lm
45981600	CorePro LEDtube 1500mm 20W 840 T8 CL	240 degree(s)	4000 K	840	2,200 lm

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux
			Temperature (Nom)	Color Code	
45983000	CorePro LEDtube 1500mm 20W 865 T8	240 degree(s)	6500 K	865	2,200 lm
45983000	CorePro LEDtube 1500mm 20W 865 T8 CL	240 degree(s)	6500 K	865	2,200 lm
48638600	CorePro LEDtube 600mm 8W 830 T8	240 degree(s)	3000 K	830	750 lm
48640900	CorePro LEDtube 1200mm 15.5W 830 T8	240 degree(s)	3000 K	830	1,700 lm
48642300	CorePro LEDtube 1500mm 20W 830 T8	240 degree(s)	3000 K	830	2,050 lm
48644700	CorePro LEDtube 600mm HO 8W 830 T8	240 degree(s)	3000 K	830	850 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
32535700	CorePro LEDtube 1200mm 14.5W840	14.5 W
32537100	CorePro LEDtube 1200mm 14.5W865	14.5 W
31692800	CorePro LEDtube 1800mm 21W 840 T8	21 W
80611100	CorePro LEDtube 1200mm HO 18W 865 T8	18 W
47558800	CorePro LEDtube 1200mm HO 18W 865 T8	18 W
80613500	CorePro LEDtube 1200mm HO 18W 840 T8	18 W
46958700	CorePro LEDtube 1200mm HO 18W 840 T8	18 W
80615900	CorePro LEDtube 1500mm HO 24W 865 T8	24 W
47560100	CorePro LEDtube 1500mm HO 24W 865 T8	24 W
80617300	CorePro LEDtube 1500mm HO 24W 840 T8	24 W
46960000	CorePro LEDtube 1500mm HO 24W 840 T8	24 W
32531900	CorePro LEDtube 600mm 8W 840 T8	8 W
32533300	CorePro LEDtube 600mm 8W 865 T8	8 W
32539500	CorePro LEDtube 1500mm 20W 840 T8	20 W
32541800	CorePro LEDtube 1500mm 20W 865 T8	20 W
41897400	CorePro LEDtube 1200mm UO 21.5W 840 T8	21.5 W
41899800	CorePro LEDtube 1200mm UO 21.5W 865 T8	21.5 W
41901800	CorePro LEDtube 1500mm UO 31.5W 840 T8	31.5 W
41903200	CorePro LEDtube 1500mm UO 31.5W 865 T8	31.5 W
42103500	CorePro LEDtube 600mm HO 8W 840 T8	8 W
42105900	CorePro LEDtube 600mm HO 8W 865 T8	8 W
44807000	CorePro LEDtube 1200mm 15.5W 840 T8	15.5 W

Temperature

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Luminous Flux
			Temperature (Nom)	Color Code	
48646100	CorePro LEDtube 1200mm HO 18W 830 T8	240 degree(s)	3000 K	830	1,850 lm
48648500	CorePro LEDtube 1500mm HO 24W 830 T8	240 degree(s)	3000 K	830	2,500 lm
48650800	CorePro LEDtube 1200mm UO 21.5W 830 T8	240 degree(s)	3000 K	830	2,250 lm
48652200	CorePro LEDtube 1500mm UO 31.5W 830 T8	240 degree(s)	3000 K	830	3,320 lm

Order Code	Full Product Name	Power Consumption
46954900	CorePro LEDtube 1200mm 15.5W 840 T8	15.5 W
44807000	CorePro LEDtube 1200mm 15.5W 840 T8 CL	15.5 W
44809400	CorePro LEDtube 1200mm 15.5W 865 T8	15.5 W
46956300	CorePro LEDtube 1200mm 15.5W 865 T8	15.5 W
44809400	CorePro LEDtube 1200mm 15.5W 865 T8 CL	15.5 W
45977900	CorePro LEDtube 600mm 8W 840 T8	8 W
45977900	CorePro LEDtube 600mm 8W 840 T8 CL	8 W
45979300	CorePro LEDtube 600mm 8W 865 T8	8 W
45979300	CorePro LEDtube 600mm 8W 865 T8 CL	8 W
45981600	CorePro LEDtube 1500mm 20W 840 T8	20 W
45981600	CorePro LEDtube 1500mm 20W 840 T8 CL	20 W
45983000	CorePro LEDtube 1500mm 20W 865 T8	20 W
45983000	CorePro LEDtube 1500mm 20W 865 T8 CL	20 W
48638600	CorePro LEDtube 600mm 8W 830 T8	8 W
48640900	CorePro LEDtube 1200mm 15.5W 830 T8	15.5 W
48642300	CorePro LEDtube 1500mm 20W 830 T8	20 W
48644700	CorePro LEDtube 600mm HO 8W 830 T8	8 W
48646100	CorePro LEDtube 1200mm HO 18W 830 T8	18 W
48648500	CorePro LEDtube 1500mm HO 24W 830 T8	24 W
48650800	CorePro LEDtube 1200mm UO 21.5W 830 T8	21.5 W
48652200	CorePro LEDtube 1500mm UO 31.5W 830 T8	31.5 W

CorePro LEDtube EM/Mains T8

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
32535700	CorePro LEDtube 1200mm 14.5W840	-20 °C to 45 °C	40 °C
32537100	CorePro LEDtube 1200mm 14.5W865	-20 °C to 45 °C	40 °C
31692800	CorePro LEDtube 1800mm 21W 840 T8	-20 °C to 45 °C	60 °C
80611100	CorePro LEDtube 1200mm HO 18W 865 T8	-20 °C to 45 °C	60 °C
47558800	CorePro LEDtube 1200mm HO 18W 865 T8	-20 °C to 45 °C	60 °C
80613500	CorePro LEDtube 1200mm HO 18W 840 T8	-20 °C to 45 °C	60 °C
46958700	CorePro LEDtube 1200mm HO 18W 840 T8	-20 °C to 45 °C	60 °C
80615900	CorePro LEDtube 1500mm HO 24W 865 T8	-20 °C to 45 °C	55 °C
47560100	CorePro LEDtube 1500mm HO 24W 865 T8	-20 °C to 45 °C	55 °C
80617300	CorePro LEDtube 1500mm HO 24W 840 T8	-20 °C to 45 °C	55 °C
46960000	CorePro LEDtube 1500mm HO 24W 840 T8	-20 °C to 45 °C	55 °C
32531900	CorePro LEDtube 600mm 8W 840 T8	-20 °C to 45 °C	50 °C
32533300	CorePro LEDtube 600mm 8W 865 T8	-20 °C to 45 °C	50 °C
32539500	CorePro LEDtube 1500mm 20W 840 T8	-20 °C to 45 °C	60 °C
32541800	CorePro LEDtube 1500mm 20W 865 T8	-20 °C to 45 °C	60 °C
41897400	CorePro LEDtube 1200mm UO 21.5W 840 T8	-20 to +45 °C	50 °C
41899800	CorePro LEDtube 1200mm UO 21.5W 865 T8	-20 to +45 °C	50 °C
41901800	CorePro LEDtube 1500mm UO 31.5W 840 T8	-20 to +45 °C	55 °C
41903200	CorePro LEDtube 1500mm UO 31.5W 865 T8	-20 to +45 °C	55 °C
42103500	CorePro LEDtube 600mm HO 8W 840 T8	-20 °C to 45 °C	45 °C
42105900	CorePro LEDtube 600mm HO 8W 865 T8	-20 °C to 45 °C	45 °C
44807000	CorePro LEDtube 1200mm 15.5W 840 T8	-20 °C to 45 °C	60 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
46954900	CorePro LEDtube 1200mm 15.5W 840 T8	-20 °C to 45 °C	60 °C
44807000	CorePro LEDtube 1200mm 15.5W 840 T8 CL	-20 °C to 45 °C	60 °C
44809400	CorePro LEDtube 1200mm 15.5W 865 T8	-20 °C to 45 °C	60 °C
46956300	CorePro LEDtube 1200mm 15.5W 865 T8	-20 °C to 45 °C	60 °C
44809400	CorePro LEDtube 1200mm 15.5W 865 T8 CL	-20 °C to 45 °C	60 °C
45977900	CorePro LEDtube 600mm 8W 840 T8	-20 °C to 45 °C	50 °C
45977900	CorePro LEDtube 600mm 8W 840 T8 CL	-20 °C to 45 °C	50 °C
45979300	CorePro LEDtube 600mm 8W 865 T8	-20 °C to 45 °C	50 °C
45979300	CorePro LEDtube 600mm 8W 865 T8 CL	-20 °C to 45 °C	50 °C
45981600	CorePro LEDtube 1500mm 20W 840 T8	-20 °C to 45 °C	60 °C
45981600	CorePro LEDtube 1500mm 20W 840 T8 CL	-20 °C to 45 °C	60 °C
45983000	CorePro LEDtube 1500mm 20W 865 T8	-20 °C to 45 °C	60 °C
45983000	CorePro LEDtube 1500mm 20W 865 T8 CL	-20 °C to 45 °C	60 °C
48638600	CorePro LEDtube 600mm 8W 830 T8	-20 °C to 45 °C	50 °C
48640900	CorePro LEDtube 1200mm 15.5W 830 T8	-20 °C to 45 °C	60 °C
48642300	CorePro LEDtube 1500mm 20W 830 T8	-20 °C to 45 °C	60 °C
48644700	CorePro LEDtube 600mm HO 8W 830 T8	-20 °C to 45 °C	45 °C
48646100	CorePro LEDtube 1200mm HO 18W 830 T8	-20 °C to 45 °C	60 °C
48648500	CorePro LEDtube 1500mm HO 24W 830 T8	-20 °C to 45 °C	55 °C
48650800	CorePro LEDtube 1200mm UO 21.5W 830 T8	-20 to +45 °C	50 °C
48652200	CorePro LEDtube 1500mm UO 31.5W 830 T8	-20 to +45 °C	55 °C


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
32535700	CorePro LEDtube 1200mm 14.5W840	15 kWh


Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
32537100	CorePro LEDtube 1200mm 14.5W865	15 kWh

CorePro LEDtube EM/Mains T8


Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
31692800	CorePro LEDtube 1800mm 21W 840 T8	21 kWh
80611100	CorePro LEDtube 1200mm HO 18W 865 T8	18 kWh
47558800	CorePro LEDtube 1200mm HO 18W 865 T8	18 kWh
80613500	CorePro LEDtube 1200mm HO 18W 840 T8	18 kWh
46958700	CorePro LEDtube 1200mm HO 18W 840 T8	18 kWh
80615900	CorePro LEDtube 1500mm HO 24W 865 T8	24 kWh
47560100	CorePro LEDtube 1500mm HO 24W 865 T8	24 kWh
80617300	CorePro LEDtube 1500mm HO 24W 840 T8	24 kWh
46960000	CorePro LEDtube 1500mm HO 24W 840 T8	24 kWh
32531900	CorePro LEDtube 600mm 8W 840 T8	8 kWh
32533300	CorePro LEDtube 600mm 8W 865 T8	8 kWh
32539500	CorePro LEDtube 1500mm 20W 840 T8	20 kWh
32541800	CorePro LEDtube 1500mm 20W 865 T8	20 kWh
41897400	CorePro LEDtube 1200mm UO 21.5W 840 T8	22 kWh
41899800	CorePro LEDtube 1200mm UO 21.5W 865 T8	22 kWh
41901800	CorePro LEDtube 1500mm UO 31.5W 840 T8	32 kWh
41903200	CorePro LEDtube 1500mm UO 31.5W 865 T8	32 kWh
42103500	CorePro LEDtube 600mm HO 8W 840 T8	8 kWh
42105900	CorePro LEDtube 600mm HO 8W 865 T8	8 kWh
44807000	CorePro LEDtube 1200mm 15.5W 840 T8	16 kWh
46954900	CorePro LEDtube 1200mm 15.5W 840 T8	16 kWh
44807000	CorePro LEDtube 1200mm 15.5W 840 T8 CL	16 kWh
44809400	CorePro LEDtube 1200mm 15.5W 865 T8	16 kWh
46956300	CorePro LEDtube 1200mm 15.5W 865 T8	16 kWh
44809400	CorePro LEDtube 1200mm 15.5W 865 T8 CL	16 kWh
45977900	CorePro LEDtube 600mm 8W 840 T8	8 kWh
45977900	CorePro LEDtube 600mm 8W 840 T8 CL	8 kWh
45979300	CorePro LEDtube 600mm 8W 865 T8	8 kWh
45979300	CorePro LEDtube 600mm 8W 865 T8 CL	8 kWh
45981600	CorePro LEDtube 1500mm 20W 840 T8	20 kWh
45981600	CorePro LEDtube 1500mm 20W 840 T8 CL	20 kWh
45983000	CorePro LEDtube 1500mm 20W 865 T8	20 kWh
45983000	CorePro LEDtube 1500mm 20W 865 T8 CL	20 kWh
48638600	CorePro LEDtube 600mm 8W 830 T8	8 kWh
48640900	CorePro LEDtube 1200mm 15.5W 830 T8	16 kWh
48642300	CorePro LEDtube 1500mm 20W 830 T8	20 kWh
48644700	CorePro LEDtube 600mm HO 8W 830 T8	8 kWh
48646100	CorePro LEDtube 1200mm HO 18W 830 T8	18 kWh
48648500	CorePro LEDtube 1500mm HO 24W 830 T8	24 kWh
48650800	CorePro LEDtube 1200mm UO 21.5W 830 T8	22 kWh
48652200	CorePro LEDtube 1500mm UO 31.5W 830 T8	32 kWh




CorePro LEDtube EM/Mains T8




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°




(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°



(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°





(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°



(cd/1000lm) 0° 150° 0-180° 180° 90-270° 150°

CorePro LEDtube EM/Mains T8



CorePro LEDtube EM/Mains T8

