



Product Description

MASTER PL-C Xtra 2 Pin

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Extra long life
- Longer lifetime and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
- Optimal light performance for long operation per switch on

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Significant reduction of early failures
- Extra long and reliable lifetime

Application

- Designed for general or supplementary lighting in professional environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps
- Suitable for use in applications where maintenance costs are high (high ceilings, difficult to reach): department stores, supermarkets, warehouses, production halls and public areas

MASTER PL-C Xtra 2 Pin

Versions




26W, G24d-3, 2P



18W, G24d-2, 2P

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C Xtra 18W/ 840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	109.7 mm	128.0 mm	150.4 mm
MASTER PL-C Xtra 26W/ 840/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.7 mm	149.0 mm	171.4 mm

MASTER PL-C Xtra 2 Pin

Approval and Application

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	3.0 mg

Controls and Dimming

Dimmable	No
----------	----

General Information

Life To 10% Failures (Nom)	12000 h
Life To 50% Failures (Nom)	16000 h
LSF 12000 h Rated	90 %
LSF 16000 h Rated	50 %
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	97 %
LSF 8000 h Rated	95 %

Light Technical

Color Code	840
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color Rendering Index (Nom)	82
LLMF 12000 h Rated	79 %
LLMF 16000 h Rated	78 %
LLMF 2000 h Rated	92 %
LLMF 20000 h Rated	77 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	83 %
LLMF 8000 h Rated	81 %

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
89886970	MASTER PL-C XTRA 26W/840/2P 1CT/5X10BOX	32 kWh
95030770	MASTER PL-C XTRA 18W/840/2P 1CT/5X10BOX	22 kWh

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
89886970	MASTER PL-C XTRA 26W/840/2P 1CT/5X10BOX	0.325 A	26.5 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
95030770	MASTER PL-C XTRA 18W/840/2P 1CT/5X10BOX	0.220 A	17.9 W

General Information

Order Code	Full Product Name	Cap-Base
89886970	MASTER PL-C XTRA 26W/840/2P 1CT/5X10BOX	G24D-3

Order Code	Full Product Name	Cap-Base
95030770	MASTER PL-C XTRA 18W/840/2P 1CT/5X10BOX	G24D-2

Light Technical

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
89886970	MASTER PL-C XTRA 26W/840/2P 1CT/5X10BOX	68 lm/W	1800 lm	1800 lm

MASTER PL-C Xtra 2 Pin

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
95030770	MASTER PL-C XTRA 18W/840/2P 1CT/ 5X10BOX	67 lm/W	1200 lm	1200 lm

