



Product Description

MASTER PL-C Xtra 2 Pin

Energy-saving compact fluorescent lamps Compact long-arc low-pressure mercury discharge lamp Envelope consists of 4 parallel narrow fluorescent tubes

Benefits

- Extra long life
- Longer lifetime and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
- Optimal light performance for long operation per switch on

Features

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Significant reduction of early failures
- Extra long and reliable lifetime

Application


- Designed for general or supplementary lighting in professional environments
- Recessed or surface-mounted downlighters, wall units, table lamps and pendant lamps
- Suitable for use in applications where maintenance costs are high (high ceilings, difficult to reach): department stores, supermarkets, warehouses, production halls and public areas

MASTER PL-C Xtra 2 Pin

Versions



Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-C Xtra 26W/ 830/2P 1CT/5X10BOX	27.1 mm	27.1 mm	130.7 mm	149.0 mm	171.4 mm

