



Product Description

PL-Q 2 Pin

Compact fluorescent lamps with a quadrant-like shape

Benefits

- High light quality and optimum lumen output provide increased value for money
- Energy-saving light with good colour rendering
- Long service lifetime
- The Philips Lighting stamp of quality

Features

- Retrofit in already installed 2D luminaires
- Assembled with the same high-quality components as all other Philips CFL-NI lamps

Application


- Ideal for applications such as
- corridors
- toilets
- stairwells
- reception areas

PL-Q 2 Pin

Versions



Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 16W/ 827/2P 1CT/ 10BOX	40 mm	13.7 mm	27.0 mm	138 mm	49 mm	40.5 mm	135 mm

