



The alternative!

PL-Q 2 Pin

PL-Q is an efficient, square-shaped compact fluorescent lamp, typically used in decorative-lighting luminaires. While offering the advantage of energy-efficient operation, it also provides design freedom for flat ceiling or wall fixtures in particular, due to its low built-in height and uniform spread of light. The 2-pin version is designed for operation on electromagnetic gear.

优点

- Low built-in height
- Multiple light color choice
- Good color rendering (CRI >80)

特点

- 2-pin base with a housing incorporating the special instant starter and capacitor
- Fluorescent tri-phosphor technology

应用

- Ideal for applications such as corridors, toilets, stairwells and reception areas

安全提示

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

PL-Q 2 Pin

Versions

