



Product Description

MASTER PL-T 2 Pin

Energy saving compact fluorescent lamp Compact long-arc low-pressure mercury discharge lamp Envelope consists of 6 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- Substantial more light (about 15% more) per light point than common
- Long life and sustainable light output

Features

- 2-pin base with a housing incorporating the lamp glow switch starter
- Fast light run up
- Philips invented bridge technology applied
- Dimming is not possible

Application

- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units

MASTER PL-T 2 Pin

Versions




18W, GX24d-2, 2P




26W, GX24d-3, 2P

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 26W/840/2P 1CT/ 5X10BOX	41 mm	86.7 mm	111.0 mm	134.2 mm
MASTER PL-T 26W/830/2P 1CT/ 5X10BOX	41 mm	86.7 mm	111.0 mm	134.2 mm



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/840/2P 1CT/ 5X10BOX	41 mm	71.8 mm	96.0 mm	119.2 mm
MASTER PL-T 18W/830/2P 1CT/ 5X10BOX	41 mm	71.8 mm	96.0 mm	119.2 mm

MASTER PL-T 2 Pin

Approval and Application

Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	1.4 mg

Controls and Dimming

Dimmable	No
----------	----

General Information

Life To 10% Failures (Nom)	6500 h
Life To 50% Failures (Nom)	10000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	98 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	78 %

Light Technical

LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	81 %

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
61050870	MASTER PL-T 18W/830/2P 1CT/5X10CC	22 kWh
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	22 kWh
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	32 kWh
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	32 kWh

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
61050870	MASTER PL-T 18W/830/2P 1CT/5X10CC	0.225 A	18.0 W
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	0.225 A	18 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	0.335 A	26.0 W
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	0.335 A	26.0 W

General Information

Order Code	Full Product Name	Cap-Base
61050870	MASTER PL-T 18W/830/2P 1CT/5X10CC	GX24D-2
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	GX24D-2

Order Code	Full Product Name	Cap-Base
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	GX24D-3
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	GX24D-3

Light Technical (1/2)

Order Code	Full Product Name	Color Code	Color Designation	Correlated	
				Color Temperature (Nom)	Color Rendering Index (Nom)
61050870	MASTER PL-T 18W/830/2P 1CT/5X10CC	830	Warm White (WW)	3000 K	>80
61061470	MASTER PL-T 18W/840/2P 1CT/5X10CC	840	Cool White (CW)	4000 K	82

Order Code	Full Product Name	Color Code	Color Designation	Correlated	
				Color Temperature (Nom)	Color Rendering Index (Nom)
61102470	MASTER PL-T 26W/830/2P 1CT/5X10CC	830	Warm White (WW)	3000 K	>80
61113070	MASTER PL-T 26W/840/2P 1CT/5X10CC	840	Cool White (CW)	4000 K	82

Light Technical (2/2)

MASTER PL-T 2 Pin

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
61050870	MASTER PL-T 18W/ 830/2P 1CT/5X10CC	67 lm/W	1200 lm	1200 lm
61061470	MASTER PL-T 18W/ 840/2P 1CT/5X10CC	67 lm/W	1200 lm	1200 lm

Order Code	Full Product Name	Luminous		
		Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
61102470	MASTER PL-T 26W/ 830/2P 1CT/5X10CC	66 lm/W	1800 lm	1725 lm
61113070	MASTER PL-T 26W/ 840/2P 1CT/5X10CC	66 lm/W	1800 lm	1725 lm

