PHILIPS Lighting



Product Description

MASTER PL-T 4 Pin

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Benefits

- \cdot Optimal light performance for short or long operation per switch on
- More light (about 15% more) per light point than common
- Long life and sustainable light output

Features

- 4-pin base without glow switch starter and capacitor
- Fast light run up under all circumstances
- Philips invented bridge technology applied
- Dimming is possible

Application

- Designed for general or supplementary lighting in professional and semiprofessional environments
- Ideal for use in recessed or surface mounted downlighters, wall units, outdoor lighting
- First choice for short switching cycles, emergency lighting and deep dimming

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-T 4 Pin

Versions





LPPR PLT4PN 18W

LPPR PLT4PN 32W

Dimensional drawing





Light Technical	
Colour rendering index (CRI)	80
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mercury (Hg) content (max.)	1.4 mg
Mercury (Hg) content (nom.)	1.4 mg

General Information

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/830/4P 1CT/5X10BOX	41.0 mm	71.7 mm	96.0 mm	111.7 mm

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 32W/830/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm
MASTER PL-T 32W/840/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm

MASTER PL-T 4 Pin

Order Code	Full Product Name	Cap base	Order Code	Full Product Name	Cap base
61076870	MASTER PL-T 18W/830/4P 1CT/5X10CC	GX24q-2	61131470	MASTER PL-T 32W/840/4P 1CT/5X10CC	GX24q-3
61128470	MASTER PL-T 32W/830/4P 1CT/5X10CC	GX24q-3			

Light Technical

		Chromaticity	Chromaticity		Correlated Colour	Luminous efficacy	
Order Code	Full Product Name	Coordinate X (Nom)	Coordinate Y (Nom)	Colour designation	Temperature	(rated) (min.)	Luminous Flux
61076870	MASTER PL-T 18W/830/4P 1CT/	0.44	0.403	Warm White (WW)	3000 K	67 lm/W	1,150 lm
	5X10CC						
61128470	MASTER PL-T 32W/830/4P 1CT/	0.44	0.403	Warm White (WW)	3000 K	75 lm/W	2,350 lm
	5X10CC						
61131470	MASTER PL-T 32W/840/4P 1CT/	0.38	0.38	Cool White (CW)	4000 K	75 lm/W	2,350 lm
	5X10CC						

Operating and Electrical

		Lamp current				Lamp current	
Order Code	Full Product Name	(nom.)	Power Consumption	Order Code	Full Product Name	(nom.)	Power Consumption
61076870	MASTER PL-T 18W/830/4P 1CT/	0.225 A	18.0 W	61131470	MASTER PL-T 32W/840/4P 1CT/	0.320 A	32.0 W
	5X10CC				5X10CC		
61128470	MASTER PL-T 32W/830/4P 1CT/	0.320 A	32.0 W				
	5X10CC						

Approval and Application

		Energy consumption kWh/1,000
Order Code	Full Product Name	hours
61076870	MASTER PL-T 18W/830/4P 1CT/5X10CC	18 kWh
61128470	MASTER PL-T 32W/830/4P 1CT/5X10CC	32 kWh

		Energy consumption kWh/1,000
Order Code	Full Product Name	hours
61131470	MASTER PL-T 32W/840/4P 1CT/5X10CC	32 kWh



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.