



Product Description

MASTER PL-T 4 Pin

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Benefits

- Optimal light performance for short or long operation per switch on
- More light (about 15% more) per light point than common
- Long life and sustainable light output

Features

- 4-pin base without glow switch starter and capacitor
- Fast light run up under all circumstances
- Philips invented bridge technology applied
- Dimming is possible

Application




- Designed for general or supplementary lighting in professional and semi-professional environments
- Ideal for use in recessed or surface mounted downlighters, wall units, outdoor lighting
- First choice for short switching cycles, emergency lighting and deep dimming

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER PL-T 4 Pin

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/840/4P 1CT/ 5X10BOX	41.0 mm	71.7 mm	96.0 mm	111.7 mm

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 26W/830/4P 1CT/ 5X10BOX	41.0 mm	86.7 mm	111.0 mm	126.7 mm
MASTER PL-T 26W/840/4P 1CT/ 5X10BOX	41.0 mm	86.7 mm	111.0 mm	126.7 mm
MASTER PL-T 32W/830/4P 1CT/ 5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm
MASTER PL-T 32W/840/4P 1CT/ 5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 42W/830/4P 1CT/ 5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm
MASTER PL-T 42W/840/4P 1CT/ 5X10BOX	41.0 mm	120.7 mm	145.0 mm	160.7 mm

MASTER PL-T 4 Pin

Approval and application

Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg

Controls and dimming

Dimmable	Yes
----------	-----

General information

Life To 50% Failures Preheat (Nom)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %

Light technical

Colour Rendering Index (Nom)	80
LLMF 12000 h Rated	81 %
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	86 %
LLMF 8000 h Rated	84 %

Temperature

Design Temperature (Nom)	28 °C
--------------------------	-------

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	18 kWh
927914683071	MASTER PL-T 26W/830/4P 1CT/5X10BOX	28 kWh
927914684071	MASTER PL-T 26W/840/4P 1CT/5X10BOX	28 kWh
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	32 kWh
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	32 kWh
927914883071	MASTER PL-T 42W/830/4P 1CT/5X10BOX	42 kWh
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	42 kWh
927914983071	MASTER PL-T 57W/830/4P 1CT/5X10BOX	54 kWh
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	54 kWh

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	0.210 A	18.0 W
927914683071	MASTER PL-T 26W/830/4P 1CT/5X10BOX	0.300 A	27.2 W
927914684071	MASTER PL-T 26W/840/4P 1CT/5X10BOX	0.300 A	27.2 W
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	0.320 A	32.0 W
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	0.320 A	32.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Nom)
927914883071	MASTER PL-T 42W/830/4P 1CT/5X10BOX	0.320 A	42.0 W
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	0.320 A	42.0 W
927914983071	MASTER PL-T 57W/830/4P 1CT/5X10BOX	0.325 A	54.0 W
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	0.325 A	54.0 W

General information

Order Code	Full Product Name	Cap-Base
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	GX24Q-2
927914683071	MASTER PL-T 26W/830/4P 1CT/5X10BOX	GX24Q-3
927914684071	MASTER PL-T 26W/840/4P 1CT/5X10BOX	GX24Q-3
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	GX24Q-3
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	GX24Q-3

Order Code	Full Product Name	Cap-Base
927914883071	MASTER PL-T 42W/830/4P 1CT/5X10BOX	GX24Q-4
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	GX24Q-4
927914983071	MASTER PL-T 57W/830/4P 1CT/5X10BOX	GX24Q-5
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	GX24Q-5

Light technical (1/2)

MASTER PL-T 4 Pin

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour	Colour
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	0.38	0.38	840	Cool White (CW)
927914683071	MASTER PL-T 26W/830/4P 1CT/5X10BOX	0.44	0.403	830	Warm white (WW)
927914684071	MASTER PL-T 26W/840/4P 1CT/5X10BOX	0.38	0.38	840	Cool White (CW)
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	0.44	0.403	830	Warm white (WW)
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	0.38	0.38	840	Cool White (CW)

Order Code	Full Product Name	Chromaticity	Chromaticity	Colour	Colour
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Designation
927914883071	MASTER PL-T 42W/830/4P 1CT/5X10BOX	0.44	0.403	830	Warm white (WW)
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	0.38	0.38	840	Cool White (CW)
927914983071	MASTER PL-T 57W/830/4P 1CT/5X10BOX	0.44	0.403	830	Warm white (WW)
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	0.38	0.38	840	Cool White (CW)

Light technical (2/2)

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated)
		(K)	(lm/W)	(lm)	(lm)
927914484071	MASTER PL-T 18W/840/4P 1CT/5X10BOX	4000 K	67 lm/W	1150 lm	1200 lm
927914683071	MASTER PL-T 26W/830/4P 1CT/5X10BOX	3000 K	66 lm/W	1800 lm	1725 lm
927914684071	MASTER PL-T 26W/840/4P 1CT/5X10BOX	4000 K	66 lm/W	1800 lm	1725 lm
927914783071	MASTER PL-T 32W/830/4P 1CT/5X10BOX	3000 K	75 lm/W	2350 lm	2400 lm
927914784071	MASTER PL-T 32W/840/4P 1CT/5X10BOX	4000 K	75 lm/W	2350 lm	2400 lm

Order Code	Full Product Name	Correlated Colour Temperature (Nom)	Luminous Efficacy (rated) (Min)	Luminous Flux (Nom)	Luminous Flux (Rated)
		(K)	(lm/W)	(lm)	(lm)
927914883071	MASTER PL-T 42W/830/4P 1CT/5X10BOX	3000 K	74 lm/W	3100 lm	3050 lm
927914884071	MASTER PL-T 42W/840/4P 1CT/5X10BOX	4000 K	74 lm/W	3100 lm	3050 lm
927914983071	MASTER PL-T 57W/830/4P 1CT/5X10BOX	3000 K	75 lm/W	4000 lm	4200 lm
927914984071	MASTER PL-T 57W/840/4P 1CT/5X10BOX	4000 K	75 lm/W	4000 lm	4200 lm

