



Combining superior high lumen, design & performance

Twist High Lumen

Energy saving lamp in spiral shape, with superior performance (long life, high switching) and high lumen warm bright light. Perfectly suitable to be used in places where high lumen is required, and the lamp is directly visible.

Benefits

- Simple installation – no ballast needed
- Save your money with long life-time
- Perfect energy-saving solution for mercury lamps replacement

Features

- Long-Life and Energy saving alternative to Incandescent lamps
- Suitable for frequent switching
- Flawless ignition at -10°C and up
- Ambient temperature range to ensure almost constant light output: 0 - 50°C

Application

- Designed primarily for professional applications (hotels, restaurants, shops), ideally high-bay type indoor applications; not suitable for household room illumination
- Enclosed fixtures required for outdoor applications
- Not suitable for use with dimmers or electronic gear


Twist High Lumen

Versions



105 W E40

Dimensional drawing



Product	D (max)	C (max)	F (max)
High Lumen Twister 105W CDL E40 HV 1CT/6	102 mm	301 mm	88.5 mm

