



# Energy savings without changing a ballast!

## Energy Advantage CDM Lamps with AllStart Technology E-Rated

Philips Energy Advantage CDM AllStart E-rated lamps provide energy savings without compromising light quality.

### Benefits

- Energy savings up to 17%\*
- Reduced maintenance and recycling costs
- Long life: 20,000 hours rated average life
- \* 145W CDM lamp with AllStart Technology compared to 175W metal halide lamp.

### Features

- Excellent color rendering of CRI >80
- Crisp white light
- Use in enclosed fixtures only
- Direct retrofit lamp to both probe and pulse start magnetic 175W ballasts (not suitable for operation on electronic ballasts)

### Application

- Ideal for low-ceiling industrial, retail and distribution centers as well as outdoor applications


# Energy Advantage CDM Lamps with AllStart Technology E-Rated

## Versions



E26, ED-17, Clear

## Dimensional drawing



Product	D	D	L (min)	L (max)	L	C
CDM145/U/4K/ED17 EA Allstart	2.125 in	54 mm	83 mm	89 mm	86 mm	5.4 in

