



Optimal lamp performance in standard fixtures

MasterColor CDM Elite MW Mogul Base

Philips MasterColor CDM Elite MW Mogul Base Lamps. A high-performing protected "O" rated ceramic lamp is now available in familiar bulb shapes, without sacrificing lamp performance.

Benefits

- Familiar ED28 and ED37 bulb shapes – can be used directly on existing fixtures
- Open-rated, EX39 mogul base used in either enclosed or open fixtures
- Operates on the Philips Advance electronic ballast IZTMH 210-315

Features

- Excellent lamp performance with 85% lumen maintenance and 20,000 hours rated average life (1)
- Up to 108 lumens per watt for the lamp or 100 lumens per watt for the system.
- Excellent color rendering of CRI 90+
- Crisp white light

Application

- Ideal for architectural facade lighting, illumination of pedestrian areas, indoor retail outlets, warehouses, manufacturing facilities.


MasterColor CDM Elite MW Mogul Base

Versions



EX39 ED37

Dimensional drawing



Product	D	D	L (min)	L (max)	L	C (max)
MasterColor CDM Elite CDM 315/U/O/4K ED37 6PK	4.625 in	118 mm	174 mm	182 mm	178 mm	288 mm

