



The next generation of white light

MasterColor CDM-T Elite Med Wattage

The Philips MasterColor Elite MW system offers an unrivalled level of light quality and performance. The lamp's sparkling white light creates a natural ambience and really brings out the best in all different types of colors. In addition, the high efficiency of the lamp and ballast together means reduced energy use and a lower cost of ownership compared to a 400W Metal Halide HID system.

Benefits

- Excellent color rendering of 90+ CRI.
- Philips "Green Flagship Product" - Low mercury, no lead.
- New socket design provides higher optical efficiency.

Features

- Significant upgrade opportunity over traditional HID systems.
- Viable alternative to fluorescent options.
- Excellent color quality and consistent light output from beginning to end.
- Being 50% smaller than traditional metal halide lamps, MasterColor CDM Elite MW gives freedom in optic and luminaire design.
- Sparkling properties of white light create a more natural and inviting ambience.
- 210 & 315 Watt, 3000 & 4200 color versions. Each powered by a Philips Advance e-Vision electronic ballast.

Application

- Ideal for architectural facade lighting, illumination of pedestrian areas, indoor retail outlets, warehouses, manufacturing facilities.


MasterColor CDM-T Elite Med Wattage

Versions




PGZX18., T12, Clear, Protected

Dimensional drawing



Product	D	D	C
CDM T12 ELITE 210W/942/U/O NA	1.5 in	38 mm	193 mm

Light Distribution Diagrams



CDM-T Elite MW 210W /942

MasterColor CDM-T Elite Med Wattage

