



MasterColor CDM ED17 Standard

MasterColor CDM ED17 Standard

Energy savings without changing a ballast! A high-efficiency enclosed E-rated CDM lighting solution that provides energy savings without compromising light quality.

Benefits

- Environmentally Responsible TCLP* Compliant ALTO® Lamp Technology.
- High lamp efficacy (up to 95 LPW)
- Energy-efficient alternative to incandescent/halogen.
- * The TCLP is the US EPA's Toxicity Characteristic Leaching Procedure.

Features

- Excellent Color Rendering.
- Superior Color Stability Over Life.
- Total Cost of Ownership Benefits.
- Sustainable lighting solution with ALTO Lamp Technology.
- Available in 50, 70, 100, and 150 watt with 3000K & 4000K color temperatures.

Application

- Ideal for general lighting, downlighting, and flood lighting.


MasterColor CDM ED17 Standard

Versions



E26, ED-17, Clear

Dimensional drawing



Product	D	C (max)
MHC150/U/M/4K ALTO 12PK	2.125 in	5.438 in

