



# Reduce maintenance costs

## Ceramalux ALTO Non-Cycling

Philips Ceramalux High Pressure Sodium Non-Cycling Lamps are a better value than standard high pressure sodium lamps, with longer life and reduced maintenance cost.

### Benefits

- More resistant to outages caused by vibration and line voltage fluctuations.
- 90% lumen maintenance.
- Sustainable lighting solution - up to 90% less mercury than standard Philips Ceramalux HPS lamps and lead free.

### Features

- Rated average life of 30,000 hours\*
- Direct replacement for standard HPS lamps
- 200, 250 and 400 Watts available in the ED18 mogul base / 50, 70, 100 and 150 Watts available in the ED 23-1/2 mogul base / 1000 Watts available in the ED 25 mogul base.
- \* Rated average life is the life obtained, on the average, from large representative groups of lamps in laboratory tests under controlled conditions at 10 or more operating hours per start. Approximate lumen output at 40% of rated life. It is based on survival of 65% of the lamps and allows for individual lamps or groups of lamps to vary considerably from the average.

### Application

- Ideal for street and roadway lighting, parking lots and garages, warehouses and manufacturing facilities where lower maintenance costs are desired.

# Ceramalux ALTO Non-Cycling

## Versions





E39, ED-23 1/2, Clear



E39, ED-18, Clear

## Dimensional drawing



Product	D	L	C (max)
C70S62/ALTO NC HPS 12PK	2.94 in	5.000 in	7.75 in

Product	D	L	C (max)
C250S50/ALTO NC HPS 12PK	2.25 in	5.750 in	9.75 in

# Ceramalux ALTO Non-Cycling

## General Information

Cap-Base	E39
Main Application	Street Lighting (S)
Operating Position	UNIVERSAL

## Luminaire Design Requirements

Bulb Temperature (Max)	400 °C
------------------------	--------

## Light Technical

Chromaticity Coordinate X (Nom)	0.523
Color Rendering Index (Nom)	21

## Mechanical and Housing

Bulb Finish	Clear
Bulb Material	Hard Glass

## Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)	Picogram Per Lumen Hour
928601155990	C70S62/ALTO NC HPS 12PK	1.4 mg	8.3 pg/lm.h
928601156190	C250S50/ALTO NC HPS 12PK	3.4 mg	4.4 pg/lm.h

## Operating and Electrical (1/2)

Order Code	Full Product Name	Lamp			
		Current (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928601155990	C70S62/ALTO NC HPS 12PK	1.45 A	60 V	44 V	52 V

Order Code	Full Product Name	Lamp			
		Current (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)
928601156190	C250S50/ALTO NC HPS 12PK	1.8 A	120 V	90 V	100 V

## Operating and Electrical (2/2)

Order Code	Full Product Name	Re-Ignition Time (Min) (Max)
928601155990	C70S62/ALTO NC HPS 12PK	5 min

Order Code	Full Product Name	Re-Ignition Time (Min) (Max)
928601156190	C250S50/ALTO NC HPS 12PK	2 min

## Light Technical (1/2)

Order Code	Full Product Name	Chromaticity Coordinate Y (Nom)	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Min)	Luminous Efficacy (rated) (Nom)
			(Nom)	(Min)	(Nom)
928601155990	C70S62/ALTO NC HPS 12PK	0.425	2150 K	79 lm/W	90 lm/W

Order Code	Full Product Name	Chromaticity Coordinate Y (Nom)	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Min)	Luminous Efficacy (rated) (Nom)
			(Nom)	(Min)	(Nom)
928601156190	C250S50/ALTO NC HPS 12PK	0.415	2100 K	102 lm/W	114 lm/W

## Light Technical (2/2)

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
		(Nom)	(Min)	(Nom)
928601155990	C70S62/ALTO NC HPS 12PK	5670 lm	5500 lm	6300 lm

Order Code	Full Product Name	Design Mean Lumens	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
		(Nom)	(Min)	(Nom)
928601156190	C250S50/ALTO NC HPS 12PK	25650 lm	25600 lm	28500 lm

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928601155990	C70S62/ALTO NC HPS 12PK	ED-23 1/2

Order Code	Full Product Name	Bulb Shape
928601156190	C250S50/ALTO NC HPS 12PK	ED-18

## Ceramalux ALTO Non-Cycling

