



High Pressure Metal Halide Lamps

Double-Ended Metal Halide

With their excellent color rendering properties, these High Pressure Metal Halide Lamps are ideal light sources for accent lighting in indoor applications. The outer bulb of the double-ended metal halide lamp is made of heat-resistant quartz. The double-ended construction, in combination with the small tubular quartz outer envelope, makes it possible to use these lamps in small luminaires with special optics.

Benefícios

• --

Características

- Immediate re-ignition is possible with special ignitors generating 25kV.
- Available in Color temperatures of 4000K and 4200K.
- Available in 1800W.

Aplicação


- Ideal for use in small luminaires.

Double-Ended Metal Halide

Versions



Desenho dimensional



Product	D (max)	O	X	A	C (max)
MASTER MHN-SA 2000W/956 400V XW HO UNP/1	41 mm	25 mm	34 mm	226 mm	369 mm



© 2019 Signify Holding Todos os direitos reservados. Signify não oferece qualquer representação ou garantia quanto à precisão ou à integridade das informações incluídas aqui e não se responsabiliza por qualquer ação em função disso.

As informações apresentadas neste documento não se destinam a qualquer oferta comercial e não compõem parte de qualquer cotação ou contrato, a menos que seja acordado pela Signify. Todas as marcas comerciais são de propriedade da Signify Holding ou de seus respectivos proprietários.

www.lighting.philips.com

2019, Abril 17 - Dados sujeitos a alteração