



# AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

## AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

### Benefits

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

### Features

- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

### Application

- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only


# AspiraVision Compact for CDM

## Versions



GPPR IAVC 0002

## Dimensional drawing



| Product                                   | D1     | C1      | A1       | A2      | B1      | B2      |
|-------------------------------------------|--------|---------|----------|---------|---------|---------|
| HID-AV C 35-70 /S CDM<br>220-240V 50/60Hz | 4.5 mm | 32.1 mm | 110.0 mm | 98.5 mm | 75.0 mm | 63.5 mm |

