



AspiraVision Compact (35, 50 & 70 W) for CDM – The smart electronic gear

AspiraVision Compact for CDM

AspiraVision is the mark of excellence in HID electronic gear technology – high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

优点

- SOFT START allows installation with fewer circuit breakers; Loop Through allows faster, cost-efficient installation
- Longer lifetime
- Driver can be set to 35, 50 or 70 W with the integrated switch, which means there is no need to replace the driver if the installation requires lower or higher-wattage lamps in the future

特点


- SOFT START
- Loop Through (in independent version)
- Improved thermal performance
- Low electromagnetic interference
- Voltage drop detection

应用


- Accent and decorative lighting for shops, public spaces, lobbies and offices
- Suitable for indoor use only

AspiraVision Compact for CDM

Versions



二维绘图



Product	D1	C1	A1	A2	B1	B2
HID-AV C 35-70 /S	4.5 mm	32.1 mm	110.0 mm	98.5 mm	75.0 mm	63.5 mm
CDM 220-240V						
50/60Hz						

Product	D1	C1	A1	A2	B1
HID-AV C 35-70 /I CDM	4.8 mm	34.7 mm	189.2 mm	170.7 mm	83.5 mm
220-240V 50/60Hz					

运营和电气	
输入频率	50 至 60 岁 Hz
输入电压	220-240 V
基本信息	
MCB 上的产品数量 (16A 类型 B) (标称)	58
灯具数量	1 件/单位
灯具类型	CDM
系统特性	
CDM 的照明功率	39-73 W
额定镇流器照明功率	35-70 W

AspiraVision Compact for CDM

机械和壳体

Order Code	Full Product Name	外壳	Order Code	Full Product Name	外壳
913700683866	HID-AV C 35-70 /S CDM 220-240V 50/60Hz	/S	913700684066	HID-AV C 35-70 /I CDM 220-240V 50/60Hz	/I

