

## Product Description

### HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Impregnated electromagnetic copper/iron double-wattage ballasts for use with an external series (superimposed) ignitor for CDO, MH, HPI (Plus) and SON lamps

#### Benefits

- Up to 40% energy saving using power-reduction controllers
- Minimal watt losses thanks to orthocyclic winding process
- Long-lasting reliable solution protected from overheating

#### Features

- Possibility of dimming with an external controller
- Multi-wattage ballasts can be used only in series circuits
- Equipped with screw terminal blocks as standard; insert contacts available upon request
- Earthing-while-mounting facility
- Ballasts for alternative mains voltages/frequencies available upon request

#### Application

- Ideal for the following applications:
- Road and residential lighting
- Recreational sports lighting, outdoor and indoor
- Floodlighting of buildings and monuments
- Area lighting, e.g. harbors, building sites, city centers, shopping centers, pedestrian areas
- Canopy lighting, e.g. petrol stations
- Climatic suitability: restricted to built-in situations where relative humidity is limited



HID-Basic BSN/BMH series multi-wattage for SON/CDO/CDM/MH/HPI

Versions



BSN 70/50 K302-A2-TS 230V 50Hz

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 70/50 K302-A2-TS 230V 50Hz	123 mm	98 mm	61 mm	52 mm	6.2 mm

