

Long-lasting, reliable solution

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Benefits

- System design: one ignitor SKD578 can trigger all lamps from 35 to 600 W
- Long-lasting reliable solution protected from overheating; better for hot environments than its predecessors; extended warranty
- Minimal watt losses thanks to orthocyclic winding process

Features

- Improved thermal features – much cooler ballast
- All ballasts are equipped with ThermoSwitch for protection against end-of-lamp-life phenomena
- Ballast can also be used in combination with series (superimposed) ignitor
- Equipped with screw terminal blocks as standard; insert contacts available upon request
- Ballasts for alternative mains voltages/frequencies available upon request

Application

- Outdoor lighting
- Horticulture

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Versions







BSN 100 K302-A2-ITS 230V

BSN 250 K302-A2-ITS 230V

GPPR BSN-BC4H 0002

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|--|--------|---------|----------|----------|---------|---------|
| BSN 400 K407-A2-ITS 230/240V 50Hz BC3 | 6.5 mm | 83.0 mm | 166.0 mm | 145.0 mm | 97.0 mm | 78.5 mm |

| Product | A1 | A2 | B1 | C1 | D1 |
|-------------------------------|--------|--------|-------|-------|--------|
| BSN 100 K302-A2-ITS 230V 50Hz | 123 mm | 98 mm | 61 mm | 52 mm | 6.2 mm |
| BSN 250 K302-A2-ITS 230V 50Hz | 160 mm | 139 mm | 76 mm | 65 mm | 6.2 mm |



HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

| Operating and Electrical | |
|--------------------------|-------|
| Input Frequency | 50 Hz |
| Line Frequency | 50 Hz |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage |
|------------|-------------------------------|---------------|
| 74086600 | BSN 100 K302-A2-ITS 230V 50Hz | 230 V |
| 74102300 | BSN 250 K302-A2-ITS 230V 50Hz | 230 V |

| Order Code | Full Product Name | Input Voltage |
|------------|--|--------------------------|
| 88704400 | BSN 400 K407-ITS 230/240V 50Hz BC3-166 | 230 V (default) or 240 V |

