



Ultimate sparkle, unbeatable value

MASTERColour CDM-TC Evolution

Single-ended, highest-efficiency, longest-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high color rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Stable color and lumen output over life keeps your store attractive season after season
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life

Features

- Crisp white sparkling light
- Excellent color rendering, with extra red
- High efficacy with unrivalled lumen maintenance
- Stable color performance over lifetime
- Clean beam

Application

- Accent and display lighting in retail
- General and decorative indoor lighting


MASTERColour CDM-TC Evolution

Versions




CDM-TC Evolution 35W /930

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) |
|------------------------|---------|--------|---------|---------|-------|---------|
| MASTERColour CDM-TC | 15 mm | 5.5 mm | 51 mm | 53 mm | 52 mm | 85 mm |
| Evolution 35W/930 G8.5 | | | | | | |

Light Distribution Diagrams



CDM-TC Evolution 35W /930

