



# Ultimate sparkle, unbeatable value

## MASTERColour CDM-TC Evolution

Single-ended, highest-efficiency, longest-life Ceramic Metal Halide discharge lamp producing crisp white sparkling light with high colour rendering

### Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Stable colour and lumen output over life keeps your store attractive season after season
- Lowest Total Cost of Ownership as a result of high efficacy (same light, less energy or same energy, more light) and long life

### Features

- Crisp white sparkling light
- Excellent colour rendering, with extra red
- High efficacy with unrivalled lumen maintenance
- Stable colour performance over lifetime
- Clean beam

### Application


- Accent and display lighting in retail
- General and decorative indoor lighting

# MASTERColour CDM-TC Evolution

## Versions



## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERColour CDM-TC	15 mm	3.6 mm	51 mm	53 mm	52 mm	85 mm
Evolution 20W/930 G8.5						

## Light Distribution Diagrams

