



Perfect sparkle, easy application

MASTERColour CDM-Rm Elite Mini

Mini, very high-efficiency Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Benefits

- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- High-intensity beam of crisp white sparkling light makes merchandise look irresistible
- Easy to install and replace, reducing installation and relamping costs
- Easy to install and replace, reducing installation and relamping costs
- Fits in small luminaires which are less visible
- Fits in small luminaires which are less visible

Features

- Crisp white sparkling light
- Crisp white sparkling light
- Excellent color rendering, with extra red
- Excellent colour rendering, with extra red
- High efficacy with unparalleled lumen maintenance
- High efficacy with unparalleled lumen maintenance
- Mini design fitting in open luminaires
- Mini design fitting in open luminaires
- UV-blocking front glass
- UV-blocking front glass

MASTERCcolour CDM-Rm Elite Mini

Application

- Accent and display lighting in retail
- Accent and display lighting in retail
- General and decorative indoor lighting
- General and decorative indoor lighting

Warnings and Safety

- Use only with electronic control gear
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

