



# Product Description

## MASTERColour CDM-TC

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Benefits

- Long lamp life compared with incandescent and halogen lamps
- Long lamp life compared with incandescent and halogen lamps
- UV-Block quartz outer bulb for reduced fading risks
- UV-Block quartz outer bulb for reduced fading risks
- Stable color impression over lifetime
- Stable colour impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation (which enhances comfort for shoppers and staff)
- High lamp efficacy results in low operating costs and low heat generation (which enhances comfort for shoppers and staff)

### Features

- Crisp white light
- Warm or cool white colour impression with good colour rendering
- Superior color quality
- Allows very small-size luminaire designs that give high beam intensities
- Allows very small-size luminaires designs that give high beam intensities

### Application


- Accent lighting display lighting with sparkling effect
- Sparkling effect, ideal for accent lighting
- General and decorative lighting
- General and decorative lighting

# MASTERCcolour CDM-TC


## Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/830 G8.5 1CT/12	15 mm	0.5 inch	5 mm	51 mm	53 mm	52 mm	85 mm



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 70W/830 G8.5 1CT/12	15 mm	0.5 inch	7 mm	51 mm	53 mm	52 mm	85 mm



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 70W/842 G8.5 1CT/12	15 mm	5 mm	51 mm	53 mm	52 mm	85 mm

# MASTERCcolour CDM-TC

## General Information

Cap-Base	G8.5
Operating Position	UNIVERSAL

## Controls and Dimming

Dimmable	No
----------	----

## Mechanical and Housing

Bulb Finish	Clear
Bulb Material	UV-Block Quartz
Bulb Shape	T14

## Light Technical

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
928085205125	MASTERC CDM-TC 35W/830 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	81	79 lm/W	3,100 lm
928086505131	MASTERC CDM-TC 70W/830 G8.5 1CT/12	0.434	0.398	Warm White (WW)	3000 K	83	86 lm/W	6,300 lm
928094605131	MASTERC CDM-TC 70W/842 G8.5 1CT/12	0.371	0.366	Cool White (CW)	4200 K	89	79 lm/W	5,800 lm

## Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928085205125	MASTERC CDM-TC 35W/830 G8.5 1CT/12	88 V	39.1 W
928086505131	MASTERC CDM-TC 70W/830 G8.5 1CT/12	83 V	73.2 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928094605131	MASTERC CDM-TC 70W/842 G8.5 1CT/12	88 V	73.2 W

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)
928085205125	MASTERC CDM-TC 35W/830 G8.5 1CT/12	40 kWh	3.1 mg	3.1 mg
928086505131	MASTERC CDM-TC 70W/830 G8.5 1CT/12	74 kWh	4.6 mg	4.6 mg
928094605131	MASTERC CDM-TC 70W/842 G8.5 1CT/12	74 kWh	7 mg	7 mg

