



# Product Description

## MASTERColour CDM-TT

High-intensity discharge lamps with a CDM discharge tube inside a SON lamp clear tubular outer bulb

### Benefits

- Runs on SON gear so directly replaces equivalent wattage SON lamp for simple upgrade from yellow to white light

### Features

- Robust lamp giving a pleasant white light and a stable color over lifetime
- Good color rendering
- Dimming not recommended because of negative effects on lamp performance (lumen maintenance, color and life)

### Application

- City centres, shopping centres and pedestrian areas, residential areas, road lighting
- City beautification: decorative lighting and floodlighting


# MASTERColour CDM-TT

## Versions




CDM-TT, 150W, E40

## Dimensional drawing



Product	D (max)	O	L	C (max)
MASTERColour CDM-TT 150W/942 E40 1SL/12	46 mm	8 mm	133 mm	211 mm

## Light Distribution Diagrams



CDM-TT 150W

