



產品說明

HPL-N

標準型高壓水銀燈

优点

- 預算受限的最佳選擇

特点

- 配備一到二個輔助電極，保證點火快速可靠
- 單端充氣型玻璃燈泡 (HG-SG)，內裝石英水銀蒸氣放電燈管
- 卵形外部燈泡，內裡鍍層處理，產生藍白冷光，光色品質合乎水準

应用

- 所有戶外照明應用，工廠、運輸業和工業區域照明需求

安全提示

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.