



Long-lasting, reliable solution

HID-High Power Basic for SON/MH/HPL

Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above. Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above.

Benefits

- Cost-effective high-performance solution
- Protected from overheating; outstanding product lifetime – 15 years on average
- Minimal watt losses, thanks to orthocyclic winding process

Features

- Aluminum wire ballasts exceeding copper performance
- Equipped as standard with screw terminal blocks
- Separate earth terminal
- Ballasts for alternative mains voltages/frequencies available on request

Application


- Outdoor lighting (most popular application areas: sports and area lighting)

HID-High Power Basic for SON/MH/HPL

Versions



Dimensional drawing



Product	D1	C1	A1	A2	A3	B1	B2
BMH 2000	6.5 mm	111.0	317.0	284.0	317.0	126.0	106.0
L5018-A2-A		mm	mm	mm	mm	mm	mm

