



Long-lasting, reliable solution

HID-High Power Basic for SON/MH/HPL

Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above. Basic aluminum/iron ballasts for use with SON (T) (Plus), HPL, HPI and MH lamps with rated wattages of 1000 W and above

Benefits

- Cost-effective high-performance solution
- Protected from overheating; outstanding product lifetime – 15 years on average
- Minimal watt losses, thanks to orthocyclic winding process

Features

- Aluminum wire ballasts exceeding copper performance
- Equipped as standard with screw terminal blocks
- Separate earth terminal
- Ballasts for alternative mains voltages/frequencies available on request

Application

- Outdoor lighting (most popular application areas: sports and area lighting)

HID-High Power Basic for SON/MH/HPL

Versions



BMH 2000 L5018-A2-A

Dimensional drawing

| Product | D1 | C1 | A1 | A2 | A3 | B1 | B2 |
|------------|-----|-------|-------|-------|-------|-------|-------|
| BMH 2000 | 6.5 | 111.0 | 317.0 | 284.0 | 317.0 | 126.0 | 106.0 |
| L5018-A2-A | mm | mm | mm | mm | mm | mm | mm |

