



# Product Description

## MASTER MHN-LA

Compact quartz metal halide lamps with double-pinch

### Benefits

- Allows compact and efficient luminaire systems with precision optics for good beam control and minimal spill light
- Good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers options for semi-professional stadiums and for professional stadiums with regular TV coverage

### Features

- Compact source (Long Arc) with high luminous efficacy
- Double-pinch concept results in long lifetime
- Natural white color appearance, high color rendering and good color stability
- Daylight color temperature eases transition from daylight to artificial lighting

### Application

- Professional and semi-professional sports lighting and floodlighting

# MASTER MHN-LA


## Versions



MHN-LA 2000W

MHN-LA, 1000W

## Dimensional drawing



Product	D (max)	O	X	A
MASTER MHN-LA 1000W/842 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 2000W/956 400V XWH	40 mm	108 mm	58 mm	353 mm
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 2000W/842 400V XWH	40 mm	108 mm	58 mm	353 mm

### Controls and Dimming

Dimmable No

### General Information

Cap-Base X528

Operating Position P5

### Luminaire Design Requirements

Bulb Temperature (Max) 920 °C

### Mechanical and Housing

Bulb Finish Clear

Bulb Shape TD40

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	2244 kWh	A+	194 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928072505130	MASTER MHN-LA 2000W/956 400V XWH	2244 kWh	A+	130 mg

# MASTER MHN-LA

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928072205130	MASTER MHN-LA 1000W/956 230V XWH	1144 kWh	A	95 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)	Mercury (Hg) Content (Nom)
928073005130	MASTER MHN-LA 1000W/842 230V XWH	1144 kWh	A+	112 mg

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (EM) (Nom)	Voltage (Max)	Voltage (Min)	Voltage (Nom)	Power (Rated) (Nom)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	9.6 A	245 V	220 V	235 V	2040.0 W
928072505130	MASTER MHN-LA 2000W/956 400V XWH	10.3 A	235 V	210 V	225 V	2040.0 W
928072205130	MASTER MHN-LA 1000W/956 230V XWH	9.3 A	140 V	110 V	125 V	1040.0 W
928073005130	MASTER MHN-LA 1000W/842 230V XWH	9.3 A	140 V	110 V	125 V	1040.0 W

## General Information

Order Code	Full Product Name	Life To		Life To	
		Life To 10% Failures (Nom)	20% Failures (Nom)	50% Failures (Nom)	Life To 5% Failures (Nom)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	6000 h	8500 h	13000 h	4500 h
928072505130	MASTER MHN-LA 2000W/956 400V XWH	6000 h	8500 h	13000 h	4500 h

Order Code	Full Product Name	Life To		Life To	
		Life To 10% Failures (Nom)	20% Failures (Nom)	50% Failures (Nom)	Life To 5% Failures (Nom)
928072205130	MASTER MHN-LA 1000W/956 230V XWH	8000 h	10000 h	15000 h	6000 h
928073005130	MASTER MHN-LA 1000W/842 230V XWH	8000 h	10000 h	15000 h	6000 h

## Light Technical (1/2)

Order Code	Full Product Name	Chromaticity	Chromaticity	Color		Correlated Color	Color	Lumen Maintenance
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Color Designation	Temperature (Nom)	Rendering Index (Nom)	1000 h (Nom)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	370	370	842	Cool White (CW)	4200 K	72	94 %
928072505130	MASTER MHN-LA 2000W/956 400V XWH	330	339	956	Daylight	5600 K	82	94 %
928072205130	MASTER MHN-LA 1000W/956 230V XWH	337	331	956	Daylight	5600 K	80	90 %
928073005130	MASTER MHN-LA 1000W/842 230V XWH	366	370	842	Cool White (CW)	4200 K	70	90 %

## Light Technical (2/2)

Order Code	Full Product Name	Lumen Maintenance 10000 h (Nom)	Lumen Maintenance 2000 h (Nom)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	63 %	89 %	76 %	105 lm/W	193000 lm	214000 lm
928072505130	MASTER MHN-LA 2000W/956 400V XWH	63 %	89 %	76 %	93 lm/W	170000 lm	190000 lm
928072205130	MASTER MHN-LA 1000W/956 230V XWH	-	80 %	-	86.0 lm/W	82000 lm	87000 lm

## MASTER MHN-LA

Order Code	Full Product Name	Lumen Maintenance 10000 h (Nom)	Lumen Maintenance 2000 h (Nom)	Lumen Maintenance 5000 h (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Rated) (Min)	Luminous Flux (Rated) (Nom)
928073005130	MASTER MHN-LA 1000W/842 230V XWH	-	80 %	-	92.00 lm/W	85800 lm	95800 lm

