



產品說明

ML

混光燈

优点

- 直接改裝白熾燈泡
- 發光效率和使用壽命皆優於白熾燈

特点

- 高壓水銀燈管串聯鎢絲燈
- 直接以主電源電壓操作，無須額外使用安定器
- 結合白熾燈的連續光譜與高壓水銀燈的線狀光譜

应用

- 停車場、工作室、車庫與店面等戶外公共照明

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.