



GreenSpace – high-efficiency sustainable LED solution

GreenSpace

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Benefits

- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Up to 70% energy saving: total cost of ownership recovered in less than 2 years
- Office lighting norm-compliant, with stable color performance and high color rendering

Features

- Energy-efficient, durable LED technology
- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Stable color performance and high color rendering
- Available with IP44 or emergency lighting
- Available in UGR22 and UGR19 versions

Application

- Offices
- Retail
- Hotels and hospitals

Versions



Standard GreenSpace Surface Mounted



Standard GreenSpace Pendant



Standard GreenSpace Surface Mounted



Greenspace Mini DN462B with Poycarbonate Cover Opal



Greenspace Compact DN472B with Poycarbonate Cover Opal




Standard GreenSpace Surface Mounted



Standard GreenSpace Track Mounted

Dimensional drawing



Product details

Greenspace_EU_gen_2-DN473B-
DPP.TIF




Greenspace_EU_gen_2-DN472B-
DPP.TIF



Product details



Greenspace_EU_gen_2-
DN462_463_472_473B-1DPP.TIF



Greenspace_EU_gen_2-
DN462_463_472_473B-3DPP.TIF



Greenspace_EU_gen_2-
DN462_463_472_473B-2DPP.TIF



Greenspace_EU_gen_2-DN462B-
DPP.TIF



Greenspace_EU_gen_2-DN463B-
DPP.TIF

General Information	
CE mark	Yes
Driver included	Yes
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Line Frequency	50 to 60 Hz
Approval and Application	
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information (1/2)

		ENEC	Flammability	Lamp	
Order Code	Full Product Name	mark	mark	Glow-wire test	family code
01306300	DN461B LED11S/840 PSD-E	ENEC	-	Temperature 650 °C, duration 30 s	-
38467800	DN463B LED11S/840 PSU-E	ENEC	-	Temperature 750 °C, duration 5 s	LED11S
79324100	DN461B LED11S/840 PSU-E	ENEC	-	Temperature 750 °C, duration 5 s	LED11S
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	ENEC	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
56476300	DN470P LED20S/830 PSU D22H16 BK	ENEC	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
98309300	DN471B LED20S/840 WIA-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
01310000	DN471B LED20S/840 PSD-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79331900	DN471B LED20S/830 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79332600	DN471B LED20S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
94584800	DN471B LED30S/840 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
38470800	DN472B LED20S/830 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
38471500	DN472B LED20S/840 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79327200	DN470B LED20S/830 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79328900	DN470B LED20S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
94575600	DN470B LED30S/830 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
94576300	DN470B LED30S/840 PSU-E C WH P	-	-	Temperature 750 °C, duration 5 s	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-	Temperature 750 °C, duration 5 s	-
56472500	DN471C LED20S/840 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-

Order Code	Full Product Name	ENEC mark	Flammability mark	Glow-wire test	Lamp family code
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	-	Temperature 750 °C, duration 5 s	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
38463000	DN462B LED11S/840 PSU-E C PCC WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
79319700	DN460B LED11S/830 PSU-E C WH P	ENEC mark	-	Temperature 650 °C, duration 30 s	LED11S
79320300	DN460B LED11S/840 PSU-E C WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
79336400	DN462B LED11S/840 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED11S
79347000	DN472B LED20S/830 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
79348700	DN472B LED20S/840 PSU-E C WH PCO P	ENEC mark	-	Temperature 750 °C, duration 5 s	LED20S
56460200	DN470C LED20S/840 PSU D22H16 WH	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	-
38948200	DN470T LED20S/840 PSU D22H16 3C BK	ENEC mark	For mounting on normally flammable surfaces	Temperature 650 °C, duration 5 s	LED20S

General Information (2/2)

Order Code	Full Product Name	Product family code	Service tag	Order Code	Full Product Name	Product family code	Service tag
01306300	DN461B LED11S/840 PSD-E C WH P	DN461B	-	38470800	DN472B LED20S/830 PSU-E C WH PCC P	DN472B	Yes
38467800	DN463B LED11S/840 PSU-E C WH PCC P	DN463B	Yes	38471500	DN472B LED20S/840 PSU-E C WH PCC P	DN472B	Yes
79324100	DN461B LED11S/840 PSU-E C WH P	DN461B	Yes	79327200	DN470B LED20S/830 PSU-E C WH P	DN470B	Yes
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	-	-	79328900	DN470B LED20S/840 PSU-E C WH P	DN470B	Yes
56476300	DN470P LED20S/830 PSU D22H16 BK	-	-	79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	DN470B	Yes
98309300	DN471B LED20S/840 WIA-E C WH P	DN471B	-	94575600	DN470B LED30S/830 PSU-E C WH P	DN470B	Yes
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	DN471B	-	94576300	DN470B LED30S/840 PSU-E C WH P	DN470B	Yes
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	DN471B	-	94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	DN470B	Yes
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	DN471B	-	56472500	DN471C LED20S/840 PSU D22H16 WH	-	-
01310000	DN471B LED20S/840 PSD-E C WH P	DN471B	-	98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	DN462B	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	DN473B	Yes	98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	DN462B	-
79331900	DN471B LED20S/830 PSU-E C WH P	DN471B	Yes	38462300	DN462B LED11S/830 PSU-E C WH PCC P	DN462B	Yes
79332600	DN471B LED20S/840 PSU-E C WH P	DN471B	Yes	38463000	DN462B LED11S/840 PSU-E C PCC WH P	DN462B	Yes
94584800	DN471B LED30S/840 PSU-E C WH P	DN471B	Yes	79319700	DN460B LED11S/830 PSU-E C WH P	DN460B	Yes
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	DN471B	Yes	79320300	DN460B LED11S/840 PSU-E C WH P	DN460B	Yes
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	DN470B	-	79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	DN460B	Yes
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	DN472B	-	79336400	DN462B LED11S/840 PSU-E C WH PCO P	DN462B	Yes
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	DN472B	-	79347000	DN472B LED20S/830 PSU-E C WH PCO P	DN472B	Yes
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	DN472B	-	79348700	DN472B LED20S/840 PSU-E C WH PCO P	DN472B	Yes

Order Code	Full Product Name	Product family code	Service tag
56460200	DN470C LED20S/840 PSU D22H16 WH	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01306300	DN461B LED11S/840 PSD-E C WH P	-	4000 K	130 lm/W	1,250 lm
38467800	DN463B LED11S/840 PSU-E C WH PCC P	- degree(s)	4000 K	123 lm/W	1,200 lm
79324100	DN461B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	122 lm/W	1,250 lm
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	88 degree(s)	4000 K	133 lm/W	2,200 lm
56476300	DN470P LED20S/830 PSU D22H16 BK	120 degree(s)	3000 K	132 lm/W	2,200 lm
98309300	DN471B LED20S/840 WIA-E C WH P	- degree(s)	4000 K	120 lm/W	1,950 lm
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	120 lm/W	1,900 lm
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	123 lm/W	1,950 lm
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	128 lm/W	3,000 lm
01310000	DN471B LED20S/840 PSD-E C WH P	-	4000 K	128 lm/W	1,950 lm
38475300	DN473B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	125 lm/W	1,900 lm
79331900	DN471B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	125 lm/W	1,900 lm

Order Code	Full Product Name	Product family code	Service tag
38948200	DN470T LED20S/840 PSU D22H16 3C BK	-	-

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
79332600	DN471B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	131 lm/W	2,000 lm
94584800	DN471B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	131 lm/W	2,950 lm
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	131 lm/W	2,950 lm
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	128 lm/W	3,000 lm
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	117 lm/W	1,850 lm
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	119 lm/W	2,800 lm
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	123 lm/W	2,900 lm
38470800	DN472B LED20S/830 PSU-E C WH PCC P	- degree(s)	3000 K	125 lm/W	1,900 lm
38471500	DN472B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	131 lm/W	2,000 lm
79327200	DN470B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	131 lm/W	2,000 lm
79328900	DN470B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	138 lm/W	2,100 lm
79352400	DN470B LED20S/840	- degree(s)	4000 K	138 lm/W	2,100 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSU-E C ELP3 WH P				
94575600	DN470B LED30S/830 PSU-E C WH P	- degree(s)	3000 K	128 lm/W	2,900 lm
94576300	DN470B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	137 lm/W	3,100 lm
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	137 lm/W	3,100 lm
56472500	DN471C LED20S/840 PSU D22H16 WH	88 degree(s)	4000 K	131 lm/W	2,200 lm
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	109 lm/W	1,150 lm
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	114 lm/W	1,200 lm
38462300	DN462B LED11S/830 PSU-E C WH PCC P	- degree(s)	3000 K	123 lm/W	1,200 lm
38463000	DN462B LED11S/840	- degree(s)	4000 K	128 lm/W	1,250 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSU-E C PCC WH P				
79319700	DN460B LED11S/830 PSU-E C WH P	- degree(s)	3000 K	122 lm/W	1,250 lm
79320300	DN460B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	127 lm/W	1,300 lm
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	127 lm/W	1,300 lm
79336400	DN462B LED11S/840 PSU-E C WH PCO P	- degree(s)	4000 K	118 lm/W	1,150 lm
79347000	DN472B LED20S/830 PSU-E C WH PCO P	- degree(s)	3000 K	106 lm/W	2,050 lm
79348700	DN472B LED20S/840 PSU-E C WH PCO P	- degree(s)	4000 K	109 lm/W	2,100 lm
56460200	DN470C LED20S/840 PSU D22H16 WH	120 degree(s)	4000 K	138 lm/W	2,300 lm
38948200	DN470T LED20S/840 PSU D22H16 3C BK	120 degree(s)	4000 K	138 lm/W	2,300 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
01306300	DN461B LED11S/840 PSD-E C WH P	-	-	0.4
38467800	DN463B LED11S/840 PSU-E C WH PCC P	1	-	-
79324100	DN461B LED11S/840 PSU-E C WH P	1	-	-
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	-	1	0.4

Order Code	Full Product Name	Number of light sources	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
56476300	DN470P LED20S/830 PSU D22H16 BK	-	1	0.4
98309300	DN471B LED20S/840 WIA-E C WH P	-	-	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	-	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	-	-

Order Code	Full Product Name	Number of light sources	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	-	-	-
01310000	DN471B LED20S/840 PSD-E C WH P	-	-	-	0.4
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1	-	-	-
79331900	DN471B LED20S/830 PSU-E C WH P	1	-	-	-
79332600	DN471B LED20S/840 PSU-E C WH P	1	-	-	-
94584800	DN471B LED30S/840 PSU-E C WH P	-	-	-	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-	-	-	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	-	-	-
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	-	-	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	-	-	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	-	-	-
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1	-	-	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1	-	-	-
79327200	DN470B LED20S/830 PSU-E C WH P	1	-	-	-
79328900	DN470B LED20S/840 PSU-E C WH P	1	-	-	-
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1	-	-	-

Order Code	Full Product Name	Number of light sources	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		Stroboscopic effect visibility measure (SVM)
94575600	DN470B LED30S/830 PSU-E C WH P	-	-	-	-
94576300	DN470B LED30S/840 PSU-E C WH P	-	-	-	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-	-	-
56472500	DN471C LED20S/840 PSU D22H16 WH	-	1	-	0.4
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-	-	-	-
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	-	-	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1	-	-	-
38463000	DN462B LED11S/840 PSU-E C PCC WH P	1	-	-	-
79319700	DN460B LED11S/830 PSU-E C WH P	1	-	-	0.4
79320300	DN460B LED11S/840 PSU-E C WH P	1	-	-	-
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1	-	-	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1	-	-	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1	-	-	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1	-	-	-
56460200	DN470C LED20S/840 PSU D22H16 WH	-	1	-	0.4
38948200	DN470T LED20S/840 PSU D22H16 3C BK	1	1	-	0.4

Operating and Electrical

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
01306300	DN461B LED11S/840 PSD-E C WH P	220-240 V	9.6 W
38467800	DN463B LED11S/840 PSU-E C WH PCC P	220 to 240 V	9.7 W
79324100	DN461B LED11S/840 PSU-E C WH P	220-240 V	10.2 W
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	220 to 240 V	16.2 W
56476300	DN470P LED20S/830 PSU D22H16 BK	220 to 240 V	16.4 W
98309300	DN471B LED20S/840 WIA-E C WH P	220-240 V	16.2 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	220-240 V	15.8 W
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	220-240 V	15.8 W
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	220-240 V	23.5 W
01310000	DN471B LED20S/840 PSD-E C WH P	220-240 V	15.2 W
38475300	DN473B LED20S/840 PSU-E C WH PCC P	220 to 240 V	15.2 W
79331900	DN471B LED20S/830 PSU-E C WH P	220-240 V	15.2 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
79332600	DN471B LED20S/840 PSU-E C WH P	220-240 V	15.2 W
94584800	DN471B LED30S/840 PSU-E C WH P	220-240 V	22.5 W
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	220-240 V	22.5 W
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	220-240 V	23.5 W
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	220-240 V	15.8 W
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	23.5 W
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	220-240 V	23.5 W
38470800	DN472B LED20S/830 PSU-E C WH PCC P	220 to 240 V	15.2 W
38471500	DN472B LED20S/840 PSU-E C WH PCC P	220 to 240 V	15.2 W
79327200	DN470B LED20S/830 PSU-E C WH P	220-240 V	15.2 W
79328900	DN470B LED20S/840 PSU-E C WH P	220-240 V	15.2 W
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	220-240 V	15.2 W
94575600	DN470B LED30S/830 PSU-E C WH P	220-240 V	22.5 W
94576300	DN470B LED30S/840 PSU-E C WH P	220-240 V	22.5 W
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	220-240 V	22.5 W

Temperature

Order Code	Full Product Name	Ambient temperature range
01306300	DN461B LED11S/840 PSD-E C WH P	+10 to +40 °C
38467800	DN463B LED11S/840 PSU-E C WH PCC P	-15 to +40 °C
79324100	DN461B LED11S/840 PSU-E C WH P	+10 to +40 °C
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	+10 to +40 °C
56476300	DN470P LED20S/830 PSU D22H16 BK	+10 to +40 °C
98309300	DN471B LED20S/840 WIA-E C WH P	+10 to +40 °C
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C
01310000	DN471B LED20S/840 PSD-E C WH P	+10 to +40 °C
38475300	DN473B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C
79331900	DN471B LED20S/830 PSU-E C WH P	+10 to +40 °C
79332600	DN471B LED20S/840 PSU-E C WH P	+10 to +40 °C
94584800	DN471B LED30S/840 PSU-E C WH P	+10 to +40 °C
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C

Order Code	Full Product Name	Input Voltage	Power
			Consumption
56472500	DN471C LED20S/840 PSU D22H16 WH	220 to 240 V	16.4 W
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	220-240 V	10.6 W
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	220-240 V	10.6 W
38462300	DN462B LED11S/830 PSU-E C WH PCC P	220 to 240 V	9.7 W
38463000	DN462B LED11S/840 PSU-E C PCC WH P	220 to 240 V	9.7 W
79319700	DN460B LED11S/830 PSU-E C WH P	220-240 V	10.2 W
79320300	DN460B LED11S/840 PSU-E C WH P	220-240 V	10.2 W
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	220-240 V	10.2 W
79336400	DN462B LED11S/840 PSU-E C WH PCO P	220-240 V	9.7 W
79347000	DN472B LED20S/830 PSU-E C WH PCO P	220-240 V	19.2 W
79348700	DN472B LED20S/840 PSU-E C WH PCO P	220-240 V	19.2 W
56460200	DN470C LED20S/840 PSU D22H16 WH	220 to 240 V	16.4 W
38948200	DN470T LED20S/840 PSU D22H16 3C BK	220 to 240 V	16.4 W

Order Code	Full Product Name	Ambient temperature range
38470800	DN472B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C
38471500	DN472B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C
79327200	DN470B LED20S/830 PSU-E C WH P	+10 to +40 °C
79328900	DN470B LED20S/840 PSU-E C WH P	+10 to +40 °C
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	+10 to +40 °C
94575600	DN470B LED30S/830 PSU-E C WH P	+10 to +40 °C
94576300	DN470B LED30S/840 PSU-E C WH P	+10 to +40 °C
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C
56472500	DN471C LED20S/840 PSU D22H16 WH	+10 to +40 °C
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	+10 to +40 °C
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C
38462300	DN462B LED11S/830 PSU-E C WH PCC P	-15 to +40 °C
38463000	DN462B LED11S/840 PSU-E C PCC WH P	-15 to +40 °C
79319700	DN460B LED11S/830 PSU-E C WH P	+10 to +40 °C
79320300	DN460B LED11S/840 PSU-E C WH P	+10 to +40 °C
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	+10 to +40 °C
79336400	DN462B LED11S/840 PSU-E C WH PCO P	-15 to +40 °C
79347000	DN472B LED20S/830 PSU-E C WH PCO P	-15 to +40 °C
79348700	DN472B LED20S/840 PSU-E C WH PCO P	-15 to +40 °C
56460200	DN470C LED20S/840 PSU D22H16 WH	+10 to +40 °C
38948200	DN470T LED20S/840 PSU D22H16 3C BK	+10 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
01306300	DN461B LED11S/840 PSD-E C WH P	Yes
38467800	DN463B LED11S/840 PSU-E C WH PCC P	No
79324100	DN461B LED11S/840 PSU-E C WH P	No
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	Yes
56476300	DN470P LED20S/830 PSU D22H16 BK	No
98309300	DN471B LED20S/840 WIA-E C WH P	Yes
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	Yes
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	Yes
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	Yes
01310000	DN471B LED20S/840 PSD-E C WH P	Yes
38475300	DN473B LED20S/840 PSU-E C WH PCC P	No
79331900	DN471B LED20S/830 PSU-E C WH P	No
79332600	DN471B LED20S/840 PSU-E C WH P	No
94584800	DN471B LED30S/840 PSU-E C WH P	No
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	No
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	Yes
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	Yes
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	Yes
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	Yes
38470800	DN472B LED20S/830 PSU-E C WH PCC P	No

Order Code	Full Product Name	Dimmable
38471500	DN472B LED20S/840 PSU-E C WH PCC P	No
79327200	DN470B LED20S/830 PSU-E C WH P	No
79328900	DN470B LED20S/840 PSU-E C WH P	No
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	No
94575600	DN470B LED30S/830 PSU-E C WH P	No
94576300	DN470B LED30S/840 PSU-E C WH P	No
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	No
56472500	DN471C LED20S/840 PSU D22H16 WH	No
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	Yes
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	Yes
38462300	DN462B LED11S/830 PSU-E C WH PCC P	No
38463000	DN462B LED11S/840 PSU-E C PCC WH P	No
79319700	DN460B LED11S/830 PSU-E C WH P	No
79320300	DN460B LED11S/840 PSU-E C WH P	No
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	No
79336400	DN462B LED11S/840 PSU-E C WH PCO P	No
79347000	DN472B LED20S/830 PSU-E C WH PCO P	No
79348700	DN472B LED20S/840 PSU-E C WH PCO P	No
56460200	DN470C LED20S/840 PSU D22H16 WH	No
38948200	DN470T LED20S/840 PSU D22H16 3C BK	No

Mechanical and Housing

Order Code	Full Product Name	Housing Color
01306300	DN461B LED11S/840 PSD-E C WH P	White
38467800	DN463B LED11S/840 PSU-E C WH PCC P	White
79324100	DN461B LED11S/840 PSU-E C WH P	White
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	Black
56476300	DN470P LED20S/830 PSU D22H16 BK	Black
98309300	DN471B LED20S/840 WIA-E C WH P	White
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	White
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	White
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	White
01310000	DN471B LED20S/840 PSD-E C WH P	White
38475300	DN473B LED20S/840 PSU-E C WH PCC P	White
79331900	DN471B LED20S/830 PSU-E C WH P	White
79332600	DN471B LED20S/840 PSU-E C WH P	White
94584800	DN471B LED30S/840 PSU-E C WH P	White
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	White
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	White
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	White
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	White
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	White
38470800	DN472B LED20S/830 PSU-E C WH PCC P	White

Order Code	Full Product Name	Housing Color
38471500	DN472B LED20S/840 PSU-E C WH PCC P	White
79327200	DN470B LED20S/830 PSU-E C WH P	White
79328900	DN470B LED20S/840 PSU-E C WH P	White
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	White
94575600	DN470B LED30S/830 PSU-E C WH P	White
94576300	DN470B LED30S/840 PSU-E C WH P	White
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	White
56472500	DN471C LED20S/840 PSU D22H16 WH	White
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	White
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	White
38462300	DN462B LED11S/830 PSU-E C WH PCC P	White
38463000	DN462B LED11S/840 PSU-E C PCC WH P	White
79319700	DN460B LED11S/830 PSU-E C WH P	White
79320300	DN460B LED11S/840 PSU-E C WH P	White
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	White
79336400	DN462B LED11S/840 PSU-E C WH PCO P	White
79347000	DN472B LED20S/830 PSU-E C WH PCO P	White
79348700	DN472B LED20S/840 PSU-E C WH PCO P	White
56460200	DN470C LED20S/840 PSU D22H16 WH	White
38948200	DN470T LED20S/840 PSU D22H16 3C BK	Black

Approval and Application

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
01306300	DN461B LED11S/840 PSD-E C WH P	IK02	IP20
38467800	DN463B LED11S/840 PSU-E C WH PCC P	IK06	IP54
79324100	DN461B LED11S/840 PSU-E C WH P	IK02	IP20
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	IK02	IP20
56476300	DN470P LED20S/830 PSU D22H16 BK	IK02	IP20
98309300	DN471B LED20S/840 WIA-E C WH P	IK02	IP20
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	IK02	IP20
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	IK02	IP20
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
01310000	DN471B LED20S/840 PSD-E C WH P	IK02	IP20
38475300	DN473B LED20S/840 PSU-E C WH PCC P	IK06	IP54
79331900	DN471B LED20S/830 PSU-E C WH P	IK02	IP20
79332600	DN471B LED20S/840 PSU-E C WH P	IK02	IP20
94584800	DN471B LED30S/840 PSU-E C WH P	IK02	IP20
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	IK02	IP20
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	IK02	IP20
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	IK02	IP54
38470800	DN472B LED20S/830 PSU-E C WH PCC P	IK06	IP54
38471500	DN472B LED20S/840 PSU-E C WH PCC P	IK06	IP54

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01306300	DN461B LED11S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
38467800	DN463B LED11S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
79324100	DN461B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	(0.38, 0.38) SDCM<3
56476300	DN470P LED20S/830 PSU D22H16 BK	(0.43, 0.40) SDCM<3
98309300	DN471B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
01310000	DN471B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
38475300	DN473B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
79331900	DN471B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79332600	DN471B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
94584800	DN471B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
38470800	DN472B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3

Order Code	Full Product Name	Mech. impact	Ingress
		protection code	protection code
79327200	DN470B LED20S/830 PSU-E C WH P	IK02	IP20
79328900	DN470B LED20S/840 PSU-E C WH P	IK02	IP20
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	IK02	IP20
94575600	DN470B LED30S/830 PSU-E C WH P	IK02	IP20
94576300	DN470B LED30S/840 PSU-E C WH P	IK02	IP20
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20
56472500	DN471C LED20S/840 PSU D22H16 WH	IK02	IP20
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	IK02	IP20
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	IK02	IP20
38462300	DN462B LED11S/830 PSU-E C WH PCC P	IK06	IP54
38463000	DN462B LED11S/840 PSU-E C PCC WH P	IK06	IP54
79319700	DN460B LED11S/830 PSU-E C WH P	IK02	IP20
79320300	DN460B LED11S/840 PSU-E C WH P	IK02	IP20
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	IK02	IP20
79336400	DN462B LED11S/840 PSU-E C WH PCO P	IK06	IP54
79347000	DN472B LED20S/830 PSU-E C WH PCO P	IK06	IP54
79348700	DN472B LED20S/840 PSU-E C WH PCO P	IK06	IP54
56460200	DN470C LED20S/840 PSU D22H16 WH	IK02	IP20
38948200	DN470T LED20S/840 PSU D22H16 3C BK	IK02	IP20

Order Code	Full Product Name	Initial chromaticity
38471500	DN472B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
79327200	DN470B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79328900	DN470B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
94575600	DN470B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
94576300	DN470B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
56472500	DN471C LED20S/840 PSU D22H16 WH	(0.38, 0.38) SDCM<3
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
38462300	DN462B LED11S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
38463000	DN462B LED11S/840 PSU-E C PCC WH P	(0.38, 0.38) SDCM<3
79319700	DN460B LED11S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79320300	DN460B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
79336400	DN462B LED11S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3
79347000	DN472B LED20S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3
79348700	DN472B LED20S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3
56460200	DN470C LED20S/840 PSU D22H16 WH	(0.38, 0.38) SDCM<3
38948200	DN470T LED20S/840 PSU D22H16 3C BK	(0.38, 0.38) SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000	
		h	
01306300	DN461B LED11S/840 PSD-E C WH P	-	
38467800	DN463B LED11S/840 PSU-E C WH PCC P	1 %	
79324100	DN461B LED11S/840 PSU-E C WH P	1 %	
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	-	
56476300	DN470P LED20S/830 PSU D22H16 BK	-	
98309300	DN471B LED20S/840 WIA-E C WH P	-	
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	
01310000	DN471B LED20S/840 PSD-E C WH P	-	
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1 %	
79331900	DN471B LED20S/830 PSU-E C WH P	1 %	
79332600	DN471B LED20S/840 PSU-E C WH P	1 %	
94584800	DN471B LED30S/840 PSU-E C WH P	1 %	
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	1 %	
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1 %	

Order Code	Full Product Name	Driver failure rate at 5000	
		h	
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1 %	
79327200	DN470B LED20S/830 PSU-E C WH P	1 %	
79328900	DN470B LED20S/840 PSU-E C WH P	1 %	
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1 %	
94575600	DN470B LED30S/830 PSU-E C WH P	1 %	
94576300	DN470B LED30S/840 PSU-E C WH P	1 %	
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	1 %	
56472500	DN471C LED20S/840 PSU D22H16 WH	-	
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-	
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1 %	
38463000	DN462B LED11S/840 PSU-E C PCC WH P	1 %	
79319700	DN460B LED11S/830 PSU-E C WH P	1 %	
79320300	DN460B LED11S/840 PSU-E C WH P	1 %	
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1 %	
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1 %	
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1 %	
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1 %	
56460200	DN470C LED20S/840 PSU D22H16 WH	-	
38948200	DN470T LED20S/840 PSU D22H16 3C BK	1 %	

Application Conditions

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
01306300	DN461B LED11S/840 PSD-E C WH P	1%	Yes
38467800	DN463B LED11S/840 PSU-E C WH PCC P	Not applicable	Yes
79324100	DN461B LED11S/840 PSU-E C WH P	Not applicable	Yes
56467100	DN471C LED20S/840 DIA-VLC D22H16 BK	1%	No
56476300	DN470P LED20S/830 PSU D22H16 BK	Not applicable	No
98309300	DN471B LED20S/840 WIA-E C WH P	1%	Yes
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	1%	Yes
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	1%	Yes
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	1%	Yes
01310000	DN471B LED20S/840 PSD-E C WH P	1%	Yes
38475300	DN473B LED20S/840 PSU-E C WH PCC P	Not applicable	Yes
79331900	DN471B LED20S/830 PSU-E C WH P	Not applicable	Yes
79332600	DN471B LED20S/840 PSU-E C WH P	Not applicable	Yes
94584800	DN471B LED30S/840 PSU-E C WH P	Not applicable	Yes
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	Not applicable	Yes
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	1%	Yes
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	1%	Yes
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	1%	Yes

Order Code	Full Product Name	Suitable for	
		Maximum dim level	random switching
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	1%	Yes
38470800	DN472B LED20S/830 PSU-E C WH PCC P	Not applicable	Yes
38471500	DN472B LED20S/840 PSU-E C WH PCC P	Not applicable	Yes
79327200	DN470B LED20S/830 PSU-E C WH P	Not applicable	Yes
79328900	DN470B LED20S/840 PSU-E C WH P	Not applicable	Yes
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	Not applicable	Yes
94575600	DN470B LED30S/830 PSU-E C WH P	Not applicable	Yes
94576300	DN470B LED30S/840 PSU-E C WH P	Not applicable	Yes
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	Not applicable	Yes
56472500	DN471C LED20S/840 PSU D22H16 WH	Not applicable	No
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	1%	Yes
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	1%	Yes
38462300	DN462B LED11S/830 PSU-E C WH PCC P	Not applicable	Yes
38463000	DN462B LED11S/840 PSU-E C PCC WH P	Not applicable	Yes
79319700	DN460B LED11S/830 PSU-E C WH P	Not applicable	Yes
79320300	DN460B LED11S/840 PSU-E C WH P	Not applicable	Yes
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
79336400	DN462B LED11S/840 PSU-E C WH PCO P	Not applicable	Yes
79347000	DN472B LED20S/830 PSU-E C WH PCO P	Not applicable	Yes
79348700	DN472B LED20S/840 PSU-E C WH PCO P	Not applicable	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
56460200	DN470C LED20S/840 PSU D22H16 WH	Not applicable	No
38948200	DN470T LED20S/840 PSU D22H16 3C BK	Not applicable	No

